




1 2 3 4 5 6 7 8

RevNo		Date	Signature	Checked
-------	--	------	-----------	---------



104XXFXXX - - - - L F	
D-Sub 90D	Vacant:Default PBT
Typ	P2:PA6T
15	P3:LCP
26 Female	P4:PA9T
44	Vacant:No Screw
62 8.Nickel	S:4.8
	L:5.8
	Vacant:No Accessories
	V0.Coalescent Nut H=5.8
	V.Lock Screw.
	VI.With Screw.
	VII.Additional Screw.
1.White	Vacant:Default 1u'
3.Black	3.3u'
4.Yellow	5.5u'
6.Green	6.10u'
9.Blue	7.15u'
10.PC99	8.30u'
	1 Full Gold
	2 Half Gold

Note:

No.	A	B	C	E	F	H
15	16.33	24.99	30.81	2.29	1.145	7.04
26	24.66	33.32	39.14	2.29	1.145	6.88
44	38.38	47.04	53.04	2.29	1.145	6.88
62	54.84	63.50	69.32	2.41	1.205	7.00




ELECTRICAL CHARACTERISTICS

Contact Current Rating:3Amperes.
 Dielectric Withstanding Voltage:AC 500V at sea level.
 Insulation Resistance:1000Megohms Min.
 Contact Resistance:25Milliohms Max.
 Operation Temperature : -55°C to +105°C.






Material

Contact :Copper Alloy.
 Insulator:PBT. **(Select PA6T /LCP /PA9T)**
 Shell: SPCC.
 Z-Piece: Copper Alloy.
 Screw: Copper Alloy.
 Rivet: Copper Alloy. or Zinc.

Re Layout P.C.B.
15 POSITION



Re Layout P.C.B.
26 /44 /62 POSITION



DRAW.BY	LinHaiFong	DATE	2005-10-10	UNIT	MM	TOLERANCE UNSPECIFIED	.X ±0.30 .XX ±0.25 .XXX ±0.150	Ang. ±2°
APPVL.BY		VERSION	A	SCALE		DWG.No.	F:/XX/ / +	

Chin Shong
Enterprise CO., LTD.

ITEM	D-SUB H-D Female 90D-DIP
PART No.	
CUSTOMER	

1 2 3 4 5 6 7 8