

FLUKE®



General specifications

	62 Max	62 Max+
<b>Temperature range</b>	-30 °C to 500 °C (-22 °F to 932 °F)	-30 °C to 650 °C (-22 °F to 1202 °F)
<b>Accuracy</b>	± 1.5 °C or ± 1.5 % of reading ± 2.0 at -10 °C to 0 °C ± 3.0 at -30 °C to -10 °C	± 1. °C or ± 1.0 % of reading ± 2.0 at -10 °C to 0 °C ± 3.0 at -30 °C to -10 °C
<b>Response time (95 %)</b>	<500 ms (95 % of reading) Spectral Response: 8 to 14 microns Emissivity: 0.10 to 1.00	<300 ms (95 % of reading) Spectral Response: 8 to 14 microns Emissivity: 0.10 to 1.00
<b>Optical resolution</b>	10:1 (calculated at 90 % energy)	12:1 (calculated at 90 % energy)
<b>Display resolution</b>	0.1 °C (0.2 °F)	0.1 °C (0.2 °F)
<b>Repeatability of readings</b>	± 0.8 % of reading or <± 1.0 °C (2 °F), whichever is greater	± 0.5 % of reading or <± 0.5 °C (1 °F), whichever is greater
<b>Power</b>	AA battery	AA battery

➔ Learn more: [www.fluke.co.uk/62max](http://www.fluke.co.uk/62max)

**Fluke Europe B.V.**  
P.O. Box 1186  
5602 BD Eindhoven  
The Netherlands  
Web: [www.fluke.com](http://www.fluke.com)

**For more information call:**  
In Europe/M-East/Africa  
+31 (0) 40 2 675 200 or  
Fax +31 (0) 40 2 675 222

**Fluke (UK) Ltd.**  
52 Hurricane Way  
Norwich, Norfolk  
NR6 6JB  
United Kingdom  
Tel.: +44 (0) 20 7942 0700  
Fax: +44 (0) 20 7942 0701  
E-mail: [industrial@uk.fluke.nl](mailto:industrial@uk.fluke.nl)  
Web: [www.fluke.co.uk](http://www.fluke.co.uk)

© Copyright 2012 Fluke Corporation. All rights reserved. Printed in The Netherlands 06/2012. Data subject to alteration without notice. Pub\_ID: 11928-eng

Modification of this document is not permitted without written permission from Fluke Corporation.

FLUKE®

# TAKES THE HEAT.

## AND THE DUST, WATER AND 3-METER DROP.

Introducing the new 62 Max IR Thermometers from Fluke.





## Introducing the Fluke 62 MAX and 62 MAX+ IR Thermometers: Small in size. Big on toughness.

### Why IR Thermometers?

Temperature is often the first indication of potential problems in electrical and mechanical applications. But how can you easily determine if an electrical panel has a hot spot, a motor is overheating or an HVAC system is inefficient? The answer is with an infrared (IR) thermometer. With handheld, non-contact IR thermometers, you can instantly measure equipment temperatures in hard-to-reach or hazardous areas. And with early detection of abnormal temperatures comes early correction of problems.

### Why Fluke 62 MAX and Fluke 62 MAX+?

Designed with your on-the-job needs in mind, the new Fluke 62 MAX and 62 MAX+ infrared thermometers are everything you'd expect from the experts in measurement tools: small in size, extremely accurate and very easy to use. IP54 rated for dust and water resistance. Precise yet rugged enough to take a 3-meter drop. In fact, the 62 MAX and 62 MAX+ are so tough, they're the only IR thermometers around you can handle without care.

**Dust and water-resistant:** IP54 rated for dust and water resistance.

**Rugged:** 3-meter (9.8-foot) drop tested.

**Ergonomically designed:** Completely redesigned for a more comfortable hand fit

**Small in size:** Small and lightweight; clips to your tool belt or belt loop or easily fits into your tool box.

**Distance to spot:** Precise laser technology makes for more accurate and repeatable measurements.

**Dual lasers:** The 62 MAX+ has dual rotating lasers to help you identify area to be measured. The measurement area is the spot between the dots.

**Large, backlit display:** Large screen makes data easier to read, even in dark areas.

**Min/Max/Avg/Dif:** Displays the minimum, maximum or average temperature, or the difference between two measurements.

**Alarm:** Hi and Lo alarms for rapid display of measurements outside the limits.

**Power:** Both the 62 MAX and 62 MAX+ are powered by a single, standard AA battery.



Learn more: [www.fluke.co.uk/62max](http://www.fluke.co.uk/62max)