

POS Printer

# RP-F10



RP-F10



RP-F10 + LCD(Optional)

- 2-way : Paper top-exit and front-exit (IPx1)
- Compact cube : 127mm x 127mm x 127mm
- Max printing speed : 250mm/sec
- Optional 4.3 inch color LCD can be mounted on RP-F10
- Easy pairing with a Bluetooth terminal via NFC (Bluetooth Model)
- Cutter lock automatic restoration mechanism
- Various drivers and wide variety utility software

Model		RP-F10
Printing	Method	Thermal line dot printing
	Resolution (dpi)	203(8dots/mm)
	Paper width (mm)	58 <sup>+0</sup> / 80 <sup>+0</sup> <sub>-1</sub>
	Printing width (mm)	54 / 72
	Speed (mm/sec) max	250
	Outside diameter of paper roll (mm) max	Φ83
	Character matrix (H x W dots)	24 x 12, 24 x 24, 16 x 8, 16 x 16
	Character size (H x W mm)	3.0 x 1.5, 3.0 x 3.0, 2.0 x 1.0, 2.0 x 2.0
Type of paper	Roll paper	
Character type	Code page(14pages), International character, Optional font, Downloaded character, JIS 1&2 Level Kanji Special character, User-defined character	
Bar code	UPC-A/E, JAN(EAN)8/13, ITF, CODABAR, Code39, Code93, Code128, QR, PDF417, GS1 Databar	
Power supply	Specified AC adapter, External power (DC24±10%)	
Communication interface	USB+USB-host, Ethernet+USB-host, Bluetooth (NFC)+USB-host, Powered USB	
Input buffer	4K bytes	
Command	ESC/POS™ conformity	
Cutting	Method	Slide type
	Cutting type	Full cut, Partial cut (Leave center point)
Operating Temperature (°C)	5 to 45	
Service life	Abrasion resistance (km)	150 *1
	Paper cutting (cut)	1,500,000 *1
Dimensions (W×D×Hmm)	127.0 x 127.0 x 127.0 <sup>*4</sup>	
Mass (g)	Approx. 840	
Standard	FCC, CE, VCCI	
Option	Wall mounting Kit, Buzzer, LCD (4.3inch color)	
Cash drawer	2 drivers (24V / 1A)	
Body color	2 colors : White / Black	
Software	Windows® : Printer Driver, Virtual COM Driver, OPOS Driver, POS for .Net Driver / SDK / Utility Linux® : CUPS Filter (Driver) / Communication Library (SDK) Android™ : SDK / Utility, iOS:SDK/Utility	

\*1 Use recommended thermal papers. \*2 Excluding protrusion

ESC/POS™: Registered trademark of SEIKO EPSON CORP.  
Windows® is the registered trademark of Microsoft Corporation(USA).  
Android™ is a trademark of Google Inc.  
This product is under development. The specs are subject to change.

Printed in Apr. 2019



Seiko Instruments Inc.  
Print System Div.  
8, Nakase 1-chome, Mihama-ku  
Chiba-shi, Chiba 261-8507, Japan  
Telephone: +81-43-211-1106 Facsimile: +81-43-211-8037  
Homepage: <http://www.sii-ps.com>

Seiko Instruments U.S.A., Inc.  
21221 S. Western Ave., Suite 250, Torrance, CA 90501, USA.  
Telephone: +1-310-517-7778 Facsimile: +1-310-517-7779  
Homepage: <http://www.siiprinters.com>

Seiko Instruments GmbH  
Siemensstrasse 9 D-63263 Neu-Isenburg, Germany  
Telephone: +49-6102-297-0 Facsimile: +49-6102-297-222  
E-mail: [info@seiko-instruments.de](mailto:info@seiko-instruments.de)  
Homepage: <http://www.seiko-instruments.de>

