

Substance **RoHS** **WEEE**

Lead Free





MATERIAL:

Insulator: 30% Glasses filled in P.B.T. UL-94V-0.
 Contact: Brass.
 Plated: Full Tin or Gold Plated over Nickel.(Lead Free)

SPECIFICATION:

Contact Resistance: 10MΩ Max. at DC 1A.
 Insulator Resistance: 500MΩ Min. at 500V.
 Current Rating: 1A Dielectric Withstanding.
 Voltage Rating: AC 5000 for one minute.
 Operating Temperature: -55°C to +105°C.

PIN HEADER 2.0 mm Pitch.



Ordering Information: For example: SD-2MM-40-T1

SS - 2MM - (No. of Pins) - (G or T1)
 SD - 2MM - (No. of Pins) - (G or T1)
 RS - 2MM - (No. of Pins) - (G or T1) **G: Full Gold Plated**
 RD - 2MM - (No. of Pins) - (G or T1) **T1: Full Tin Plated(Lead Free).**

SS: Straight, Single row. RS: R/A, Single row.
SD: Straight, Dual row. RD: R/A, Dual row.

FEATURES:

- Low Profile Header body helps maximum packing.
- Available with Wrap post tail header
- Available with Straight or Right Angle pins.
- Available with Customer Design and Dual body.
- Pin Header suitable for mating with 2.0mm Pitch Female Header.
- 2.0mm pitch used 0.50mm square pins.

Special Pins Length: (2.0 mm Pitch)

