



Visit
tosibox.com
for more
information

TOSIBOX® SOLUTIONS AND SERVICES

Your secure and scalable solution from
remote access to global OT networking

TOSIBOX

NODE

CONTENTS

TOSIBOX PLATFORM	3
TOSIBOX® NODES	
TOSIBOX® Lock 150	4
TOSIBOX® 175	5
TOSIBOX® Lock 500	6
TOSIBOX® 610	8
TOSIBOX® 650	9
TOSIBOX® 670	10
TOSIBOX® 675	11
TOSIBOX® KEYS	12
TOSIBOX® Key	12
TOSIBOX® Mobile Key	12
TOSIBOX® SoftKey	12
TOSIBOX® HUB	13
TOSIBOX® Virtual Central Lock	13


KEY

HUB

TOSIBOX SOLUTION GROWS FROM SECURE REMOTE ACCESS TO GLOBAL OT NETWORKING


Tosibox has automated secure connectivity and made it simple. It is a standardized way of building VPN connections based on a patented connection method. The configuration-free Plug & Go™ implementation easy to carry out even without special IT skills. The unique feature of TOSIBOX® technology is the two-way connectivity that brings the benefits of IP networking plus remote maintenance with one technology.

The game-changing solution consists of globally patented point-to-point data flow between ends allowing for a secure connection and associated marriage between two modules. The communication is end-to-end encrypted and not decrypted at any point along the way. A third-party cloud service is not included, but you can choose your own cloud or server, wherever you want.



TOSIBOX® solution consists of modular components that offer unlimited expandability and flexibility. All components are compatible with each other as well as internet connection, operator, and device agnostic. The solution works both in internal and external networks, and you can connect both modern IoT devices and legacy systems.

- TOSIBOX® Node is an industry router or a software sharing access to devices.
- TOSIBOX® Key is a client used to access the network.
- TOSIBOX® Hub is the platform for OT network and access rights management.
- TOSIBOX® Platform is a hosted management layer that turns operational applications, machines and their users into a controlled OT network.



Tosibox Platform is an automated and open cybersecurity platform for your operational technology networks and infrastructure. It scales from one user and one device to an enterprise-level OT network solution with hundreds or even thousands of users, devices, and sites connected. Tosibox Platform fits all industries and organizations, regardless of the size or vertical, and is designed to meet your needs today and well into the future.

CERTIFIED CYBER SECURITY

Tosibox is ISO27001 certified, underlining the importance we place on protecting customers' data. Platform security is based on automated firewall settings and point-to-point VPN technology with 256 Bit AES data encryption. Tosibox Platform supports Layer 2 and layer 3 routing functions and protocols.

Tosibox Platform is data agnostic and secure. We can transfer any data to any environment without opening your environment to cyber security risks. The Platform automatically routes data traffic between your operational applications, machines, and users. You own the data – we enable the flow.

NODE

TOSIBOX® Lock 150



Compliance with
IMDA Standards
DB107332



TOSIBOX® Lock 150 is an industrial router with firewall and secure Plug & Go™ connectivity. It serves as an endpoint for secure remote connections.

IoT devices connected to the Lock can be securely accessed over the Internet and most LAN and WAN networks through an encrypted VPN connection. TOSIBOX® Lock 150 is compatible with all existing TOSIBOX® products.

Technical data

Product codes
TBL15

Ports

- 1 x USB 2.0, type A
- 1 x RJ-45 WAN connection, 10/100 Mb/s, auto-negotiation (MDI / MDI-X)
- 3 x RJ-45 LAN connection, 10/100 Mb/s, auto-negotiation (MDI / MDI-X)
- x RJ-45 Service connection, 10/100 Mb/s, auto-negotiation (MDI / MDI-X)

Connections

- 10-30V DC $\pm 10\%$ (reverse polarity protected)
- 2 x Wireless network antenna connector, RP-SMA Female
- DIN rail attachment (bottom), angle bracket available as an accessory (TBMBD1)

WAN connection features

- Independent of operating systems
- Works in all Internet connections (operator independent)
- Supports HTTP proxy servers with and without authentication
- Firewall friendly
- Works with dynamic, static and private IP addresses
- Built-in firewall, NAT
- Up to 10 concurrent VPN connections
- VPN throughput 10 Mb/s

Mobile connection features

- Supported 4G USB modems: TOSIBOX® 4G modem

- TosiOnline™ Automatic network recovery that recovers from most mobile operator and modem problems

WLAN

- IEEE 802.11 b/g/n, max. 150 Mbps
- WEP, WPA-PSK, WPA2-PSK, WPA-PSK/WPA2-PSK Mixed encryption
- Frequency 2.412 – 2.462 GHz, 11 channels
- Output power 20 dBm max

Included accessories

- RJ-45 Cat6 Ethernet cable, USB extension cable
- 2 x WLAN antennas, 2 dBi
- AC Adapter: Input 100 – 240V AC, frequency 47 – 63 Hz, Output 24.0 V, 0.8 A, max 7.2 W. EU, UK, AU or US Power Socket
- DC input plug
- DIN rail mounting bracket

Physical properties

- 132 mm x 99 mm x 35.5 mm / 5.2" x 3.9" x 1.4" (L x W x H)
- Weight 593 g / 1.31 lbs (net weight article)
- Cast aluminium casing
- Operating temperature -20 °C ... +55 °C / -4 °F ... 131 °F
- Operating humidity: 20 – 80% RH, non-condensing
- Storage temperature -40 °C ... +70 °C / -40 °F ... 158 °F
- Protection class IP20

N O D E

TOSIBOX® 175



TOSIBOX® 175 is a cost-effective Plug & Go™ connectivity device and is ideal for demanding industry sectors that require an all-in-one solution that is compact, able to handle all environments and suited to global market usage. The 4G module and external 4G antenna provides stable Internet access, so the node can be easily configured anywhere. The versatile connectivity options, utilized in conjunction with leading edge Cyber security technology from TOSIBOX® enable diverse application scenarios.

The durable aluminium alloy shell and small form factor allows for ideal mounting conditions. Creating secure and sustainable infrastructure has never been this easy, is an industrial router with firewall and secure Plug & Go™ connectivity. It serves as an endpoint for secure remote connections. TOSIBOX® 175 is compatible with all existing TOSIBOX® products.

Technical data

Product codes
TBL175

Ports

- 1 x RJ-45 WAN connection, 10/100 Mb/s, auto-negotiation (MDI / MDI-X)
- 1 x RJ-45 LAN connection, 10/100 Mb/s, auto-negotiation (MDI / MDI-X)
- LAN can be assigned as Service connection, 10/100 Mb/s, auto-negotiation (MDI / MDI-X)
- RS485 port is not supported in the software. The device can be powered through the port

Connections

- 9-35V DC
- 1 x WiFi antenna connector, RP-SMA Male
- 1 x LTE antenna connector, SMA Female
- DIN rail attachment (back)
- Maximum power consumption 10W

Connection features

- 3-way WAN priority
- Proxy server support
- WAN access with static addressing or DHCP
- Network Time Protocol (NTP) server
- Automatic LAN network discovery
- LAN access with mixed static addressing and DHCP server
- Static routes
- Works in all Internet connections (operator independent)
- Firewall friendly

- Works with dynamic, static and private IP addresses
- Built-in firewall, NAT
- Up to 10 concurrent VPN connections
- VPN throughput up to 10 Mbit/s
- TosiOnline™ Automatic network recovery that recovers from most mobile operator and modem problems
- Built-in firewall, NAT

4G Module

- Region: GLOBAL
- LTE Cat-4
- Up to 150 Mbps DL, 50 Mbps UL

Frequency Bands

- LTE FDD: B1/B2/B3/B4/B5/B7/B8/B12/B13/B18/B19/B20/B25/B26/B28
- LTE TDD: B38/B39/B40/B41
- WCDMA: B1/B2/B4/B5/B6/B8/B19

WLAN

- IEEE 802.11 b/g, 2.4 GHz, max. 150 Mbps
- Encryptions WEP, WPA-PSK, WPA2-PSK, WPA-PSK/WPA2-PSK mixed mode
- Frequency 2.412 – 2.462 GHz, 11 channels
- Access point or client mode
- Output power 20 dBm max

Included accessories

- RJ-45 Cat5e Ethernet cable
- 1 x LTE antenna
- 1 x WiFi antenna
- DIN rail mount
- Power supply unit
- AC adapter - Input 100 – 240 V AC, frequency 50/60Hz 0,3A, Output 12.0 V, 1.0 A, max 12.0 W. EU, UK, AU and US power socket

Physical properties

- 104 mm x 28 mm x 110 mm / 4.09" x 1.10" x 4.33" (L x W x H)
- Storage temperature -30 °C ... +70 °C / -22 °F ... +158 °F
- Protection class IP30
- Weight 305 g / 0.67 lbs (net weight article)
- Operating temperature -20 °C ... +55 °C / -4 °F ... +131 °F



TOSIBOX® Lock 500



Compliance with
IMDA Standards
DB107332

PTCRB AT&T VERIZON T-MOBILE

Verizon and T-Mobile pending for Lock 500iD

TOSIBOX® Lock 500 is a high-end connectivity device bringing unprecedented possibilities for customers to manage their operations and to build new IoT solutions. The Lock 500 is ideal for demanding industrial environments and opens up new opportunities in security and office networking sectors. The Lock 500 is compatible with all existing TOSIBOX® products.

Technical data

Product codes

TBL5, TBL5PS, TBL5iA, TBL5iAPS, TBL5iB, TBL5iBPS, TBL5iC, TBL5iCPS, TBL5iD, TBL5iDPS

Ports

- 1 x USB 2.0, type A
- 1 x RJ-45 WAN connection, 10/100 Mb/s, auto-negotiation (MDI / MDI-X)
- 3 x RJ-45 LAN connection, 10/100 Mb/s, auto-negotiation (MDI / MDI-X)
- LAN3 can be assigned as Service connection, 10/100 Mb/s, auto-negotiation (MDI / MDI-X)
- Ethernet port isolation: 1500 Vrms 1 minute (when device frame connected to system ground potential)

Connections

- 12-48V DC (+/-20%), reverse polarity protected
- Device frame connector
- 2 x WiFi antenna connector, RP-SMA Female
- (TBL5i*) 2 x LTE antenna connectors, SMA Female
- 2 x Digital Input, 2 x Digital Output, 24V DC out
- DIN rail attachment (back)
- Maximum power consumption 10W

WAN connection features

- Independent of operating systems
- Works in all Internet connections (operator independent)
- Supports HTTP proxy servers with and without authentication
- Firewall friendly
- Works with dynamic, static and private IP addresses
- Built-in firewall, NAT
- Up to 50 concurrent VPN connections
- VPN throughput up to 70 Mbit/s

Mobile connection features

- Supported External USB modem: TOSIBOX® 4G modem (TB4GM2EU, TB4GM2AU).
- TosiOnline™ Automatic network recovery that recovers from most mobile operator and modem problems

TBL5iA*

- Region: EMEA
- LTE Cat-6
- Up to 300 Mbps DL, 50 Mbps UL
- Frequency Bands (4G LTE): B1, B2, B3, B4, B5, B7, B12, B13, B20, B25, B26, B29, B41
- Dual SIM

TBL5iB*

- Region: APAC
- LTE Cat-6
- Up to 300 Mbps DL, 50 Mbps UL
- Frequency Bands (4G LTE): B1, B3, B5, B7, B8, B18, B19, B21, B28, B38, B39, B40, B41
- Dual SIM

TBL5iC*

- Region: US/CAN
- LTE Cat-6
- Up to 300 Mbps DL, 50 Mbps UL
- Frequency Bands (4G LTE): B1, B2, B3, B4, B5, B7, B12, B13, B20, B25, B26, B29, B41
- Dual SIM

TBL5iD*

- Region: US/CAN
- CBRS
- LTE Cat12 / carrier aggregation
- Up to 600 Mbps DL, 100 Mbps UL
- Frequency Bands (4G LTE): B1, B2, B3, B4, B7, B8, B9, B12, B13, B14, B18, B19, B20, B5, B42, B43, B26, B29, B41, B30, B66, B32, B46, B48
- Dual SIM

WLAN

- IEEE 802.11 b/g/n, max. 150 Mbps
- WEP, WPA-PSK, WPA2-PSK, WPA-PSK/WPA2-PSK Mixed, WPA-EAP, WPA2-EAP TKIP/AES encryption
- Frequency 2.412 – 2.462 GHz, 11 channels
- Output power 20 dBm max



Included accessories

- RJ-45 Cat5e Ethernet cable
- 2 x WiFi antennas, 2 dBi
- I/O connector plug
- Power connector plug
- TBL5*PS: AC adapter - Input 100 – 240 V AC, frequency 47 – 63 Hz, Output 12.0 V, 1.6 A, max 19.2 W. EU, UK, AU and US power socket
- TBL5*PS: DC feed cable
- TBL5iA*: EMEA Modem
- TBL5iB*: APAC Modem
- TBL5iC*: US/CAN modem
- TBL5i*: 2 x LTE antennas

I/O specifications

- 2 x digital inputs, galvanic isolation, current limited to <5mA, Voltage 0 - 32V nom. >12V is interpreted as '1', 0-5V is '0'
- 2 x digital outputs, 24V DC, 50 mA current shared by the outputs and 24V DC out
- 1 x 24V DC out, 50 mA current shared by 24V DC out, output 1 and output 2
- Software Configurable I/O state

Physical properties

- 110 mm x 58 mm x 127 mm / 4.33" x 2.28" x 5.0" (L x W x H)
- Storage temperature -40 °C ... +70 °C / -40 °F ... +158 °F
- Protection class IP20

TBL5*

- Weight 495 g / 1.09 lbs (net weight article)
- Operating temperature -20 °C ... +60 °C / -4 °F ... +140 °F

TBL5i*

- Weight 505 g / 1.11 lbs (net weight article)
- Operating temperature -20 °C ... +60 °C / -4 °F ... +140 °F

TOSIBOX® 610



Reliable and powerful Plug & Go™ connectivity device



TOSIBOX® 610 is a perfect choice for professional applications when wireless networking is not required. Leading edge cybersecurity technology from TOSIBOX enable diverse application scenarios. The durable aluminium alloy shell and small form factor is ideal for rugged mounting conditions.

Tosibox 600 series contains devices for all connectivity scenarios and meets the most demanding operating conditions. Bringing connectivity to those hard to reach locations has never been this easy. TOSIBOX® 610 is compatible with all existing TOSIBOX® products.

Technical data

Product codes

TBL610EU, TBL610UK, TBL610AU, TBL610US

Ports

- 1 x RJ-45 WAN connection, 10/100/1000 Mb/s, auto-negotiation (MDI / MDI-X)
- 3 x RJ-45 LAN connection, 10/100/1000 Mb/s, auto-negotiation (MDI / MDI-X)
- 1 x USB 2.0, type A

Connections

- 4 pin industrial DC power socket
- 9-50V DC, reverse polarity protection, voltage surge/transient protection
- DIN rail mounting slot in the back
- Maximum power consumption 6W

Connection features

- Proxy server support
- WAN access with static addressing or DHCP
- Network Time Protocol (NTP) server
- Automatic LAN network discovery
- LAN access with mixed static addressing and DHCP server
- Static routes
- Works in all Internet connections (operator independent)
- Firewall friendly

- Works with dynamic, static and private IP addresses
- Built-in firewall, NAT
- Up to 50 concurrent VPN connections
- VPN throughput up to 70 Mbit/s
- TosiOnline™ Automatic network recovery that recovers from most mobile operator and modem problems

I/O specifications

- 1 x Digital input, 0 - 6 V detected as logic low, 8 - 30 V detected as logic high
- 1 x Digital output, open collector output, max output 30 V, 300 mA
- Software configurable I/O state
- Requires separate I/O cable (TB600PAC1 or TB600PAC2)

Included accessories

- Ethernet cable (1.5 m)
- DIN rail mount
- Power supply unit
- AC adapter - Input 100 – 240 V AC, frequency 50/60Hz 0,6A, Output 12.0 V, 1.5 A, max 18 W
- Power plug with contact terminals

Physical properties

- 115 mm x 32.2 mm x 95.2 mm / 4.52" x 1.26" x 3.74" (W x H x L)
- Protection class IP30
- Weight 345 g / 0.76 lbs (net weight article)
- Storage temperature -40 °C ... +75 °C / -40 °F ... +167 °F
- Operating temperature -40 °C ... +75 °C / -40 °F ... +167 °F

N O D E

TOSIBOX® 650



All-around Plug & Go™ connectivity device

TOSIBOX® 650 is ideal performer in enterprise solutions. The versatile connectivity options, utilized in conjunction with leading edge Cyber security technology from TOSIBOX enable diverse application scenarios. The durable aluminium alloy shell and small form factor is ideal for rugged mounting conditions.

Extended IP30 Rating and operating temperature provides installation and use in demanding environmental conditions.

Tosibox 600 series contains devices for all connectivity scenarios and meets the most demanding operating conditions. Bringing connectivity to those hard to reach locations has never been this easy. TOSIBOX® 650 is compatible with all existing TOSIBOX® products.

Technical data

Product codes

TBL650EU, TBL650UK, TBL650AU, TBL650US

Ports

- 1 x RJ-45 WAN connection, 10/100/1000 Mb/s, auto-negotiation (MDI / MDI-X)
- 3 x RJ-45 LAN connection, 10/100/1000 Mb/s, auto-negotiation (MDI / MDI-X)
- 1 x USB 2.0, type A

Connections

- 4 pin industrial DC power socket
- 9-50V DC, reverse polarity protection, voltage surge/transient protection
- 2 x RP-SMA for WiFi
- DIN rail mounting slot in the back
- Maximum power consumption 9W

Connection features

- 2-way WAN priority
- Proxy server support
- WAN access with static addressing or DHCP
- Network Time Protocol (NTP) server
- Automatic LAN network discovery
- LAN access with mixed static addressing and DHCP server
- Static routes

- Works in all Internet connections (operator independent)
- Firewall friendly
- Works with dynamic, static and private IP addresses
- Built-in firewall, NAT
- Up to 50 concurrent VPN connections
- VPN throughput up to 70 Mbit/s
- TosiOnline™ Automatic network recovery that recovers from most mobile operator and modem problems

WLAN

- IEEE 802.11 b/g/n, 2.4 GHz, max. 150 Mbps
- Encryptions WEP, WPA-PSK, WPA2-PSK, WPA-PSK/WPA2-PSK mixed mode
- Frequency 2.412 – 2.462 GHz, 11 channels
- Access point or client mode
- Output power 20 dBm max

I/O specifications

- 1 x Digital input, 0 - 6 V detected as logic low,
- 8 - 30 V detected as logic high
- 1 x Digital output, open collector output, max output 30 V, 300 mA
- Software configurable I/O state
- Requires separate I/O cable (TB600PAC1 or TB600PAC2)

Included accessories

- Power supply unit
 - AC adapter - Input 100 – 240 V AC, frequency 50/60Hz 0,6A, Output 12.0 V, 1.5 A, max 18 W
- 2 x WiFi antennas (swivel, RP-SMA male)
- *1 x Bluetooth antenna (*Not supported)
- Power plug with contact terminals* (*Shipments starting from 2022-04-19)
- Ethernet cable (1.5 m)
- DIN rail mount

Physical properties

- 115 x 32.2 x 95.2 mm / 4.52" x 1.26" x 3.74" (W x H x L)
- Protection class IP30
- Weight 355 g / 0.78 lbs (net weight article)
- Storage temperature -40 °C ... +75 °C / -40 °F ... +167 °F
- Operating temperature -40 °C ... +75 °C / -40 °F ... +167 °F

N O D E

TOSIBOX® 670



LTE enabled Plug & Go™ connectivity device



TOSIBOX® 670 is ideal as a main or backup internet source, where steady connection and high data throughput is necessary. The versatile connectivity options, utilized in conjunction with leading edge Cyber security technology from TOSIBOX enable diverse application scenarios. The durable aluminium alloy shell and small form factor is ideal for rugged mounting conditions.

Tosibox 600 series contains devices for all connectivity scenarios and meets the most demanding operating conditions. Bringing connectivity to those hard to reach locations has never been this easy. TOSIBOX® 670 is compatible with all existing TOSIBOX® products.

Technical data

Product codes

TBL670EU, TBL670UK, TBL670AU, TBL670US

Ports

- 1 x RJ-45 WAN connection, 10/100/1000 Mb/s, auto-negotiation (MDI / MDI-X)
- 3 x RJ-45 LAN connection, 10/100/1000 Mb/s, auto-negotiation (MDI / MDI-X)
- 1 x USB 2.0, type A

Connections

- 4 pin industrial DC power socket
- 9-50V DC, reverse polarity protection, voltage surge/transient protection
- 2 x SMA for LTE
- 1 x GNSS
- DIN rail mounting slot in the back and on both sides
- Maximum power consumption 9W

Connection features

- 3-way WAN priority
- Proxy server support
- WAN access with static addressing or DHCP
- Network Time Protocol (NTP) server
- Automatic LAN network discovery
- LAN access with mixed static addressing and DHCP server
- Static routes
- GNSS coordinates display on UI via GPS, GLONASS, BeiDou, Galileo and QZSS
- Works in all Internet connections (operator independent)
- Firewall friendly
- Works with dynamic, static and private IP addresses

- Built-in firewall, NAT
- Up to 50 concurrent VPN connections
- VPN throughput up to 70 Mbit/s
- TosiOnline™ Automatic network recovery that recovers from most mobile operator and modem problems

4G Module

- TBL670US
- Region: North America and Mexico
- LTE Cat-6
- Up to 300 Mbps DL, 42 Mbps UL

Frequency Bands*

For more detailed - please check data sheet.

I/O specifications

- 1 x Digital input, 0 - 6 V detected as logic low, 8 - 30 V detected as logic high
- 1 x Digital output, open collector output, max output 30 V, 300 mA
- Software configurable I/O state
- Requires separate I/O cable (TB600PAC1 or TB600PAC2)

Included accessories

- Power supply unit
- AC adapter - Input 100 - 240 V AC, frequency 50/60Hz 0,6A, Output 12.0 V, 1.5 A, max 18 W
- 2 x LTE antennas (swivel, SMA male)
- 1 x GNSS antenna (adhesive, SMA male, 3 m cable)
- Power plug with contact terminals
- SIM Adapter kit
- Ethernet cable (1.5 m)
- DIN rail mount

Physical properties

- 115 mm x 44.2 mm x 95.1 mm / 4.52" x 1.74" x 3.74" (W x H x L)
- Protection class IP30
- Weight 455 g / 1.00 lbs (net weight article)
- Storage temperature -40 °C ... +75 °C / -40 °F ... +167 °F
- Operating temperature -40 °C ... +75 °C / -40 °F ... +167 °F

N O D E

TOSIBOX® 675



High performance Plug & Go™ connectivity device

TOSIBOX® 675 is a powerful device for high demanding application in demanding industrial environments. With a wide range of connectivity interfaces the demand for always on connectivity is guaranteed. This device can be used in power-hungry industrial applications where speed and robustness are at the heart of the solution.

The versatile connectivity options, utilized in conjunction with leading edge Cyber security technology from TOSIBOX enable diverse application scenarios. The durable aluminium alloy shell and small form factor is ideal for rugged mounting conditions. Extended IP30 Rating and operating temperature provides installation and use in demanding environmental conditions.

Tosibox 600 series contains devices for all connectivity scenarios and meets the most demanding operating conditions. Bringing connectivity to those hard to reach locations has never been this easy. TOSIBOX® 675 is compatible with all existing TOSIBOX® products.

Technical data

Product codes

TBL675US, TBL675EU, TBL675UK, TBL675AU

Ports

- 1 x RJ-45 WAN connection, 10/100/1000 Mb/s, auto-negotiation (MDI / MDI-X)
- 3 x RJ-45 LAN connection, 10/100/1000 Mb/s, auto-negotiation (MDI / MDI-X)
- 1 x USB 2.0, type A

Connections

- 4 pin industrial DC power socket
- 9-50V DC, reverse polarity protection, voltage surge/transient protection
- 2 x RP-SMA for WiFi
- 2 x SMA for LTE
- 1 x GNSS
- DIN rail mounting slot in the back and on both sides
- Maximum power consumption 16W

Connection features

- 4-way WAN priority
- Proxy server support
- WAN access with static addressing or DHCP
- Network Time Protocol (NTP) server
- Automatic LAN network discovery



- LAN access with mixed static addressing and DHCP server
- Static routes
- GNSS coordinates display on UI via GPS, GLONASS, BeiDou, Galileo and QZSS
- Works in all Internet connections (operator independent)
- Firewall friendly
- Works with dynamic, static and private IP addresses
- Built-in firewall, NAT
- Up to 50 concurrent VPN connections
- VPN throughput up to 70 Mbit/s
- TosiOnline™ Automatic network recovery that recovers from most mobile operator and modem problems

I/O specifications

- 1 x Digital input, 0 - 6 V detected as logic low, 8 - 30 V detected as logic high
- 1 x Digital output, open collector output, max output 30 V, 300 mA
- Software configurable I/O state
- Requires separate I/O cable (TB600PAC1 or TB600PAC2)

Included accessories

- Power supply unit
- AC adapter - Input 100 – 240 V AC, frequency 50/60Hz 0,6A, Output 12.0 V, 1.5 A, max 18 W
- 2 x LTE antennas (swivel, SMA male)
- 2 x WiFi antennas (swivel, RP-SMA male)
- 1 x GNSS antenna (adhesive, SMA male, 3 m cable)
- *1 x Bluetooth antenna (*Not supported)
- Power plug with contact terminals
- DIN rail mount
- Ethernet cable (1.5 m)
- SIM Adapter kit

Physical properties

- 115 mm x 44.2 mm x 95.1 mm / 4.52" x 1.74" x 3.74" (W x H x L)
- Protection class IP30
- Weight 456 g / 1.00 lbs (net weight article)
- Storage temperature -40 °C ... +75 °C / -40 °F ... +167 °F

TOSIBOX® Key

TOSIBOX® Key is an intelligent cryptoprocessing device that enables a secure connection between your computer and one or more TOSIBOX® Locks/ Nodes, giving you a full visibility and control over the network devices connected to the Node.


Connections are established through a secure, encrypted VPN tunnel over the Internet or other common WANs and LANs, and permissions can be easily granted, revoked and configured in an unlimited number of ways. TOSIBOX® Key comes with a durable light metal alloy casing.

Starting from the ID "EF" TOSIBOX® Key conforms to the FIPS 140-2 level 3 regulations. The ID is the first two letters of the serial number found on the nameplate.



Physical properties

- 83 mm x 22 mm x 10 mm / 3.27" x 0.87" x 0.39" (L x W x H)
- Weight 27 g / 0.06 lbs
- Casing aluminium and plastic
- Operating temperature 0 °C ... +70 °C / +32 °F ... +158 °F
- Storage temperature -20 °C ... +80 °C / -4 °F ... +176 °F



TOSIBOX® Mobile Client

TOSIBOX® Mobile Client gives you secure and easy remote access on the go by enabling secure VPN connections to matched TOSIBOX® Node devices, using the mobile device's Wi-Fi or mobile data connection.

TOSIBOX® Mobile Client is built on the physical security foundation of TOSIBOX® products: the access rights are granted and controlled from the physical TOSIBOX® Key, after which the Mobile Client remains bound to it. The access rights are device-specific and non-transferrable.



TOSIBOX® SoftKey

TOSIBOX® SoftKey is a computer software that enables a secure connection between your computer and one or more TOSIBOX® Nodes, giving you full visibility and control over the network devices connected to the Node.

The SoftKey works without a physical TOSIBOX® Key device. The SoftKey corresponds a Sub Key that is controlled via a physical Master Key, and therefore it cannot be used to create more keys or Mobile Clients. The access rights are granted and controlled from the physical TOSIBOX® Key, after which the SoftKey remains bound to it. The access rights are device-specific and non-transferrable.



TOSIBOX® SoftKey

TOSIBOX® HUB is the platform for OT network and access management. You can limit access, add new users and objects simply by drag and drop.

TOSIBOX® Virtual Central Lock

TOSIBOX® Virtual Central Lock cuts access management work time from days into minutes, enabling easy management of big networks without special IT skills.

TOSIBOX® Virtual Central Lock turns your TOSIBOX ecosystem into a controlled OT network of always-on VPN connections for remote maintenance, continuous monitoring, real-time data collection and data logging.

Because it's virtual, it can be deployed in your office network, in leading cloud services AWS or Azure, or anywhere else where you prefer.

Functions	TOSIBOX® Virtual Central Lock
TOSIBOX® Plug & Go™ Technology	Yes
Mounting options	N/A
Power input	N/A
3G / 4G USB modem support	N/A
WAN port	One required, dependent on virtual platform
LAN ports	One required, dependent on virtual platform
VPN throughput	Dependent on virtual platform
VPN encryption	Blowfish 128 bit CBC, AES 128/192/256 bit CBC
VPN connection authentication	PKI, 3072 bit RSA
Concurrent VPN connections	Dependent on virtual platform and license
Supported platforms	VMWare ESXi, Microsoft, Hyper-V, Linux KVM
WLAN	N/A
Operating temperature	N/A
Measurements (LxWxH)	N/A
Power consumption	N/A
Approvals	N/A
Product codes	TBVCL1 TBVCL1LP100 Licence Package required



TOSIBOX

sales@tosibox.com
support@tosibox.com

www.tosibox.com

Copyright © 2022 Tosibox. All rights reserved. Tosibox reserves the right to change and improve any product mentioned herein without prior notice.

v 1.1

