

# Wiha SoftFinish®.

Tangible advantages.



product  
design  
award


1997



Fraunhofer Institut  
Arbeitswirtschaft und  
Organisation



Wiha SoftFinish®.



#### Quick-turning zone

- Safe, fast turning between the thumb and index finger
- Perfect guidance thanks to tapered handle end
- Long, slim handles
- Circular cross-section



#### Power turning zone

- Comfortable maximum power transmission
- All fingers can be placed on the handle
- No painful edges
- Large, octagonal cross-section

**Long lifespan:**  
Through hardened blade of chrome-vanadium-molybdenum steel

**Perfect fit in the screw head:**  
Precisely manufactured tip

**Durable corrosion protection:**  
Chromed surface

**Fast tip identification:**  
Cap imprint for tip and size

**No complaints even after intensive use, no pressure marks, calluses, or blisters:**  
Burr-free and offset-free




**Optimal material distribution:**  
The position of the soft and hard zones also supports the perfect grip for quick and powerful turning

**Optimal for scanning:**  
EAN code on each article

**Work safety:**  
Dual roll-off protection

# Wiha SoftFinish® range

Made in Germany.

Caps	SoftFinish	Blades	Drive
 		   	
 		   	
 		   	
 		   	

① round, ② round, insulated, ③ slimTECHNOLOGIE, ④ Hex, wrench



## Applications

	Standard
	Stubby
	Reversible blade system
	Torque
	Magazine bit holder
	Magazine bit holder Stubby
	Magazine bit holder LiftUp

# Wiha SoftFinish®.

The convenient expert for dry applications.



product  
design  
award

1997



*The right tool at a glance, thanks to the printed screw symbol on the handle end.*

The Wiha SoftFinish® zone features a solid moulded core with soft outer grip. This requires less force, yet achieves 40% more torque than conventional handles. The handle is shaped to fit comfortably in the hand, providing maximum through forces in dry working conditions.

If a stuck screw has to be loosened, a precise hammer blow can be applied to the solid steel cap. Due to the hex blade extending through the handle to the steel cap, there is no loss of impact energy.



*The solid steel cap at the end of the SoftFinish® handle enables controlled hammer blows, for example, when loosening a tight screw.*



*Due to the solid steel cap and hex blade extending through the handle, there is no loss of impact energy when a precise hammer blow is applied.*

*Blade with hex bolster for wrenches to use on particularly tight screws.*



## Wiha SoftFinish®.

- Multi-component SoftFinish® handle provides maximum user comfort
- Ergonomically perfect handle design
- Printed screw symbol on handle end for fast identification
- Available in versions with round blade, hex blade or hex blade with solid steel cap
- Blade made of high quality CVM-steel, through-hardened and chrome plated
- Wiha ChromTop®-finish on tip for a perfect fit every time

# Wiha SoftFinish®.

The convenient expert for dry applications.

## Stubby-screwdriver.



### 302 SoftFinish® slotted screwdriver. Short round blade.

**Blade:** High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.  
Wiha ChromTop® finish on tip for a perfect fit every time.

**Handle:** Ergonomic Wiha Stubby SoftFinish® handle, multi-component with roll-off protection.

**Standards:** DIN 5265, ISO 2380, handle based on DIN 5268 - style K.

**Application:** For working in confined spaces.

Order-No.	⌀	↔	⊖	●	↔	↔	↔
26964	4.0	25	0.8	4.0	81	34	10
26965	5.5	25	1.0	5.5	81	34	10
26966	6.5	25	1.2	6.5	81	34	10
26967	8.0	25	1.2	8.0	81	34	10



### 311 SoftFinish® Phillips screwdriver. Short round blade.

**Blade:** High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.  
Wiha ChromTop® finish on tip for a perfect fit every time.

**Handle:** Ergonomic Wiha Stubby SoftFinish® handle, multi-component with roll-off protection.

**Standards:** DIN ISO 8764, handle based on DIN 5268 - style K.

**Application:** For working in confined spaces.

Order-No.	⊕	↔	●	↔	↔	↔
26968	PH1	25	4.5	81	34	10
26969	PH2	25	6.0	81	34	10
26970	PH3	25	8.0	81	34	10



### 313 SoftFinish® Pozidriv screwdriver. Short round blade.

**Blade:** High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.  
Wiha ChromTop® finish on tip for a perfect fit every time.

**Handle:** Ergonomic Wiha Stubby SoftFinish® handle, multi-component with roll-off protection.

**Standards:** DIN ISO 8764, handle based on DIN 5268 - style K.

**Application:** For working in confined spaces.

Order-No.	⊕	↔	●	↔	↔	↔
26971	PZ1	25	4.5	81	34	10
26972	PZ2	25	6.0	81	34	10
26973	PZ3	25	8.0	81	34	10

## For TORX® screws.



### 362 SoftFinish® TORX® screwdriver. Round blade.

**Blade:** High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.  
Wiha ChromTop® finish on tip for a perfect fit every time.

**Handle:** Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

**Application:** Particularly suitable for dry applications.

Order-No.	⊗	↔	●	↔	↔	↔
26259	T3	60	2.5	164	23	10
26260	T4	60	2.5	164	23	10
01285	T5	60	2.5	164	23	10
01286	T6	60	3.5	164	23	10
01287	T7	60	3.5	164	23	10
01288	T8	60	3.5	164	23	10
01289	T9	60	4.0	171	30	10
01290	T10	80	4.0	191	30	10
01291	T15	80	4.0	191	30	10
01292	T20	100	4.0	218	36	10
01293	T25	100	4.5	218	36	10
01294	T27	115	5.5	233	36	10
01295	T30	115	6.0	233	36	10
01296	T40	130	7.0	254	41	10
01297	T45	130	8.0	254	41	5



### 362BE SoftFinish® TORX® ball end screwdriver. Hex blade.

**Blade:** High-quality chrome-molybdenum steel, through-hardened, chrome-plated.  
Wiha ChromTop® finish on tip for a perfect fit every time.

**Handle:** Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

**Application:** For all hard-to-reach TORX® screws.

**Extra:** The TORX® ball end enables fastening and unfastening at an angle of up to 25°.  
With elongated TORX® profile behind ball end.

Order-No.	⊗	↔	●	⊖	↔	↔	↔
32250	T9	60	7/64	2.8	164	23	10
32251	T10	60	1/8	3.2	184	23	10
32252	T15	80	9/64	3.6	191	30	10
32253	T20	80	5/32	4.0	211	30	10
32254	T25	100	3/16	4.8	218	36	10
32255	T27	115	7/32	5.6	233	36	10
32256	T30	115	1/4	6.4	233	36	10