

Bradrad HSS – Stufenbohrer

Universeller Einsatz in alle Materialien 3 schneidige Ausführung



Bezeichnung	Ø gestuft	L1	L	d
PG 21	12.5/15.2/18.6/20.4/ 22.5/25.8/28.3/30.5	32	55	12
PG 29	12.5/15.2/18.6/20.4/22.5/ 25.8/28.3/30.5/33.6/37.0	36	73	9
BS M1	5.5/8.5/11.5/14.5/17.5/20.5/ 23.5/26.5/29.5/32.5/35.5	40	62	10
BS M2	6/9/12/15/18/21/24/27/ 30/33/36	40	67	10
BS M3	6.5/9.5/12.5/15.5/18.5/21.5/ 24.5/27.5/30.5/33.5/36.5	40	67	10
BS M4	7/10/13/16/19/22/25/28/31/ 34/37	40	67	10
BS M5	7.5/10.5/13.5/16.5/19.5/22.5/ 25.5/28.5/31.5/34.5/37.5	40	67	10
BS M6	8/11/14/17/20/23/26/29/32/ 35/38	40	67	10

Multicut HSS – Stufenbohrer

Universeller Einsatz in alle Werkstoffe 2 schneidige Ausführung



Bezeichnung	Ø gestuft	L1	L	d
MC 1M	4-12	35	56	6
MC 2M	10-20	37	58	10
MC 3M	20-30	41	63	12
MC 4M	4-12	40	61	6
MC 5M	6-24	45	66	9
MC 6M	6-18	27	49	9
MC 7M	4-20	29	50	10
MC 8M	14-24	20	42	12
MC 9M	20-34	32	54	12
MC 10M	4-30	54	75	12
Set MCS 1	MC 1M - MC 2M - MC 3M in Metallbox			

Hexibit HSS – Stufenbohrer für die Metallbearbeitung

Universeller Einsatz in Metallische Werkstoffe 2 Lippig



Bezeichnung	Ø gestuft	L1	L	d
XS 412	4-12	14	36	1/4"
XS 513	5-13	14	36	1/4"
XS 820	8-20	28	50	1/4"
XS 921	9-21	28	50	1/4"
XSTS 1 - Set	XS 412, XS 513, XS 820 + Schälbohrer XT 314 im Kunststoffkoffer			