



Original Consumables Catalogue

ALIVE WITH COLOUR



OKI Original Consumables

5 Reasons why OKI Original Consumables gives you the best value for money.




Big on colour, small on mono costs

With OKI's LED colour range for the office, it will never cost you more to print mono pages on an OKI colour device than on a standard mono printer. So you can keep printing your black and white documents and colour is available when you want to stand out. We believe that every business deserves great graphics, reliable printing and flexible media capability.

Always the best quality

Using OKI's Original Consumables with OKI's hardware guarantees quality for every print. Third party products aren't designed specifically for OKI's devices, so they can't guarantee the stunning print quality, low cost and reliability you enjoy with OKI's Original Consumables.



Warranty

To give you complete peace of mind, OKI's hardware comes with a three-year warranty as standard on registration of your device within 30 days of purchase, and providing you continue to use OKI Original Consumables.

Helpful advice when you need it

If you're ever unsure about OKI's products, our dedicated Customer Service Desk and friendly, professional staff are always on hand to help you with any queries you may have. However, we can only provide support for OKI Original Consumables.



Guaranteed toner yields

OKI uses ISO-approved testing methods to accurately determine the declared yield for our original toner cartridges. That means you always get the number of pages promised from your OKI Original Consumables.

Protect your business

OKI Original Consumables are specifically designed and crafted to fit your device perfectly. This precision matching is why only OKI Original Consumables offer guaranteed reliability and print quality.



Keypoint Intelligence Buyers Lab, an industry-leading independent research analyst and testing firm, compared the performance, image quality, reliability and yields of genuine OKI Original Consumables versus three third-party compatible cartridges.*

BLI tested OKI Original Consumables and third-party products used in OKI devices and found the following benefits of OKI Original Consumables:



Better print yields



Higher quality print



Consistent colour and quality



No delivery spillage



No damage to devices

*Visit your local OKI website for further information on BLI Testing.

How to check if your consumables are OKI Original



1) Look for the hologram

You can always tell if a product is an OKI Original Consumable by looking for the hologram on the packaging and making sure you can see numbers 18 and 81 in the holographic 'window'.

2) Check the serial number

Every OKI Original Consumable has a unique serial number. Visit the OKI website for the authentication tool.



Colour pg 4

Mono pg 14

MFPs pg 17

Dot Matrix pg 26

To get the full picture...



...use OKI Original Consumables

OKI Original Consumables offer guaranteed page yields and protect your device so your business can enjoy stunning print quality for longer.

Improving the global environment is one of our key values, which is why we're committed to reducing plastic waste. As well as increasing the amount of recycled products in our packaging, our resource circulation initiative enables customers to return used OKI original consumables to us, so we can safely and effectively recycle them and help protect the planet.

OKI Original Consumables - the full picture, guaranteed.

Visit www.oki.com/eu/printing



Print Smart, Print OKI

MFPs


Did you know...
All OKI MFPs offer scan to email at no additional cost if you have installed SENDYS Explorer.



MC160 colour MFP

Printer model	Consumable	Order code	Unitary EAN code	Life (pages)	Gross dimensions (mm) w x d x h
MC160	High Cap Black Toner	44250724	5031713044604	2,500	399 x 108 x 110
MC160	High Cap Cyan Toner	44250723	5031713044598	2,500	399 x 108 x 110
MC160	High Cap Magenta Toner	44250722	5031713044581	2,500	399 x 108 x 110
MC160	High Cap Yellow Toner	44250721	5031713044574	2,500	399 x 108 x 110
MC160	Std Cap Cyan Toner	44250719	5031713044550	1,500	399 x 108 x 110
MC160	Std Cap Magenta Toner	44250718	5031713044543	1,500	399 x 108 x 110
MC160	Std Cap Yellow Toner	44250717	5031713044536	1,500	399 x 108 x 110
MC160	Imaging Unit	44250801	5031713044697	Mono: up to 45,000 Colour: up to 11,250	433 x 333 x 255

NB Toner yields based on 5% coverage • Imaging unit yield based on continuous print • Std Cap = Standard Capacity High Cap = High Capacity



MC160 toners

Banner Totems

A4/A3 free standing plastic totem

Model	Order code	Unitary EAN code	Gross weight (kg)	Gross dimension (mm) w x d x h
A3 free standing PLASTIC totem 30 x 120cm	09006046	5017534 950867	1.8kgs	365x55x1235
A4 free standing PLASTIC totem 21 x 90cm	09006043	5017534 950850	1.2kgs	303x65x923



A3 free standing metal totem

Model	Order code	Unitary EAN code	Gross weight (kg)	Gross dimension (mm) w x d x h
OKI FASTDISPLAY. A3 free standing METAL totem 30 x 90cm	09006044	0660902551507	6.5Kgs	400x200x950
OKI FASTDISPLAY. A3 free standing METAL totem 30 x 120cm	09006045	0660902551514	7.5Kgs	400x200x1250
OKI FASTDISPLAY. A3 free standing METAL totem 30 x 141cm	09006047	0660902551521	8.5Kgs	400x200x1460
OKI FASTDISPLAY. A3 free standing METAL totem 30 x 162cm	09006048	0660902551538	9.5Kgs	400x200x1670




A3 ceiling hanging metal totem

Model	Order code	Unitary EAN code	Gross weight (kg)	Gross dimension (mm) w x d x h
OKI FASTDISPLAY. A3 ceiling METAL totem 30 x 90cm	09006049	0660902551545	5.5Kgs	400x160x950
OKI FASTDISPLAY. A3 ceiling METAL totem 30 x 120cm	09006050	0660902551552	6.5Kgs	400x160x1250
OKI FASTDISPLAY. A3 ceiling METAL totem 30 x 141cm	09006051	0660902551569	7.5Kgs	400x160x1460
OKI FASTDISPLAY. A3 ceiling METAL totem 30 x 162cm	09006052	0660902551576	8.5Kgs	400x160x1670



A3 wall mounted metal totem

Model	Order code	Unitary EAN code	Gross weight (kg)	Gross dimension (mm) w x d x h
OKI FASTDISPLAY. A3 wall mounted METAL totem 30 x 90cm	09006053	0660902551583	5.5Kgs	400x160x950
OKI FASTDISPLAY. A3 wall mounted METAL totem 30 x 120cm	09006054	0660902551590	6.5Kgs	400x160x1250
OKI FASTDISPLAY. A3 wall mounted METAL totem 30 x 141cm	09006055	0660902551606	7.5Kgs	400x160x1460
OKI FASTDISPLAY. A3 wall mounted METAL totem 30 x 162cm	09006056	0660902551613	8.5Kgs	400x160x1670



Product compatibility

C100 / MC100 Series toner / imaging unit

Order codes	44250724	44250723	44250722	44250721	44250719	44250718	44250717	44250801
C110/C130	T	T	T	T	T	T	T	IU
MC160	T	T	T	T	T	T	T	IU

Key: T = Toner IU = Imaging Unit

C300 Series / C3000 MFP Series / C500 Series / MC300 Series / MC500 Series toner

Order codes	43459324	43459371	43459370	43459369	44469803	44469706	44469705	44469704	44469804	44469724	44469723	44469722	44973508	44973536	44973535	44973534	44973533	46490608	46490607	46490606	46490605	46490404	46490403	46490402	46490401	46508716	46508715	46508714	46508713	46508712	46508711	46508710	46508709			
C301/C321													T	T	T	T																				
C310/C330					T	T	T	T																												
C331					T	T	T	T																												
C332																											T	T	T	T	T	T	T	T		
C510/C530					T	T	T	T	T	T	T	T																								
C511/C531					T	T	T	T		T	T	T	T																							
C532/C542																		T	T	T	T	T	T	T	T	T										
C3520 MFP/C3530 MFP	T	T	T	T																																
MC332/MC342													T	T	T	T																				
MC350/MC360	T	T	T	T																																
MC351/MC361					T	T	T	T																												
MC352/MC362					T	T	T	T																												
MC363																										T	T	T	T	T	T	T	T	T		
MC561					T	T	T	T	T	T	T	T																								
MC562					T	T	T	T		T	T	T																								
MC563/MC573																		T	T	T	T	T	T	T												

Key: T = Toner

Business Printing Specialists

OKI is a global business-to-business brand dedicated to creating cost effective, professional in-house printing solutions which are designed to increase the efficiency of today's and tomorrow's businesses and their workflows. As pioneers in innovative print technologies from digital LED to High Definition Colour, we have a portfolio of award winning A3 and A4 colour and mono printers and MFPs, for workgroups and businesses of all sizes. This combined with our solutions enables businesses to achieve both image focused, vibrant, professional quality print communications and budget flexibility.

OKI's portfolio also includes precision-engineered large-format printing systems specifically designed for the sign, graphics, CAD and GIS markets that provide industry-leading productivity and image quality. In addition, our POS and dot matrix printers complete our range of printing solution.



Considering the Environment

OKI is committed to its role as a responsible partner for all its stakeholders: Shareholders, business partners, end-users, local communities and employees.

As part of the OKI Group's Charter of Corporate Conduct, OKI continually reviews its efforts to provide environmentally sound solutions to its customers:

- OKI products are designed and manufactured with reducing the impact on the environment in mind.
- Increasing the amount of our hardware products and consumables that are recycled is one of our strategic objectives.
- We feel responsible for conducting our business in an environmentally sound manner, contributing to conservation and activities within our local communities.

OKI's Green Leaf symbol, found on all products and packaging, represents our total commitment to collection, recycling and environmental processes.



3 Year Warranty

Our devices are manufactured to the highest standards of quality and technology, which has been confirmed by independent tests.

We are so convinced of the high quality of our products that we are offering you an extension of the standard warranty period to 3 years – for free! Simply register your product within 30 days of purchase to be eligible for our unique all inclusive offer. Fully covered by OKI! For further information please visit your local website.



20 years of LED Technology

OKI pioneered the development of digital LED technology in printers over 20 years ago. This innovation delivers High Definition printing – for more accurate, striking printed documents. Thanks to this digital LED technology, our printers are compact, environmentally friendly and energy efficient, using significantly less raw materials in the manufacturing process and consuming less energy. LED print heads have no moving parts, making our LED printers robust and ultra reliable.



High Definition Colour

High Definition Colour is OKI's own unique collection of market-defining hardware and software technologies. Together, these components deliver unsurpassed colour printing – simply, intelligently, perfectly.

We pioneered Single-pass Flat Paper Path technology to bring you fast affordable colour printing. In consumables, we created a special Microfine High Definition Toner to ensure your documents are printed in superior quality.

We championed digital LED printing technology: our High Definition LED printheads have no moving parts and deliver pin sharp images.

The combination of the range of media and software solutions we offer means you have much more control of what you want to print, when you want to print – without leaving the office.

OKI EUROPE LTD.

EMEA Head Office
Blays House, Wick Road
Egham TW20 0HJ
United Kingdom
T +44(0) 20 8219 2190
F +44(0) 20 8219 2199
WWW.OKI.COM/EU