Precision tweezers

Precision tweezers: Pointed tips straight

- For applications in microelectronics, jewelrymaking, watchmaking, medicine and laboratory technology
- Suitable for delicate standard applications and precision work on small components or wires
- ◆ For all models with the suffix SA or SASL in the order number: Special stainless steel, non-magnetic, nonrusting, acid-proof, heat-resistant
- For all models with the suffix S in the order number: Stainless steel, robust tips, non-rusting, non-reflecting surface



				,	
3.150 Inch / 80 mm	Model	Weight		Material	Description
		oz.	g		
N5-5	M5S	0.21	6	Stainless steel	Micro-tweezers, very pointed tips, e.g. for precision work under a microscope.
4.252 Inch / 108 mm	Model	Weigh	nt	Material	Description
		OZ.	g		·
	ACSA	0.56	16	Special stainless steel	Precision tweezers with serrated finger grips for secure handling. For precise bending and holding of components or wires.
3 ² ks	20AS	0.42	12	Special stainless steel	Precision tweezers with serrated finger grips and inside-serrated tips for secure handling. Guide pin to avoid overlapping of tips. For precise bending and holding of components or wires.
4.331 Inch / 110 mm	Model	Weight		Material	Description
		OZ,	g		
14 60	3CSA	0.39	11	Special stainless steel	Precision tweezers, standard model for delicate work.
111 60	3CSASL	0.39	11	Special stainless steel	Precision tweezers, standard model for delicate work. Same as 3CSA, but economy model.
Log	53CSA	0.39	11	Special stainless steel	Precision tweezers with anti-crush feature. Prevents damage to sensitive components. Tweezers relieved at front for secure handling.