

YR-LINE

DISCOVER A NEW WORLD

MORE POWER... SLIM SIZE!

BM1R
BM2R
BL1R
BL2R
BA1R
BA2R



2x8A
DOUBLE
OUTPUT

16A
SINGLE
OUTPUT

DISCOVER THE MOST **POWERFUL** TIMERS



ABOUT **SYR-LINE**

The new specialized range at Crouzet Control, aimed to satisfy the most unique requirements of your applications by innovating in design, engineering and development.

Meet the first member of the Syr-Line range:

The 17.5 mm Analog Timers, a new family of 6 timers with higher power of 16 A and double output of 8 A, with all the classic functions and 2 additional special functions.

HIGH POWER 1 x 16 A

CONTROL MORE OR BIGGER LOADS

Forget about having a combination of Timer and Contactor to control bigger loads or a larger number of loads, Syr-Line are your all-in-one solution..

EXTRA PROTECTION WHEN YOU NEED IT

Syr-Line products have greater capacity to withstand surge or inrush current than standard timers due to higher current capacity.

SPECIAL FUNCTIONS:

LATCHING AND DELAYED LATCHING

Along with the classic functions, Syr-Line offers the special functions Latching (Alternating) (TL) and Delayed Latching (Alternating) (Tt), allowing you to turn on and off the output relay with a voltage signal.

WIDE TIME RANGE

Program your timer to work from as little as 0.5 seconds delay to as long as a 10-day delay (240 hours).

DOUBLE OUTPUT 2 x 8 A

INSTANTANEOUS OR TIMED RELAY IN A SLIM PACKAGE

The only 17.5 mm timer on the market offering a dual output version with easy selection on the front face, allowing the option of both outputs to work together simultaneously, or one working instantaneously and the other delayed.

OPTION 1: INSTANTANEOUS

Turn on one output instantaneously and the second output with a time delay, to allow different loads to be switched-on gradually.

OPTION 2: TIMED

Select the two output relays working together and reduce costs by controlling different loads with the same device.

MONO OR MULTI FUNCTION

Select between a multifunction version with the 12 most popular functions or a monofunction version ON-Delay or Repeat-Cycle.

INTERNATIONAL CERTIFICATIONS


Compliant with the highest standards, Syr-Line 17.5 mm timers are cULus, CE, RoHS and CCC certified.

ENGINEERING EXPERTISE FOR CUSTOM NEEDS

Crouzet can easily customize Syr-Line timers for your specific application.



› Part Number System



AMERICAS

CANADA

InnoVista Sensors™
Tel.: +1 (800) 677 5311
Fax: +1 (800) 677 3865
americas.custserv@crouzet.com

MEXICO

InnoVista Sensors™
Tel.: +1 (800) 677 5311
Fax: +1 (800) 677 3865
americas.custserv@crouzet.com

USA

InnoVista Sensors™
Tel.: +1 (800) 677 5311
Fax: +1 (800) 677 3865
americas.custserv@crouzet.com

COUNTRIES NOT LISTED

InnoVista Sensors™
Tel.: +1 (800) 677 5311
Fax: +1 (800) 677 3865
americas.custserv@crouzet.com

EUROPE / MIDDLE EAST / AFRICA

BELGIUM

InnoVista Sensors™
Tel.: +32 (0) 2 462 07 30
Fax: +32 (0) 2 461 00 23
klantenservice@crouzet.com

FRANCE

InnoVista Sensors™
Tel.: +33 (0) 475 802 101
Fax: +33 (0) 475 828 900
relationclient@crouzet.com

GERMANY / AUSTRIA

InnoVista Sensors™
Tel.: +49 (0) 2103/980-0
Fax: +49 (0) 2103/980-222
kundenservice@crouzet.com

ITALY

InnoVista Sensors™
Tel.: +39 (02) 66 599 211
Fax: +39 (02) 66 599 218
assistenzaclienti@crouzet.com

SPAIN / PORTUGAL

InnoVista Sensors™
Tel.: +34 (93) 484 39 70
Fax: +34 (93) 484 39 73
atencionalcliente@crouzet.com

SWITZERLAND

InnoVista Sensors™
Tel.: +41 (0) 62 887 30 30
Fax: +41 (0) 62 887 30 40
kundenservice@crouzet.com

THE NETHERLANDS

InnoVista Sensors™
Tel.: +31 (0) 71-581 20 30
Fax: +31 (0) 71-541 35 74
klantenservice@crouzet.com

UNITED KINGDOM

InnoVista Sensors™
Tel.: +44 (0) 1202 416 172
Fax: +44 (0) 1202 416 198
customer.relation@crouzet.com

COUNTRIES NOT LISTED

InnoVista Sensors™
Tel.: +33 (0) 475 802 102
Fax: +33 (0) 475 828 900
customer.relation@crouzet.com

ASIA / PACIFIC

CHINA

InnoVista Sensors™
Tel.: +86 (21) 8025 7166
Fax: +86 (21) 6107 1771
china@crouzet.com

INDIA

InnoVista Sensors™
Tel.: +91 (80) 4113 2204/05
Fax: +91 (80) 4113 2206
india@crouzet.com

SOUTH KOREA

InnoVista Sensors™
Tel.: +82 (2) 2679 8312
Fax: +82 (2) 2679 9888
korea@crouzet.com

EAST ASIA PACIFIC

InnoVista Sensors™
Tel.: +86 (21) 8025 7177
Fax: +86 (21) 6107 1771
eap@crouzet.com

WWW.CROUZET-CONTROL.COM



WWW.INNOVISTASENSORS.COM



Warning:

The product information contained in this catalogue is given purely as information and does not constitute a representation, warranty or any form of contractual commitment. Crouzet Automatismes SAS and its subsidiaries reserve the right to modify their products without notice. It is imperative that we should be consulted over any particular use or application of our products and it is the responsibility of the buyer to establish, particularly through all the appropriate tests, that the product is suitable for the use or application. Under no circumstances will our warranty apply, nor shall we be held responsible for any application (such as any modification, addition, deletion, use in conjunction with other electrical or electronic components, circuits or assemblies, or any other unsuitable material or substance) which has not been expressly agreed by us prior to the sale of our products.

PRODUCT OFFER

BM1R		BM2R		BA1R		BA2R		BL1R		BL2R	
BM1R16MV1		BM2R08MV1		BA1R16MV1		BA2R08MV1		BL1R16MV1		BL2R08MV1	
	1 X 16 A		2 X 8 A		1 X 16 A		2 X 8 A		1 X 16 A		2 X 8 A
	12-240 V \sim		12-240 V \sim		12-240 V \sim		12-240 V \sim		12-240 V \sim		12-240 V \sim
	Multifunction		Multifunction		Delay on Make A: ON-Delay At: + Memory		Delay on Make A: ON-Delay At: + Memory		Repeat Cycle L: OFF Start Li: ON Start		Repeat Cycle L: OFF Start Li: ON Start
	R1: Timed		R1: Timed R2: Timed/ Instantaneous		R1: Timed		R1/R2: Timed		R1: Timed		R1/R2: Timed

PRODUCT MARKET

ENERGY & INFRASTRUCTURE

- › Water & Waste Treatment
- › Water Filtration
- › Water Disinfection
- › Compactors

FOOD & BEVERAGE

- › Baking Ovens
- › Refrigeration
- › Food & Drink Dispensers
- › Food Processing

TRANSPORTATION

- › Trucks and Buses
- › Specialty Vehicles
- › Construction Equipment

INDUSTRIAL


- › Assembly Machines
- › Machine Tools
- › Materials Handling
- › Metal Process
- › Motors and Drives
- › Packaging Equipment
- › Plastic Machinery
- › Test Equipment
- › Textile Manufacturing
- › Wood Process
- › Others

COMMERCIAL

- › Printing & Other

BUILDING

- › Access Control
- › Parking Barrier
- › Door Control
- › HVAC
- › Air
- › Filtration
- › Lighting
- › Building Automation



PRODUCT LAYOUT

PROTECTIVE COVER

- › Protect the knobs and the front face from the environment and avoid accidental movement

UNIVERSAL POWER SUPPLY

- › Syr-line timers fits all popular voltages from 12 → 240 V $\overline{\sim}$
- › Connexion compatible with the standard industrial layout

MODULAR SHAPE

- › To fit in modular panels

SIGNAL INPUT

- › For functions when controlling the timer with a signal is needed

SMALL SCREW POTENTIOMETERS

- › For right tuning of your timer

DIN RAIL MOUNT

- › For easy installation in your panel

LARGE POTENTIOMETERS

- › Allows to set the right configuration in your timer with your fingers

SLIM PACKAGE

- › 17.5 mm width plastic housing that helps you save space in your panel

FUNCTIONS MARKING

- › With all the function diagrams available for each part number

2 LED INDICATORS

- › For visualization of the status and output of your timer

SPECIAL FUNCTION


- › To select special functions Latching (Alternating) and Delayed Latching (Alternating) or select in double output versions if second relay works timed or instantaneous

HIGH POWER 1 x 16 A















- › Relay output version for high power applications

DOUBLE 2 x 8 A

- › Relay output version available for standard power applications that requires two relays



PRODUCT FUNCTIONS

	BM1R	BM2R	BA1R	BA2R	BL1R	BL2R		BM1R	BM2R	BA1R	BA2R	BL1R	BL2R	
A  ON-Delay (Delay on Make)	✓	✓	✓	✓			H  Interval	✓	✓					
Ac  ON/OFF Delay (Delay on Make/Break)	✓	✓					Ht  Interval with Memory	✓	✓					
At  Summation Time	✓	✓	✓	✓			N  Watchdog	✓	✓					
B  Single Shot (One Shot)	✓	✓					TL  Latching (Alternating) – Leading Edge	✓	✓					
C  OFF-Delay (Delay on Break)	✓	✓					Tt  Delayed Latching (Alternating) – Leading Edge	✓						
D  Flasher (Symmetrical) – OFF Start	✓	✓					L  Repeat Cycle (Asymmetrical) – OFF Start					✓	✓	
Di  Flasher (Symmetrical) – ON Start	✓	✓					Li  Repeat Cycle (Asymmetrical) – ON Start					✓	✓	

U: Power Supply (A1/A2)
 Y1: Trigger Signal (A1/Y1)
 R1/R2: Relays Outputs Timed → R1 (15/16/18) → R2 (25/26/28)

R2: Relay Output Instantaneous (21/22/24)
 T: Timing
 ∞: Infinity