





REVISIONS					
REV	DESCRIPTION	DATE	ECO	DR	APPD
A	CHANGED TO MARKING LABEL ON LEADS	8-17-13	1889595	LRK	MTW



8. PART IS RoHS COMPLIANT.
7. DIMENSIONS PRECEDED BY AN * ARE CONTROLLED BY ENGINEERING DESIGN AND TOOLING.
6. LEADWIRE: A.W.G. #24, STRANDED, TFE INSULATED PER MIL-W-16878/4 AND UL1716.
5. INSULATION: SILICONE RUBBER.
4. DIELECTRIC STRENGTH: 1,200 VOLTS RMS AT 60 Hz FOR 1 SECOND MINIMUM, ELEMENT TO HEAT SINK SURFACES. 1 mA. MAXIMUM LEAKAGE CURRENT.
3. TEMPERATURE LIMIT: 150°C MAXIMUM AT ZERO POWER.
2. RESISTANCE: 99.14 (109.05/89.23).
1. ELEMENT: NON-INDUCTIVE PATTERN.

UNLESS OTHERWISE SPECIFIED DIMENSIONS AND TOLERANCES IN INCHES DIMENSIONS IN [] ARE IN MILLIMETERS		INITIALS	DATE	ITEM	REQD	PART/STOCK NO	MATERIAL DESCRIPTION					
ONE PLACE (.0)	} ±.030 [±0.76]	DR	LRK 2368	6-20-11	TITLE: THERMOFOIL(TM) HEATER SPECIFICATION DRAWING		 www.minco.com COMPANY CONFIDENTIAL PROPRIETARY INFORMATION OF MINCO PRODUCTS, INC. DO NOT DUPLICATE					
TWO PLACE (.00)		CHK										
THREE PLACE (.000)		APP	BGB 5234	8-23-11								
ANGLES:		ENGR	M WINGERT	8-29-11								
MATERIAL:		QA										
		PRD	MK 1333	8-30-11								
FINISH:		NEXT ASSY	CATEGORY									
		USED ON	INIT. JOB	STOCK NO	SCALE	NONE	DWG SIZE	B	 	CAGE IDENT. 09359	SHEET 1 OF 1	REV A