

2.4. Adhesive Tape Dispensers



Adhesive Tape Dispenser 50 mm (max)

- Coating: conductive powder coated finish
- Core diameter: 76 mm
- Surface resistance: $R_{pp} < 1 \times 10^3 \Omega$
- Colour: Black

Reference: 42-100-6007

IEC 61340
Compliant

Adhesive Tape Dispensers 29 mm

- Metal conductive dispenser with black colour epoxy coating
- Material: ABS
- Core diameter: 25 mm and 76 mm
- Surface resistance: $1 \times 10^5 < R_{pp} < 1 \times 10^9 \Omega$
- Colour: Black

Reference: 41-092-0103

3. ACCESSORIES

3.1. Conditioning

a. Dissipative stretch film



Technical Data

- Excellent mechanical properties
- Electrostatic characteristics: pink electrostatic dissipative LDPE



- Suitable for machine and hand wrapping
- Recyclable

EN 61340
and
ANSI/ESD
S20.20 –
1999
Compliant

Thickness μm 23

Dimensions available

Dimensions m	Weight kg	Core diameter mm	Usage	Reference
0,5 x 250 (+/- 5%)	3 (+/- 5%)	50	Manual	85-100-0018
0,5 x 1000 (+/- 5%)	12 (+/- 5%)	75	Automatic	85-100-0019