



## Vishay Semiconductors

## Ultrabright White LED, Ø 3 mm



#### **DESCRIPTION**

The VLHW4400 is a diffused, untinted 3 mm LED for high end applications where supreme luminous intensity is required.

These lamps utilize the highly developed ultrabright InGaN technologies.

The lens and the viewing angle is optimized to achieve best performance of light output and visibility.


#### PRODUCT GROUP AND PACKAGE DATA


Product group: LEDPackage: 3 mm

Product series: standard
Angle of half intensity: ± 30°

#### **FEATURES**

- Diffused, untinted lens
- · Utilizing ultrabright InGaN technology
- · High luminous intensity







#### **APPLICATIONS**

- · Interior and exterior lighting
- Outdoor LED panels
- · Instrumentation and front panel indicators
- Replaces incandescent lamps
- · Light guide compatible

PARTS TABLE												
PART COLOR		OUS INTENSITY (mcd)		at I <sub>F</sub>	מנ יי		OORDINATE (x, y)		FORWARD VOLTAGE (V)		TECHNOLOGY	
		MIN.	TYP.	MAX.	(mA)	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.	
VLHW4400-JKPL	Cool white	450	800	1125	5	ı	0.33, 0.33	-	2.6	2.8	3.2	InGaN and converter
VLHW4400-QPMM	Warm white	450	800	1125	5		0.44, 0.41	ı	2.6	2.8	3.2	InGaN and converter

ABSOLUTE MAXIMUM RATINGS (T <sub>amb</sub> = 25 °C, unless otherwise specified) VLHW4400						
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT		
Reverse voltage		V <sub>R</sub>	5	V		
DC forward current		I <sub>F</sub>	20	mA		
Peak forward current	at 1 kHz, t <sub>p</sub> /T = 0.1	I <sub>FSM</sub>	0.1	А		
Power dissipation		P <sub>V</sub>	85	mW		
Junction temperature		Tj	+ 120	°C		
Operating temperature range		T <sub>amb</sub>	- 40 to + 85	°C		
Storage temperature range		T <sub>stg</sub>	- 40 to + 85	°C		
Soldering temperature	t ≤ 5 s	T <sub>sd</sub>	260	°C		
Thermal resistance junction/ambient		R <sub>thJA</sub>	400	K/W		



## VLHW4400-....

# Vishay Semiconductors

OPTICAL AND ELECTRICAL CHARACTERISTICS (T <sub>amb</sub> = 25 °C, unless otherwise specified) VLHW4400-JKPL, COOL WHITE							
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Luminous intensity	$I_F = 5 \text{ mA}$	Ι <sub>V</sub>	450	800	1125	mcd	
Chromatically coordinate x acc. to CIE 1931	$I_F = 5 \text{ mA}$	х	-	0.33	-		
Chromatically coordinate y acc. to CIE 1931	$I_F = 5 \text{ mA}$	У	-	0.33	-		
Angle of half intensity	$I_F = 5 \text{ mA}$	φ	-	± 30	-	deg	
Forward voltage	$I_F = 5 \text{ mA}$	V <sub>F</sub>	2.6	2.8	3.2	V	
Reverse current	V <sub>R</sub> = 5 V	I <sub>R</sub>	-	-	10	μA	

OPTICAL AND ELECTRICAL CHARACTERISTICS ( $T_{amb} = 25  ^{\circ}C$ , unless otherwise specified) VLHW4400-QPMM, WARM WHITE							
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Luminous intensity	$I_F = 5 \text{ mA}$	I <sub>V</sub>	450	800	1125	mcd	
Chromatically coordinate x acc. to CIE 1931	$I_F = 5 \text{ mA}$	х	-	0.44	-		
Chromatically coordinate y acc. to CIE 1931	$I_F = 5 \text{ mA}$	У	-	0.41	-		
Angle of half intensity	$I_F = 5 \text{ mA}$	φ	-	± 30	-	deg	
Forward voltage	$I_F = 5 \text{ mA}$	V <sub>F</sub>	2.6	2.8	3.2	V	
Reverse current	V <sub>R</sub> = 5 V	I <sub>R</sub>	-	-	10	μΑ	

HROMATICATION OF THE STATE OF T		TED CLASSIFIC	CATION (T <sub>amb</sub> = 25 °C	C, unless otherwise sp	pecified)
	Х	Υ		Х	Υ
	0.2960	0.2590		0.3189	0.3302
IIZ	0.2910	0.2680	1   1	0.3288	0.3452
JK	0.3005	0.2825	ML	0.3288	0.3282
	0.3045	0.2715	]	0.3197	0.3131
	0.2910	0.2680		0.3288	0.3081
11	0.2850	0.2790	NIZ	0.3288	0.3282
JL	0.2960	0.2955	NK	0.3386	0.3426
	0.3005	0.2825	1	0.3386	0.3235
	0.3045	0.2715		0.3288	0.3282
KK	0.3005	0.2825	NL	0.3288	0.3453
NN	0.3100	0.2970	- INL	0.3386	0.3591
	0.3130	0.2840	]	0.3386	0.3426
	0.3005	0.2825		0.3386	0.3235
KL	0.2960	0.2955	ОК	0.3386	0.3426
NL .	0.3070	0.3120		0.3484	0.3571
	0.3100	0.2970	]	0.3484	0.3388
	0.3100	0.2970		0.3386	0.3426
LIZ	0.3197	0.3131		0.3386	0.3591
LK	0.3205	0.2956	OL	0.3484	0.3730
	0.3130	0.2840	]	0.3484	0.3571
	0.3070	0.3120		0.3484	0.3388
LL	0.3189	0.3302	PK	0.3484	0.3571
LL	0.3197	0.3131	]   PN	0.3582	0.3715
	0.3100	0.2970	]	0.3582	0.3542
	0.3197	0.3131		0.3484	0.3571
MIZ	0.3288	0.3282	DI	0.3484	0.3730
MK	0.3288	0.3081	PL	0.3582	0.3792
	0.3205	0.2956	1	0.3582	0.3715

#### Note

Chromaticity coordinate groups are tested at a current pulse direction of 25 ms and a tolerance of ± 0.01.



### VLHW4400-....

## Vishay Semiconductors

	Х	Υ			Х	Y
	0.421	0.433	-		0.452	0.443
	0.437	0.438			0.469	0.448
QM	0.430	0.421		NM	0.460	0.431
	0.415	0.416			0.444	0.426
	0.415	0.416			0.444	0.426
	0.430	0.421			0.460	0.431
QN	0.423	0.405		NN	0.451	0.414
	0.409	0.400			0.436	0.409
	0.409	0.400			0.436	0.409
0.0	0.423	0.405		NO	0.451	0.414
QO	0.416	0.387		NO	0.443	0.397
	0.402	0.382			0.428	0.392
	0.402	0.382		ND	0.428	0.392
OD	0.416	0.387			0.443	0.397
QP	0.409	0.372		NP	0.435	0.382
	0.397	0.367			0.421	0.377
	0.437	0.438			0.469	0.448
PM	0.452	0.443		MM	0.487	0.454
FIVI	0.444	0.426		IVIIVI	0.477	0.437
	0.430	0.421			0.460	0.431
	0.430	0.421			0.460	0.431
PN	0.444	0.426		MN	0.477	0.437
111	0.436	0.409		IVIIV	0.467	0.420
	0.423	0.405			0.451	0.414
	0.423	0.405			0.451	0.414
PO	0.436	0.409		МО	0.467	0.420
10	0.428	0.392		WIG	0.458	0.403
	0.416	0.387			0.443	0.397
	0.416	0.387			0.443	0.397
PP	0.428	0.392		MP	0.458	0.403

#### Note

• Chromaticity coordinate groups are tested at a current pulse direction of 25 ms and a tolerance of ± 0.01.

LUMINOUS INTENSITY CLASSIFICATION						
GROUP	LIGHT INTENSITY (mcd)					
STANDARD	MIN.	MAX.				
U1	450	560				
U2	560	715				
V1	715	900				
V2	900	1125				

#### Note

• Luminous intensity is tested with an accuracy of ± 15 %.

The above type Numbers represent the order groups which include only a few brightness groups. Only one group will be shipped on each reel (there will be no mixing of two groups on each reel). In order to ensure availability, single brightness groups will not be orderable.

In a similar manner for colors where color groups are measured and binned, single color groups will be shipped on any one reel. In order to ensure availability, single color groups will not be orderable.

## Vishay Semiconductors

### **TYPICAL CHARACTERISTICS** (T<sub>amb</sub> = 25 °C, unless otherwise specified)




Fig. 1 - Forward Current vs. Ambient Temperature




Fig. 2 - Relative Luminous Intensity vs. Angular Displacement




Fig. 3 - Relative Intensity vs. Wavelength




Fig. 4 - Relative Intensity vs. Wavelength




Fig. 5 - Forward Current vs. Forward Voltage




Fig. 6 - Relative Luminous Intensity vs. Forward Current



#### www.vishay.com

# Vishay Semiconductors




Fig. 7 - Coordinates of Colorgroups for Cool White





Fig. 8 - Coordinates of Colorgroups for Warm White

#### **PACKAGE DIMENSIONS** in millimeters



technical drawings according to DIN specifications

Not indicated tolerances ± 0.25

Drawing-No.: 6.544-5403.01-4

Issue: 2; 18.06.10

21948

Rev. 1.0, 31-May-12


2.54 nom.



### VLHW4400-....

## Vishay Semiconductors

### **BAR CODE PRODUCT LABEL** (example)



- A. Type of component
- B. Manufacturing plant
- C. SEL selection code (bin):

e.g.: EA = code for luminous intensity group 4C = code for chromaticity coordinate

- 1 = code for forward voltage
- D. Date code year/week
- E. Day code (e.g. 1: Monday)
- F. Batch no.
- G. Total quantity
- H. Company code



### **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.