# 8845A/8846A 6.5 Digit Precision Multimeters






Fluke 8845A



Fluke 8846A



Use the built-in TrendPlot paperless chart recorder to graphically identify the extent of drift and intermittent events in analog circuits



View results in Histogram mode to reveal stability or noise problems in analog circuits

ANLZ MATH STATE Max 1.000102V=	1.000054V-			
# 65 /100	Ave 1.000032			
Min .999946V=	StdDv .000056			
#SAMPLEST MOUNE T	1 SHOT ) STOP			

Handle even the most demanding measurements with high accuracy and 6.5 digit resolution



#### Included Accessories

LCI Line Power Cord, TL71 Test Lead Set, Spare Line Power fuse, Programmers Manual/User Manual on CD-ROM, FVF-BASIC FlukeView Forms Software Basic Version.

#### **Ordering Information**

Fluke 8845A	6.5 Digit Precision Multimeter
Fluke 8845A/SU	6.5 Digit Precision Multimeter
	(software & cable)
Fluke 8846A	6.5 Digit Precision Multimeter
Fluke 8846A/SU	6.5 Digit Precision Multimeter
	(software & cable)

## Precision and versatility for bench or systems applications

The Fluke 8845A and 8846A, 6.5 digit precision multimeters have the precision and versatility to handle your most demanding measurements on the bench or in a system.

Dual Display offers versatile graphical capabilities: The 8845A and 8846A features a unique graphical display that can reveal signal quality issues like drift, intermittent and stability by viewing the measurement data as a real time TrendPlot<sup>™</sup>, Histogram or Statistics using the unique analyze mode.

Wide Measurement Ranges: Resistance or current has been extended to cover the widest range possible. Perform 4-wire measurements easily

with two leads: Patented split terminal jacks for 2x4 Ohms function allow you to perform precise 4-wire measurements with only two leads instead of four. Optional Kelvin leads accessories are available to enable you to establish a 4-wire connection even in tight spaces. Systems Capabilities: Both instruments include an RS-232, IEEE-488 and Ethernet interface as standard, with popular DMM emulation modes make systems integration a simple task.

**Software:** Transfer data points from your meter to your PC with the free copy of FlukeView Forms Basic. To customize your forms upgrade with FVF-UG.

### Features

	8845A	8846A			
Display	Dual VFD Dot Matrix				
Resolution	6.5 Digits				
Measurement Rate (Rdgs/s)	1000				
Continuity / Diode Test	Yes				
Analytical Functions	Statistics, Histogram, TrendPlot™, Limit Compare				
Math Functions	NULL, Min/Max, dB/dBm				
USB Device Port	-	USB Memory Drive port			
Real Time Clock	_	Yes			
Interfaces	RS232, IEEE-488.2, Ethernet				
Programming Languages/ Emulation Modes	SCPI (IEEE-488.2), Agilent 34401A, Fluke 45				
Safety	Designed to comply with IEC 61010-12000-1, ANSI / ISA-S82.01-1994, CAN /				

Designed to comply with IEC 61010-12000-1, ANSI / ISA-S82.01-1994, CAN / CSA-C22.2 No.1010.1-92 1000V CATI / 600V CATII

## Specifications

(Check the Fluke web for detailed specifications)

		8845A			8846A	
Function*	Range	Resolution	Accuracy* (%)	Range	Resolution	Accuracy* (%)
Voltage DC	1000 V	100 nV	0.0035	1000 V	100 nV	0.0024
Voltage AC (Freq 300 Hz)	750 V	100 nV	0.06	1000 V	100 nV	0.06
Resistance (2x4 Wire)	100 MΩ	100 μΩ	0.01	1 GΩ	10 μΩ	0.01
Current DC	10 A	100 pA	0.05	10 A	100 pA	0.05
Current AC (Freq. 3Hz-10kHz)	10 A	1 μA	0.10	10 A	10 nA	0.10
Freq/Period	300 kHz	1 μHz	0.01	1 MHz	1 µHz	0.01
Capacitance	-	-	-	1 nF to 0.1 F	1 pF	1
Temperature RTD	-	-	-	-200 to +600°	0.001°	0.06

\* Accuracy =+/- (% of reading)

Size (HxWxD): 88 mm x 215 mm x 293 mm Weight: 3.6 kg One Year Warranty

## **Recommended Accessories**

884X-512M

USB Memory 512M







**TL2X4W-PT** 2x4 Wire Ohms Test lead 2mm Probe Tip **FVF-UG** FlukeView Forms Software Upgrade

For more accessories see website: www.fluke.com and check the Fluke 8845A/8846A product pages