


# Keysight Technologies

## N9322C Basic Spectrum Analyzer

### Configuration Guide



This step-by-step process will help you determine which option numbers to specify when ordering your Keysight N9322C BSA to ensure the meets your testing needs.

## Ordering Information

Description	Model number	Additional information
Basic spectrum analyzer 9 kHz to 7 GHz	N9322C	Accessories supplied as standard with each analyzer: USB cable, N-BNC adapter, BNC cable, power cord, and documentation CD-ROM


### Step 1. Add performance options

Description	Option number	Additional information
Preamplifier, 7 GHz	N9322C-P07	Improves the noise floor for low-level signal detection
Precision frequency reference	N9322C-PFR	Reduces frequency drift for more accurate measurements; aging rate: $\pm 1 \times 10^{-7}$ /year. Orderable only with initial purchase of the N9322C base model
Baseband input	N9322C-BB1	Optimizes DANL <sup>1</sup> and phase noise performance in the low frequency band for xDSL and AM/FM IBOC <sup>2</sup> measurements

1. DANL: Displayed average noise level
2. BOC: In-band On-channel

### Step 2. Add spectrum analysis features

Description	Option number	Additional information
Time-gated spectrum analysis	N9322C-TMG	Measures any one of several signals separated in time, or excludes periodic interfering signals
Signal monitor with spectrogram record and playback	N9322C-MNT	Adds spectrogram view, record, and playback for spectrum monitoring
Channel scanner	N9322C-SCN	Provides channel power measurement of multiple channels, max. 20 channels
Task planner	N9322C-TPN	Implements customized test task that includes 20 consecutive instrument setups. Improves test efficiency for repetitive tasks. Find more information at <a href="http://www.keysight.com/find/taskplanner">www.keysight.com/find/taskplanner</a>
EMI filters and quasi-peak detector	N9322C-EMC	Provides CISPR compliant resolution bandwidth (200 Hz, 9 kHz, 120 kHz and 1 MHz) and quasi-peak detector for basic EMI precompliance test.




Using spectrogram for signal monitoring

## Ordering Information (continued)

### Step 3. Add demodulation analysis capability

Description	Option number	Additional information
AM and FM demodulation analysis	N9322C-AMA	Provides modulation metrics of an AM or FM signal: carrier power, modulation rate, AM depth, frequency deviation, SINAD <sup>3</sup> , and carrier frequency offset
ASK and FSK demodulation analysis	N9322C-DMA	Provides modulation metrics of an ASK or FSK signal: carrier power, ASK error, depth, and index, FSK deviation, FSK error, magnitude error, and carrier frequency offset


3. SINAD: Signal-to-noise and distortion ratio



Viewing FSK demodulation metrics with option DMA

### Step 4. Add stimulus-response measurement capability

Description	Option number	Additional information
Tracking generator, 7 GHz	N9322C-TG7	Provides transmission measurement of RF devices, from 5 MHz to 7 GHz. Output level from -20 dBm to 0 dBm, in 1 dB steps
Reflection measurement (requires Option TG7)	N9322C-RM7	<ul style="list-style-type: none"> <li>Provides reflection measurements including return loss, VSWR, insertion loss, and distance-to-fault</li> <li>Requires the tracking generator module (Option TG7)</li> <li>Recommended accessories include N9311X-201 precision mechanical calibrator (3-in-1 OSL) and N9311X-586 phase stable cable N(m) to N(f)</li> </ul>



Using the option RM7 for reflection measurements

### Step 5. Add additional features and connectivity

Description	Option number	Additional information
USB average power sensor support (U2000 Series)	N9322C-PWM	
USB peak and average power sensor support (U2020 X-Series)	N9322C-PWP	
Security features	N9322C-SEC	Includes user data sanitation and port control
GPIO interface	N9322C-G01	IEEE-488 bus connector, used in test automation systems

## Ordering Information (continued)

### Step 6. Select physical instrument configuration

Description	Option number	Additional information
Benchtop configuration	Standard	Provides two side carrying straps, four rear feet, and four button feet with a tilt stand
Portable configuration	N9322C-PRC	Provides a convenient, pivoting carrying handle as well as rubber protective bumpers



N9322C portable configuration

### Step 7. Add optional accessories

Description	Option number	Additional information
Hard transit case	N9322C-1TC	645 x 444 x 268 mm, 13 kg nominal
Rack mount kit	N9322C-1CM	Includes a rack mount flange. Fits standard 9-inch rack and occupies three units (3U) of rack space
Rack mount and handle kit	N9322C-1CP	Includes a rack mount flange and front handle kit. Fits standard 9-inch rack and occupies 3U rack space
Precision mechanical calibrator, 3-in-1 OSL	N9311X-201	DC to 7 GHz, N (m) connector
Minimum loss pad	N9311X-548	50 to 75 $\Omega$ adapter, DC to 1 GHz

Looking for more N9311X series RF accessories? Visit [www.keysight.com/find/n9311x](http://www.keysight.com/find/n9311x).

### Step 8. Choose localized User's Guide

Description	Option number	Additional information
English User's Guide	N9322C-ABA	
Simplified Chinese User's Guide	N9322C-AB2	
Japanese User's Guide	N9322C-ABJ	

## Ordering Information (continued)

### Step 9. Choose warranty length

Description	Option number	Additional information
<b>Select coverage</b>		
3-year warranty (return to Keysight), standard	Included	
5-year warranty assurance plan (return to Keysight)	R-51B-001-5Z	Priority warranty service includes one-time coverage for an EOS/ESD failure

### Step 10. Add calibration, technical training, support, and upgrade services

Description	Option number	Additional information
Commercial calibration certificate with test data	N9322C-UK6	Calibration certificate only available at time of instrument purchase; only provides measurement results
<b>Select Keysight calibration plan</b>		
3-year calibration assurance plan (return to Keysight)	R-50C-011-3	Priority calibration service covering all calibration costs for 3 years; 15% cheaper than buying stand-alone calibrations
5-year calibration assurance plan (return to Keysight)	R-50C-011-5	Priority calibration service covering all calibration costs for 5 years; 20% cheaper than buying stand-alone calibrations

Other calibration options may available, for more information on calibration, go to [www.keysight.com/find/calibration](http://www.keysight.com/find/calibration).

For more information on training and application support services, go to [www.keysight.com/find/training](http://www.keysight.com/find/training).

## Instrument Upgrades

### Upgrade your existing N9322C

Fast license-key upgrades that do not require additional hardware:

1. Place an order for the upgrade with Keysight and request to receive the software entitlement certificate through email.
2. Install the license key in the N9322C. Upgrade firmware to the latest revision if required.
3. Restart the N9322C.
4. Begin using the new capability.

Installation, calibration, and verification information is available at <http://www.keysight.com/find/n9322c>.

### Select additional upgrades



Description	Upgrade number	Additional information
Preamplifier, 7 GHz	N9322CK-P07	
Baseband input	N9322CK-BB1	
Time-gated spectrum analysis	N9322CK-TMG	
Signal monitor with spectrogram record and playback	N9322CK-MNT	
Channel scanner	N9322CK-SCN	
Task planner	N9322CK-TPN	
AM/FM demodulation analysis	N9322CK-AMA	
ASK/FSK demodulation analysis	N9322CK-DMA	
Tracking generator, 7 GHz	N9322CK-TG7	The tracking generator requires additional hardware that is installed inside the N9322C. Upgrade at Keysight's local service center
Reflection measurement	N9322CK-RM7	
USB average power sensor support (U2000 Series)	N9322CK-PWM	
USB peak and average power sensor support (U2020 X-Series)	N9322CK-PWP	
Security features	N9322CK-SEC	
GPIB interface	N9322CK-G01	Requires additional hardware installed inside the N9322C
Hard transit case	N9322CK-1TC	
Rack mount kit	N9322CK-1CM	
Rack mount and handle kit	N9322CK-1CP	
English User's Guide	N9322CK-ABA	
Simplified Chinese User's Guide	N9322CK-AB2	
Japanese User's Guide	N9322CK-ABJ	
Portable configuration	N9322CK-PRC	
EMI filters and quasi-peak detector	N9322CK-EMC	

## For More Information

Please refer to these resources:

- *Keysight N9322C Basic Spectrum Analyzer*, Brochure, literature number 5991-1166EN.
- *Keysight N9322C Basic Spectrum Analyzer*, Data Sheet, literature number 5991-1167EN.

From Hewlett-Packard through Agilent to Keysight  
 For more than 75 years, we've been helping you unlock measurement insights.  
 Our unique combination of hardware, software and people can help you reach  
 your next breakthrough. **Unlocking measurement insights since 1939.**



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: [www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)

**Americas**

Canada (877) 894 4414  
 Brazil 55 11 3351 7010  
 Mexico 001 800 254 2440  
 United States (800) 829 4444

**Asia Pacific**

Australia 1 800 629 485  
 China 800 810 0189  
 Hong Kong 800 938 693  
 India 1 800 11 2626  
 Japan 0120 (421) 345  
 Korea 080 769 0800  
 Malaysia 1 800 888 848  
 Singapore 1 800 375 8100  
 Taiwan 0800 047 866  
 Other AP Countries (65) 6375 8100

**Europe & Middle East**

Austria 0800 001122  
 Belgium 0800 58580  
 Finland 0800 523252  
 France 0805 980333  
 Germany 0800 6270999  
 Ireland 1800 832700  
 Israel 1 809 343051  
 Italy 800 599100  
 Luxembourg +32 800 58580  
 Netherlands 0800 0233200  
 Russia 8800 5009286  
 Spain 800 000154  
 Sweden 0200 882255  
 Switzerland 0800 805353  
 Opt. 1 (DE)  
 Opt. 2 (FR)  
 Opt. 3 (IT)  
 United Kingdom 0800 0260637

For other unlisted countries:  
[www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)  
 (BP-09-28-15)



[www.keysight.com/go/quality](http://www.keysight.com/go/quality)  
 Keysight Technologies, Inc.  
 DEKRA Certified ISO 9001:2008  
 Quality Management System

This information is subject to change without notice.  
 © Keysight Technologies, 2013 - 2015  
 Published in USA, October 22, 2015  
 5991-1168EN  
[www.keysight.com](http://www.keysight.com)

**myKeysight**

[www.keysight.com/find/mykeysight](http://www.keysight.com/find/mykeysight)  
 A personalized view into the information most relevant to you.

**Three-Year Warranty**

[www.keysight.com/find/ThreeYearWarranty](http://www.keysight.com/find/ThreeYearWarranty)  
 Keysight's commitment to superior product quality and lower total cost of ownership. The only test and measurement company with three-year warranty standard on all instruments, worldwide.

**Keysight Assurance Plans**

[www.keysight.com/find/AssurancePlans](http://www.keysight.com/find/AssurancePlans)  
 Up to five years of protection and no budgetary surprises to ensure your instruments are operating to specification so you can rely on accurate measurements.

[www.keysight.com/go/quality](http://www.keysight.com/go/quality)

Keysight Technologies, Inc.  
 DEKRA Certified ISO 9001:2008  
 Quality Management System

**Keysight Channel Partners**

[www.keysight.com/find/channelpartners](http://www.keysight.com/find/channelpartners)  
 Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

Insert registered trademarkss and copyright notes here. If none, remove row from table.

[www.keysight.com/find/n9322c](http://www.keysight.com/find/n9322c)

**myKeysight**

