

Cabinets - 19" lab racks

19" lab rack, stationary



- Modular design with base/plinth and cover plate, please order uprights according to desired height separately
- Stationary load-carrying capacity 150 kg, at a defined centre of gravity in the centre of the lab rack
- Recommended max. chassis depth 400 mm

Delivery comprises (kit)

Item.	Qty	Description
1	1	Base/plinth, St, 2 mm, RAL 7035
2	1	Trim at top, St, 1.5 mm, RAL 7035
4	1	Assembly kit

Order Information

Description	Item	Part no.
Base and trim	1 + 2 + 4	20118-743
Uprights (item 3) with EIA perforation, 24 U, RAL 7035, PU 2 pieces		20118-741
Uprights (item 3) with EIA perforation, 39 U, RAL 7035, PU 2 pieces		20118-742
Adjustable feet load-carrying capacity 100 kg per foot, PU 4 pieces		21190-571
Castors load-carrying capacity 150 kg per kit, castor diameter 52 mm, PU 4 pieces (2 locking, 2 non-locking)		20118-462
19" assembly kit (50 x screws, 50 x washers, 50 x nuts)		21101-809
19" assembly kit (100 x screws, 100 x washers, 100 x nuts)		21101-810

Technical data


Usable height	h	H
U	mm	mm
24	1067	1164
39	1733	1831

Note

- Please order uprights separately



For further information www.schroff.biz/oneclick
oneClick search code = Part no.



ServicePLUS see page 1.361