
Test adaptors

Photo shows 23021-607



- a: Measuring field for current and voltage measurement
- b: Header for wire wrap



ServicePLUS see page 10.29

Test adaptors, type B

- For DIN 41612 connectors, type B
- Measuring field for current and voltage measurement (U/I), (a)
- Header with pin diameter 0.6 mm for wire wrap (b)
- Outer pin rows (pin 1a, c and pin 32a, c) with wider tracks for power supply (2 A per track)

Delivery comprises

Item	Qty	Description
1	1	Test adaptor with fitted guide rails and equipped test bridges
2	10	Replacement test bridges

Order Information

Connector type	Height U	For board depth mm	Backplane type	Measuring field for	Part no.
B64	3	160	1L	U/I	23021-607
B64	3	220	1L	U/I	23021-651

Note

- Detailed dimensions and test adaptor types see page 10.28
- 6/9 U test adaptors see page 10.26



For further information <u>www.schroff.biz/oneclick</u> oneClick search code = Part no.