



XNT Soldering Tip Family

- + Most difficult, high mass soldering jobs
- + Maximum power and response for top performance
- + Optimal balance between power, control and running costs with wide range of tips
- + Highest quality soldering standard for widest range of applications



| | Article | a / b (mm) / (inch) | Article | a / b (mm) / (inch) | Article | a / b (mm) / (inch) | |
|---------------------|---|--|---|--|---|---|--|
| Chisel | XNT A T0054485199 BESTSELLER | 1.6 mm / 0.4 mm 0.063 inch / 0.016 inch | XNT CS T0054487099 | 3.2 mm / 0.8 mm 0.126 inch / 0.315 inch | XNT MX T0054488399 | 3.2 mm / 0.8 mm 0.126 inch / 0.315 inch | |
| | XNT AX T0054486499 | 1.6 mm / 0.8 mm 0.063 inch / 0.315 inch | XNT D T0054485399 | 4 mm / 0.8 mm 0.157 inch / 0.315 inch | XNT 6 T0054485699 | 1.6 mm / 0.4 mm 0.063 inch / 0.016 inch | |
| | XNT B T0054485799 BESTSELLER | 2.4 mm / 0.8 mm 0.094 inch / 0.315 inch | XNT H T0054485999 BESTSELLER | 0.8 mm / 0.4 mm 0.031 inch / 0.016 inch | XNT 1SC T0054486299 BESTSELLER | 0.4 mm / 0.15 mm 0.016 inch / 0.006 inch | |
| | XNT BX T0054488299 | 2.4 mm / 0.8 mm 0.094 inch / 0.315 inch | XNT K T0054486099 | 1.2 mm / 0.4 mm 0.047 inch / 0.016 inch | XNT 1SCNW T0054488199 | 0.3 mm / 0.1 mm 0.012 inch / 0.004 inch | |
| | XNT C T0054485899 only US | 3.2 mm / 0.8 mm 0.126 inch / 0.315 inch | XNT L T0054486699 | 3.2 mm / 0.8 mm 0.126 inch / 0.315 inch | XNT 4X 45° T0054487499 | 1.2 mm / 0.4 mm 0.047 inch / 0.016 inch | |
| Round | XNT 1L T0054487199 | 0.2 mm 0.008 inch | XNT 4 T0054485599 | 1.2 mm 0.047 inch | High mass soldering jobs | Power Response | Heat up time °C -350 -300 -200 -100 0 5 Sec.* *from 50°C to 350°C / 120°F to 620°F |
| | XNT 1LX T0054487299 | 0.2 mm 0.008 inch | XNT AA 45° T0054488499 | 1.6 mm 0.063 inch | | | |
| | XNT 1S T0054485299 | 0.2 mm 0.008 inch | XNT BB 45° T0054488599 | 2.4 mm 0.094 inch | | | |
| | XNT 1SLX 45° T0054487599 | 0.4 mm 0.016 inch | XNT CC 45° T0054488699 | 3.2 mm 0.126 inch | | | |
| | XNT 1X T0054486599 | 0.4 mm 0.016 inch | XNT F 45° T0054488799 | 1.2 mm 0.047 inch | | | |
| | XNT AS T0054486999 only US | 1.6 mm 0.063 inch | | | | | |
| Conical | XNT 1 T0054485099 BESTSELLER | 0.5 mm 0.02 inch | Measuring tip Measuring tip T0054486199N | | | | |
| | XNT S T0054486899 | 0.4 mm 0.016 inch | | | | | |
| Gullwing | XNT GW1 T0054485499 | 1.6 mm 0.063 inch | | | | | |
| | XNT GW2 short T0054488099 | 1.0 mm 0.039 inch | | | | | |
| Knife | XNT KN T0054486399 | 2.0 mm 0.079 inch | | | | | |

Weller®

weller-tools.com/toolselector/en
weller-tools.com/toolselector/us