



Designed to get the **job done**



BMP™ 51
LABEL MAKER

BMP™ 53
LABEL MAKER

with Bluetooth® Technology

Designed to get the **job done**

When you need clear, durable labels on the spot, you need the BMP™51 or BMP™53 Label Maker from Brady. It offers crisp printing, easy formatting, convenient label sizes, and portability required for electrical and datacom installations, laboratory identification, facility and safety labelling.

Get the job done **FASTER.**

Change supplies in seconds. Hassle free drop-in cartridges have both the label material & ribbon inside!

Automatic label formatting. Cartridges feature smart cell technology that tells the printer how to correctly format your label. You just drop in a cartridge and the printer calibrates the rest.

Quick to print. Prints 25.4 mm per second – which means no more waiting around for labels to print.

Durable built-in cutter. There's a self-cleaning cutter that can cut through any material with ease, and even grips the label until you need it.



Get the job done **EASIER.**

Battery options for portability. Use with the AC power supply, AA-batteries or simply with the rechargeable Li-Ion battery which allows you to print over 3,000 labels on a single charge.

Wireless capabilities. Built-in Bluetooth® technology and the optional Wi-Fi card provide wireless printing options.

Robust software. LabelMark™ Labelling Software enables the printer to print: bar code symbologies, time/date stamps, imported graphics, automatic data serialisation, and more.

Continuous & die-cut label materials. Whether you need to label wires, cables, panels or equipment, you can do it all with this one printer. There are 18 material types and more than 130 label parts to choose from.

Labels up to 38.10 mm wide. Make large labels that can easily be identified from a distance (or make continuous labels up to 1m long!).

Magnet. Keep your printer handy, use the magnet to hold your printer on panel doors, metal ladders or any metal surface.

Get the job done **WITH CONFIDENCE.**

Label for the long haul. Our labels won't fade, smear or fall off – so you only need to label something once.

A rugged printer you can rely on. This printer can survive in all kinds of harsh environments, temperatures and has a rugged, drop tested construction.

APPLICATIONS

Electrical ID



Self-Laminating Wire & Cable Markers



Terminal Block Markers



PermaSleeve™ Wire Marking Sleeves




Control Panel & Electrical Panel Labels

Voice & DataCom ID



Cable Flags



Punch Block & Patch Panel Labels



Faceplate & Outlet Labels




Self-Laminating Cable Markers

Laboratory ID



Cryo Tube Labels



Slide Labels



Tissue Cassette Labels



Centrifuge & PCR Tube Labels

Product ID



Rough Surface Labels



Tamper Resistant Labels



Rating Plate Labels

Facility & Safety ID



Indoor / Outdoor Grade Facility & Safety Labels

SPECIFICATIONS



BMP51



BMP53

Print Technology	Thermal Transfer	
Print Resolution	300 dpi	
Print Speed	25.40 mm / sec	
Colour Capability	Single Colour Printing	
Max. Labels Per Day	250 labels / day	
Keyboard	Fully featured QWERTY keyboard	N/A
Portability	Yes	
Weight	1.400 g	1.278 g
Power Supply	Lithium Ion Battery and AC Power	
PC Connectivity	USB	
Stand Alone Printing	Yes	No
Connectivity Options	USB, Bluetooth & optional Ethernet, WiFi	
Continuous vs. Die Cut Labels	Continuous and Die-cut Labels	
Materials Supported	more than 130 Stock Parts	
Tape Widths	Continuous Widths from 9.53 to 38 mm Variety of Die-cuts	
Max. Label Width	38 mm	
Max. Print Width	36 mm	
Label Roll Length	Up to 7.62 m	
Text Sizes	4 to 196 point	
Multi-Line Print	Yes	
Print Rotation	Yes	
Serialisation	Yes	
Bar code	Yes	
Warranty	1 Year Limited Warranty included	

Order Reference	Description
BMP51 PRINTER KIT EU	BMP51 printer with Battery Pack and AC-adaptor/Battery Charger EU
BMP53 PRINTER KIT EU	BMP53 printer with Battery Pack and AC-adaptor/Battery Charger EU
BMP51 PRINTER KIT EU-LM	BMP51 printer with Battery Pack and AC-adaptor/Battery Charger EU and LabelMark
BMP53 PRINTER KIT EU-LM	BMP53 printer with Battery Pack and AC-adaptor/Battery Charger EU and LabelMark
BMP51 PRINTER KIT UK	BMP51 printer with Battery Pack and AC-adaptor/Battery Charger UK
BMP53 PRINTER KIT UK	BMP53 printer with Battery Pack and AC-adaptor/Battery Charger UK
BMP51 PRINTER KIT UK-LM	BMP51 printer with Battery Pack and AC-adaptor/Battery Charger UK and LabelMark
BMP53 PRINTER KIT UK-LM	BMP53 printer with Battery Pack and AC-adaptor/Battery Charger UK and LabelMark

Printer comes with a hard carrying case, Rechargeable Li-on Battery and AC Adaptor with power cord, USB Cable, Drivers CD, Product CD, Quick Start Guide, MC-1500-595-WT-BK

ACCESSORIES

We have a variety of accessories to speed up the label making process:

- Magnet to apply printer to panel doors, metal ladders or any metal surface
- Li-Ion Battery allows you to print over 3,000 labels on a single charge
- Wireless, Ethernet, USB or Bluetooth options give you the flexibility to network your printer however you prefer

Order Reference	Description
UBP-Li-Ion-AC-EUR	Universal Li-Ion Battery Pack with AC-adaptor/Battery Charger EU
UBP-Li-Ion-AC-UK	Universal Li-Ion Battery Pack with AC-adaptor/Battery Charger UK
UBP-Li-Ion-AC-120V	Universal Li-Ion Battery Pack with AC-adaptor/Battery Charger US
M50-MAGNET	BMP50 Magnet Accessory
M50-HC	BMP50 Hard Case
M50-USB CABLE	BMP50 USB Cable
BMP-UBP 12V	Universal Li-Ion Battery Pack
NET-BT	BMP50 Bluetooth Network Card
NET-WIFI	BMP50 Bluetooth/WIFI Network Card
NET-LAN	BMP50 LAN Network Card
NET- BT-WIFI-LAN	BMP50 Bluetooth/WIFI/LAN Network Card
M50-71-AC-BC-EU	BMP50/71-AC Adaptor/Battery charger EU
M50-71-AC-BC-UK	BMP50/71-AC Adaptor/Battery charger UK
M50-71-AC-BC-120V	BMP50/71-AC Adaptor/Battery charger US
M50-BATT-TRAY	BMP50 Battery Tray for 8 AA batteries
LabelMark™ 5 Standard	LabelMark™ 5 Standard Labelling Software



Brady Mobile Software

Create, edit and print labels using your Android™ phone.

Introducing “Brady Mobile” – the first Brady application for on-the-job label making. Simply download the Brady Mobile App on your Android Smartphone for instant, quick and easy access - right from the palm of your hand. There is no need to carry a laptop or any other device!

With Brady Mobile, you can use your Android Smartphone to:

- Design a label from scratch
- Edit an existing label
- Create and edit label templates
- Print to your BMP™51 or BMP™53 Label Maker using Bluetooth® technology

Import Microsoft Excel® files

Want to use Microsoft Excel to create labels from existing data? Simply import your data from Excel to the Brady Mobile App. You can print the labels wirelessly from your mobile device whenever you need them.

Save label files on your mobile device

Any files or label templates you create in the app can be saved on your mobile device for quick and easy label making in the future.

Built-in bar coding, symbols and pictograms

Brady Mobile App features the ability to create bar code labels and has hundreds of symbols and pictograms that you can insert into your label files.

Automatic updates (No software upgrade costs!)

The Brady Mobile App will be automatically updated when new label types, printers, and materials become available.



The Brady Mobile App includes the following label types:

- General ID and Bar code Labels
- Terminal Blocks
- BIX Blocks
- Patch Panels
- 110 Blocks
- Wire / Cable ID
- Flags
- 66 Blocks



To Download:

Open the Android Market on your Android Smartphone. Search for “Brady Mobile” and download the app. Brady Mobile App is designed to run on Android OS Version 2.2 or higher.



Scan this QR code to go to the Android Market and search for “Brady Mobile”.

Microsoft Excel is a registered trademark of Microsoft Corporation.
Android is a trademark of Google Inc.



LabelMark™ Labelling Software

Brady's LabelMark™ Labelling Software lets you easily design, edit and print labels for Asset ID, Component Marking, Telecom/Datacom Labelling, Wiremarkers and more. Integrates completely with Microsoft® office, Autocad® applications and more. You can download more detailed information on our LabelMark Labelling Software on www.bradyeurope.com.

Get the job done **your way**

Wireless, Ethernet, USB or Bluetooth options

The BMP™51/BMP™53 Label Maker includes a Bluetooth enabled network card that can work only with the Brady Mobile App on your Android Smartphone.

Additional options are available to network your Brady BMP™53 Label Maker - making it quick and easy to print to the BMP™51/BMP™53 Label Maker without physically connecting it to multiple PCs. This gives you the flexibility to network your printer however you prefer.

Network Card Options:

- Ethernet Only
- WiFi + Bluetooth
- WiFi + Bluetooth + Ethernet



Hassle Free Cartridges

Easy-to-load cartridges with “Anti-jam” technology.

- Drop and Print - quick loading cartridge lets you change ribbon and labels in one fast step locking mechanism prevents labels from retracting into cartridge.
- Easy access to cartridge for quick changes.

Ribbon and label materials: all in ONE cartridge!

- Install or remove ribbon and material together in one easy step.
- No need to worry about matching the right ribbon to your materials.
- Ribbon and material run out simultaneously (less waste!)



Did you know?

The BMP™51/53 Label Maker has a built-in label retention feature. Your labels will remain on the cutter of the printer, after cutting. Paired with the magnet accessory and Brady's Mobile App, this is the ultimate answer to your “on the job” labelling requirements.

Voice & Datacom, Electrical, Product, Facility and Safety ID Materials


B #	Material Type	Description	Temp Ranges	Agency Approvals
B-109	Polyethylene tag	Cross-laminated polyethylene provides extreme tear resistance and excellent cold weather performance.	-40°C to 80°C	RoHS
B-342	PermaSleeve® PS Wire Marking Sleeves	3:1 heat shrinkable wire marking sleeve. Fits snugly around wire for identification and protection. Fade resistant and flame retardant. Sleeves meet insulating material and physical property specifications: SAE-AMS-DTL23053/5C (Class 1), SAE-AS-81531, MIL-STD-202, RoHS Compliant. Tested per ASTM E162, ASTM E662.	-55°C to 135°C	UL, RoHS
B-351	Destructible Vinyl Labels	White vinyl material with matt finish and permanent adhesive. Tamper-resistant material fractures to show signs of product tampering and prevent label removal in one piece. Use caution when removing from liner as material is fragile. Used for rating and serial plates.	-40°C to 80°C	RoHS
B-412	Polypropylene Tags	Thick polypropylene material used for punch block & patch panel identification. Offers high print legibility and high tensile strength.	-40°C to 100°C	RoHS
B-422	Polyester Labels	White label stock with glossy finish and 2 mils of adhesive for rough surface applications. Designed to withstand solvent exposure. UL rated for surfaces commonly used in solar panel manufacturing. Also used for component identification, punch block & patch panel labels, asset and inventory tracking.	-40°C to 100°C	UL, CSA, RoHS
B-427	Self-Laminating Vinyl Labels	Brady's most popular wire and cable marker. Self-laminating vinyl features white printable area with a clear "tail" that wraps around marker. Tail serves as overlaminate to protect the print. Superior resistance to abrasion, solvents, water, oil and dirt.	-80°C to 70°C	UL, RoHS
B-428	Metallised Polyester Labels	Withstands solvents and variable temperatures. Excellent for serial and rating plate applications with nameplate quality and a metal looking finish. Thermal transfer printable metallised polyester with matt finish.	-40°C to 120°C	UL, CSA, AGA, RoHS
B-483	Ultra Aggressive Adhesive Polyester Labels	White polyester thermal transfer label with glossy finish and aggressive adhesive. Specifically designed for powder coated and low energy surface application.	-40°C to 120°C	UL, CSA, RoHS
B-498	Repositionable Vinyl Cloth Labels	Repositionable vinyl cloth label for wire, cable, and component marking. Adhesive and cloth backing offers excellent holding power, while easily being repositioned and removed.	-80°C to 80°C	UL, RoHS
B-499	Nylon Cloth Labels	Nylon cloth with permanent adhesive allows labelling in environments with heat, cold, oil and dirt. Ideal for wire and cable marking, electronic component marking, laboratory vial identification, and general labelling.	-196°C to 90°C	UL, CSA, RoHS
B-584	Reflective Vinyl labels	Reflective quality makes material ideal for use in low light conditions.	-40°C to 82°C	-
B-595	Indoor/Outdoor Vinyl Tape	Durable, low-shrink vinyl with our most aggressive adhesive. Conforms to irregular, curved, rough and highly textured surfaces (painted cinder blocks, uneven wood, textured plastics, paper jacketed pipes, powder coated surfaces). Also adheres to difficult low energy surface items (PVC piping, blow-moulded equipment cases, ABS plastics, recycled plastics.)	-40°C to 82°C	RoHS

Laboratory ID Materials

B #	Material Type	Description	Temp Ranges	Agency Approvals
B-425	Polypropylene Labels	Matt white polypropylene labels with excellent solvent resistance.	-70°C to 100°C	UL, CSA, RoHS
B-427	Self-Laminating Vinyl Labels	Self-laminating vinyl labels feature a white printable area with a clear "tail" to wrap around the printed legend. Tail acts as an overlaminate protecting the print from freezers and liquid nitrogen temperatures. Die-cut to fit small and large straws and laboratory rods.	-80°C to 70°C	UL, RoHS
B-432	Polyester labels	Clear polyester with permanent acrylic based adhesive that withstands numerous solvents and can be applied to variable surfaces.	-80°C to 100°C	UL, CSA, RoHS
B-461	Self-Laminating Polyester Labels	Polyester label with a white thermal transfer printable zone and clear self-laminating tail. Performs well in common laboratory environments, including liquid nitrogen and autoclave applications. Good smudge and solvent resistance, to be used for tube and vial identification.	-196°C to 130°C	RoHS
B-481	StainerBondz™ Polyester Labels	Clear polyester, resistant to exposure of xylene and other chemicals that are commonly used in the slide staining process.	-80°C to 130°C	RoHS
B-482	Polyester Labels	Matt white polyester label with permanent acrylic based adhesive.	up to 35°C	RoHS
B-488	Matt White Polyester Labels	Polyester label with moderate chemical resistance. Resists short term xylene exposure, DMSO, and ethanol. Can be used for basic slide identification.	-80°C to 120°C	UL, CSA
B-490	FreezerBondz™ Polyester Labels	When wrapped upon itself by at least 3 mm, can be applied to frozen or room temperature vials and tubes. Also, ideal for labelling flat frozen surfaces. Can be stored in liquid nitrogen or freezers and lasts in autoclaves and hot water baths.	-196°C to 120°C	RoHS
B-492	FreezerBondz™ Polyester Labels	Can be applied to frozen or room temperature vials and tubes without needing to overlap itself. Extremely thin for fitting in snug racks and centrifuges. Can be stored in liquid nitrogen or freezers and lasts in autoclaves and hot water baths.	-196°C to 120°C	-
B-498	Repositionable Vinyl Cloth Labels	Repositionable vinyl cloth label for re-identification of post process tissue cassettes or other applications needing removability.	-80°C to 80°C	UL, RoHS
B-499	Nylon Cloth Labels	Nylon cloth material with a thick construction for easy handling, but highly conformable. Can be used on polypropylene in liquid nitrogen or freezer temperatures and lasts in autoclaves. Temperature range increases to 121°C when used in autoclave process.	-196°C to 90°C	UL, HF, CSA, RoHS

Brady Application Kits

Get the job done for less with a Brady Application Kit



Voice / Data Communications Kit

Everything you need to get started with your voice/data labelling.

BMP51: Part No. 710928 (EUR) or 710929 (UK) • **BMP53:** Part No. 710937 (EUR) or 710938 (UK) includes:

- BMP51 or BMP53 Printer with hard case, USB cable, rechargeable Li-on Battery and AC Adaptor with power cord
- Magnet Accessory
- Brady LabelMark™ 5 Labelling Software
- Self-laminating cable markers (M-18-427)
- Port, faceplate and general ID labels (M-375-422)
- General Id Label (MC-1500-595-WT-BK)



Electrical Kit

This kit includes a variety of wire and cable marking materials.

BMP51: Part No. 710930 (EU) or 710931 (UK) • **BMP53:** Part No. 710939 (EUR) or 710940 (UK) includes:

- BMP51 or BMP53 Printer with hard case, USB cable, rechargeable Li-on Battery and AC Adaptor with power cord
- Magnet Accessory
- Brady LabelMark™ 5 Labelling Software
- Wire and Cable Marking labels (M-132-499)
- Self-laminating cable markers (M-115-427)
- General Id Label (MC-1500-595-WT-BK)



Laboratory Identification Kit

Accurately identify and track samples in your laboratory.

BMP51: Part No. 710932 (EU) or 710933 (UK) • **BMP53:** Part No. 710941 (EUR) or 710942 (UK) includes:

- BMP51 or BMP53 Printer with hard case, USB cable, rechargeable Li-on Battery and AC Adaptor with power cord
- Brady LabelMark™ 5 Labelling Software
- Vial & tube labels (M-122-461)
- Well plate labels (M-131-499)
- General Id Label (MC-1500-595-WT-BK)



Check out our online catalogue with further information on materials and part numbers on www.bradyeurope.com/BMP51



WHEN PERFORMANCE MATTERS MOST™

BRADY Africa

PO BOX 18015
Jebel Ali, Dubai, UAE
Tel: +971 4 881 2524
Fax: +971 4 881 3183

BRADY Benelux

Industriepark C/3
Lindestraat 20
9240 Zele, Belgium
Tel. +32 (0) 52 45 78 11
Fax +32 (0) 52 45 78 12

Brady Central & Eastern Europe

Na Pántoch 18
831 06 Bratislava, Slovakia
Tel. +421 2 3300 4800
Fax +421 2 3300 4801

BRADY Denmark

Svendborgvej 39D
5260 Odense S
Tel. +45 66 14 44 00
Fax +45 66 14 44 50

BRADY France

Parc EURO CIT
45, avenue de l'Europe
59436 Roncq Cedex
Tel. +33 (0) 3 20 76 94 48
Fax +33 (0) 3 20 76 76 06

BRADY Germany

Büchenhöfe 2
63329 Egelsbach
Tel. +49 (0) 6103 7598 660
Fax +49 (0) 6103 7598 670

BRADY Hungary

Puskás Tivadar u. 4.
2040 Budaörs
Tel. +36 23 500 275
Fax +36 23 500 276

BRADY Italy

Via Pitagora 18
20128 Milano
Tel. +39 02 26 00 00 22
Fax +39 02 25 75 351

BRADY Middle East FZE

PO BOX 18015
Jebel Ali, Dubai, UAE
Tel. +971 4881 2524
Fax +971 4881 3183

BRADY Norway

Lerstadveien 506
6018 Ålesund
Tel. +47 70 13 40 00
Fax +47 70 13 40 01

BRADY Spain & Portugal

Calle Aragón 271
08007 Barcelona, Spain
Tel. +34 900 902 993
Fax +34 900 902 994

BRADY Sweden

Vallgatan 5
170 67 Solna
Tel. +46 (0) 8 590 057 30
Fax +46 (0) 8 590 818 68

BRADY Turkey

Selvili Sok. No: 3/4
4.Levent Istanbul 34330
Tel. +90 212 264 02 20 / 264 02 21
Fax +90 212 270 83 19

BRADY UK & Ireland

Wildmere Industrial Estate
Banbury, Oxon – OX16 3JU, UK
Tel. +44 (0) 1295 228 288
Fax +44 (0) 1295 228 100

BRADY WORLDWIDE

Australia 612-8717-6300
Brazil 55-11-3686-4720
Canada 1-800-263-6179
China (Beijing) 86-10-6788-7799
China (Shanghai) 86-21-6886-3666
China (Wuxi) 86-510-528-2222
Hong Kong 852-2359-3149
Japan 81-45-461-3600
Korea 82-31-451-6600
Latin America 1-414-540-5560
Malaysia 60-4-646-2700
Mexico 525-399-6963
New Zealand 61-2-8717-2200
Philippines 63-2-658-2077
Singapore 65-6477-7261
Taiwan 886-3-327-7788
Thailand 66-2-793-9200
USA 1-800-537-8791

Your distributor