

# COBRA

The ultra-purpose all rounder with a panoramic visual field.

Enveloping and without any visual interference the Cobra offers 180° panoramic visual field with perfect optical quality. The ability to interchange the temples with an adjustable strap and foam option makes the Cobra an ultra versatile model.

The Cobra adapts to all risks, versatile, modern design combined with quality and precision.

Ref: COBFSPSI and COBHDP  
Supplied with a microfibre pouch



COBHDP **HD**  
References supplied with an adjustable cord:



COBPSI



COBESP



COBPSF



COBPSJ



COBCONT



Europe Bolle Safety  
95 Rue Louis Guérin  
69100 Villeurbanne - France  
tel: 00 33 (0) 4 78 85 23 64  
fax: 00 33 (0) 4 78 85 28 56  
contact@bolle-safety.com

U.K. Bolle Safety  
Unit C83 - Barwell Business Park  
Leatherhead Road - Chessington  
Surrey - KT19 2NY  
tel. 00 44 (0)208 391 4700  
fax 00 44 (0)208 391 4733  
e-mail : sales@bolle-safety.co.uk

Other references available:  
KITFSCOB: Foam and strap kit  
OCCOBPSI: Clear spare lens anti-scratch, anti-fog

STANDARDS MARKINGS :

Products ref.	LENSES													FRAMES												
			Bolle Protection logo	Optical quality									Coatings (Optional marking K: anti-scratch N: anti-fog)		CE logo	Bolle Protection logo	Standards									CE logo
	EN 170 - UV	EN 172 - Solar (100% UV)		Permanent wear	Intermittent wear	Short period	Low energy impact 45 m/s	Medium energy impact 120 m/s	High energy impact 190 m/s	Extremes of temperature impact	Electric arc short circuiting	Molten metals and hot solids	anti-scratch	anti-fog				Liquid drops	Large dust particles > 5 microns	Gas and fine dust particles < 5 microns	Electric arc short circuiting	Low energy impact 45 m/s	Medium energy impact 120 m/s	High energy impact 190 m/s	Extremes of temperature impact	
COBPSI	2C-1,2			1		N/A	B	N/A	T	N/A	N/A			CE		EN 166	N/A	N/A	N/A	N/A	F	N/A	N/A	T	N/A	CE
COBHDPI 	2C-1,2			1		N/A	B	N/A	T	N/A	N/A		hydro- phobic	CE		EN 166	N/A	N/A	N/A	N/A	F	N/A	N/A	T	N/A	CE
COBPSJ	2C-1,2			1		N/A	B	N/A	T	N/A	N/A			CE		EN 166	N/A	N/A	N/A	N/A	F	N/A	N/A	T	N/A	CE
COBPSF		5-3,1		1		N/A	B	N/A	T	N/A	N/A			CE		EN 166	N/A	N/A	N/A	N/A	F	N/A	N/A	T	N/A	CE
COBESP		5-1,4		1		N/A	B	N/A	T	N/A	N/A			CE		EN 166	N/A	N/A	N/A	N/A	F	N/A	N/A	T	N/A	CE
COBCONT		5-1,1/1,4		1		N/A	B	N/A	T	N/A	N/A			CE		EN 166	N/A	N/A	N/A	N/A	F	N/A	N/A	T	N/A	CE
COBFSPSI	2C-1,2			1		N/A	B	N/A	T	N/A	N/A			CE		EN 166	3		N/A	N/A	N/A	B	N/A	T	N/A	CE
OCCOBPSI	2C-1,2			1		N/A	B	N/A	T	N/A	N/A			CE												
KIFSCOB																										

N/A: Non applicable

CHARACTERISTICS :

Lenses	PC - 2,2 mm - Curve 9
Frame	PC + Nylon + TPR
Strap	15mm adjustable
Foam	Yes on the COBFSPSI version
Spare lenses	Yes, clear spare lens

PACKAGING AND EAN 13 CODE :

	COBPSI	COBFSPSI
individual plastic bag	3660740006129	3660740005986
10 safety spectacles and 20 foam and strap kit per box	3660740106126	3660740105983
240 safety spectacles and 240 foam and strap kit per outer pack	3660740206123	3660740205980

Notified laboratories for certification :



PACKAGING AND EAN 13 CODE :

	COBPSI	COBHDPI	COBPSJ	COBPSF	COBESP	COBCONT
individual plastic bag	3660740006129	3660740006013	3660740006143	3660740006136	3660740006006	3660740005993
10 safety spectacles per box	3660740106126	3660740106010	3660740106140	3660740106133	3660740106003	3660740105990
200 safety spectacles per outer pack	3660740206123	3660740206017	3660740206147	3660740206130	3660740206000	3660740205997

PACKAGING AND EAN 13 CODE :

	OCCOBPSI
individual plastic bag	3660740006020
25 safety spectacles per box	3660740106027
300 safety spectacles per outer pack	3660740206024