


TOLERANCE ±0.15 .XX ±0.10 THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.





ISSUE NUMBER **ORIGINAL**











PCB LAYOUT LAYOUT TOLERANCE: ±0.05mm

SPECIFICATION:

CONTACT: BRASS


PLATING: 0.075µm Au MIN PLATED OVER 1.25µm TO 3.0µm Ni


INSULATION: PA9T, BLACK


MAGNET: N52, 5.0µm Ni MIN PLATED

VOLATGE RATING: 5V CURRENT RATING: 2A MAX

OPERATING TEMPERATURE RATING: -30°C ~+85°C











EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC. AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.: 686-0	0032220-111	UNIT: MM
DRAWN: E.S	DATE: JUN.22	2022
CHECKED: J.L.	DATE: AUG.04	/2022
SCALE: (IN C.A.D. 1:1)	SHEET 1 C)F 1

686-0032220-111 **ISSUE** DRAWING NUMBER: PART NUMBER: 686-0032220-111