



REACH
RoHS

UNLESS OTHERWISE SPECIFIED
TOLERANCE :
.X 0.38
.XX 0.25
.XXX 0.10
ANGLES : ±5°
DO NOT SCALE DRAWING

MATERIAL			
HOUSING	<input type="checkbox"/> PC UL94V-0 <input checked="" type="checkbox"/> PC UL94V-2	TYPE OF PLUG	<input checked="" type="checkbox"/> SHIELD <input type="checkbox"/> UNSHIELD
CONTACT	PHOSPHOR BRONZE FINE GOLD	COLD-PLATING	<input type="checkbox"/> 0.15U M/6U" MINIMUM <input type="checkbox"/> 0.38U M/15U" MINIMUM
	PLATED OVER NICKEL		<input type="checkbox"/> 0.76U M/30U" MINIMUM <input checked="" type="checkbox"/> 1.27U M/50U" MINIMUM
APPLICATION	<input type="checkbox"/> 4P4C <input type="checkbox"/> 6P2C <input type="checkbox"/> 6P4C <input type="checkbox"/> 6P6C <input checked="" type="checkbox"/> 8P8C		
	<input type="checkbox"/> 24 AWG SOLID <input type="checkbox"/> 24 AWG STRANDED <input type="checkbox"/> 26 AWG SOLID <input type="checkbox"/> 26 AWG STRANDED		
REV.	DESCRIPTION	ENG.	APPROVAL

Designed BY	Gene
DRAWN BY	gene-luo
CHECKED BY	Eric
APPROVED BY	Mark
Type No.	-

TITLE Shielded Cat5 RJ45 EMT modular data plug				G00350	
SIZE A4	UNIT mm	PART NO.	-	REV.	B
SCALE	2:1	THIRD ANGLE PROJECTION			
PAGE 1 OF 1			DATE 2021-12-13		

