


REVISIONS					
REV	DESCRIPTION	DATE	ECO	DR	APPD
A	CHANGED TO MARKING LABEL ON LEADS	8-17-13	1889595	LRK	MTW



8. PART IS RoHS COMPLIANT.
7. DIMENSIONS PRECEDED BY AN \* ARE CONTROLLED BY ENGINEERING DESIGN AND TOOLING.
6. LEADWIRE: A.W.G. #24, STRANDED, TFE INSULATED PER MIL-W-16878/4 AND UL1716.
5. INSULATION: SILICONE RUBBER.
4. DIELECTRIC STRENGTH: 1,200 VOLTS RMS AT 60 Hz FOR 1 SECOND MINIMUM, ELEMENT TO HEAT SINK SURFACES. 1 mA. MAXIMUM LEAKAGE CURRENT.
3. TEMPERATURE LIMIT: 150°C MAXIMUM AT ZERO POWER.
2. RESISTANCE: 60.28 (66.30/54.26).
1. ELEMENT: NON-INDUCTIVE PATTERN.

UNLESS OTHERWISE SPECIFIED DIMENSIONS AND TOLERANCES IN INCHES DIMENSIONS IN [ ] ARE IN MILLIMETERS		INITIALS	DATE	ITEM	REQD	PART/STOCK NO	MATERIAL DESCRIPTION		
ONE PLACE (.0)	} ±.030 [±0.76]	DR	LRK 2368	6-20-11		TITLE:  THERMOFOIL(TM) HEATER SPECIFICATION DRAWING	 www.minco.com COMPANY CONFIDENTIAL PROPRIETARY INFORMATION OF MINCO PRODUCTS, INC. DO NOT DUPLICATE		
TWO PLACE (.00)		CHK							
THREE PLACE (.000)		APP	BGB 5234	8-23-11					
ANGLES:	ENGR	M WINGERT	8-29-11						
	QA								
MATERIAL:		PRD	MK 1333	8-30-11			HR6936		
FINISH:		NEXT ASSY		CATEGORY				REV	A
		USED ON		INIT. JOB	STOCK NO	SCALE	NONE	DWG SIZE	B
								CAGE IDENT.	09359
								SHEET	1 OF 1