# Conductive Sensors 2-point level controller Type CL with potentiometer





- Conductive level controller
- Sensitivity adjustment from 250  $\Omega$  to 500 K $\Omega$
- For filling or emptying applications
- Low-voltage AC electrodes
- Easy installation on DIN rails or with 11 pin circular plug
- Rated operational voltage:
   24 VAC/DC, 115 VAC or 230 VAC
- Output 2 x 8A/250 VAC DPDT relay
- LED indication for: Output ON and Power ON





# **Product Description**

μ-Processor based level controller for liquids with a wide sensitivity range (like sewage water, chemicals, salt water etc.).

Max./min. control of charging/ discharging. The sensitivity is adjustable by means of the potentiometer and the rotary switch.

2 x 8A DPDT relay output.

Conductive level
DIN rail or plug mounting
No of inputs
Charge/discharge
Adjustment potentiometer
1 relay output
Relay DPDT
Power supply

# **Type Selection**

Mounting	Relay	Ordering no. Supply: 24 VAC/DC	Ordering no. Supply: 115 VAC	Ordering no. Supply: 230 VAC
DIN-rail	DPDT	CLD2EA1CM24	CLD2EA1C115	CLD2EA1C230
11-p circular plug		CLP2EA1CM24	CLP2EA1C115	CLP2EA1C230

# **Specifications**

Rated operational voltage (U <sub>B</sub> )					
Pin 2 & 10	230	195 to 265 VAC, 45 to 65 Hz			
	115	98 to 132 VAC, 45 to 65 Hz			
Supply class 2	24	19.2 to 28.8 VAC/DC			
Rated insulation voltage		<2.0 kVAC (rms)			
Rated impulse withstand					
voltage		4 kV (1.2/50 μs) (line/neutral)			
Rated operational power					
AC supply		5 VA			
AC/DC supply		5 VA / 5 W			
Delay on operate (t <sub>v</sub> )		< 300 mS			
Outputs					
Rated insulation voltage		250 VAC (rms) (cont./elec.)			
Relay Rating (AgCdO)		μ (micro gap)			
Resistive loads	AC1	8 A / 250 VAC (2500 VA)			
	DC1	1 A / 250 VDC (250 W)			
		or 10 A 25 VDC (250 W)			
Small induc. Loads	AC15	0,4 A 250 VAC			
	DC13	0,4 A / 30 VDC			
Mechanical life (typical)		≥ 30 x 10 <sup>6</sup> operations			
		@ 18'000 imp/h			
Electrical life (typical)	AC1	> 250'000 operations			
Level probe supply	Max. 5 VAC				
Level probe current	Max. 2 mA				
Sensitivity	250 $\Omega$ to 500K $\Omega$				
		Factory settings standard			
		range "S" 100KΩ			
Ranges L (Low sensitivity)	250 $\Omega$ to 5 K $\Omega$ , C <sub>F</sub> = 4.7 nF*				

Pangas C (Standard consitivity)	5 KO to 100 KO C - 2.2 nE*	
Ranges S (Standard sensitivity) Ranges H (High sensitivity)	5 KΩ to 100 KΩ, $C_F = 2.2 \text{ nF}^*$ 50 KΩ to 500 KΩ, $C_F = 1.0 \text{ nF}^*$	
	, .	
Dielectric voltage	>2.0 KVAC (rms)	
	(contacts / electronics)	
Rated impulse withstand volt.	4 kV (1.2/50 μS) (contacts /	
	electronics) (IEC 664)	
Operating frequency (f)		
Relay output	0.5 HZ	
Response time		
OFF-ON (t <sub>on</sub> )	1 s	
ON-OFF (t <sub>off</sub> )	1 s	
Environment		
Overvoltage category	III (IEC 60664)	
Degree of protection	IP 20 /IEC 60529, 60947-1)	
Pollution degree	2 (IEC 60664/60664A,	
	60947-1)	
Temperature		
Operating	-20° to +50°C (-4° to + 122°F)	
Storage	-50° to +85°C (-58° to +185°F)	
Housing material CLP	NORYL PPO, light grey	
CLD	ABS VO, light grey	
Weight		
AC supply	200 g	
AC/DC supply	125 g	
UL Approvals c <b>%</b> us	UL508, UL325, CSA-C22.2	
	No.247	
CE marking	Yes	
-		

<sup>\*</sup>C<sub>F</sub> = maximum Cable Capacitance

1



## **Mode of Operation**

#### Connection cable

2, 3, or 4 conductor PVC cable, normally screened. Cable length: max. 100 m. The resistance between the cores and the ground must be at least 500k. Normally, it is recommended to use a screened cable between probe and controller, e.g. where the cable is placed in parallel to the load cables (mains). The screen has to be connected to Y3 (reference).

#### Example 1


The diagram shows the level control connected as max. and min. control. The relays react to the low alternating current created when the


electrodes are in contact with the liquid.

The reference (Ref) must be connected to the container or if the container consists of a non-conductive material, to an additional electrode. (To be connected to pin Y3). (In the diagram this electrode is shown by the dotted line).

#### NB!

If only one level detection is required - interconnect the two inputs Y1 and Y2.







[D-version] (P-version)





# **Wiring Diagram**





# **Dimension Drawings**





### **Accessories**

- 11 pole circular socket
- Retaining spring

ZPD11 HF

## **Delivery Contents**

- Amplifier
- Packaging: Carton box
- Manual