

33ft HDMI Signal Booster and Extender - 8K 60Hz




33FT-8K-HDMI-BOOSTER






Front



Rear



| Component | | Function | |
|-----------|------------------|--|--|
| 1 | Power LED | Green: HDMI Booster is receiving power | |
| 2 | USB Power Port | Connect to an available USB Port or USB Wall Charger USB Power is recommended, but not required for every setup | |
| 3 | HDMI Input Port | Connect to an HDMI Source Device | |
| 4 | HDMI Output Port | Connect to an HDMI Display | |

Product Information

For the latest drivers/software, technical specifications, and declarations of conformance, please visit: <u>www.StarTech.com/33FT-8K-HDMI-BOOSTER</u>

Requirements

- HDMI Source Device x 1
- HDMI Display Device x 1
- HDMI Cables x 2

Note: It is recommended to use Premium HDMI Cables when connecting Devices to the HDMI Signal Booster and Extender.

Package Contents

- HDMI Booster x 1
- USB Power Cable x 1
- Quick-Start Guide x 1

Installation

Installing the HDMI Booster

Note: Power off all Source Devices, Displays, and Peripherals before completing the following installation steps

- Connect an HDMI Cable from the HDMI Source Device to the HDMI Input Port, 1. located on the front of the HDMI Booster.
- 2. Connect an HDMI Cable from the HDMI Display to the HDMI Output Port, located on the rear of the HDMI Booster.
- 3. (Optional) Connect the USB Power Cable from an available USB Port or USB Wall Charger to the USB Power Port, located on the front HDMI Booster.
- Power On all of the connected Devices. 4.

Supported Cable Lengths

| Max Cable Length From Source | Max Cable Length to Display | Total Cable Length | Maximum Resolution |
|---------------------------------|--------------------------------|-----------------------|-----------------------|
| 4m (13ft) | 6m (20ft) | 10m (33ft) | 8K 60Hz |
| 10m (33ft) | 15m (50ft) | 25m (83ft) | 4K 60Hz |
| 20m (65ft) | 25m (82ft) | 45m (147ft) | 1080p |

Regulatory Compliance FCC - Part 15

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

• Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.

Consult the dealer or an experienced radio/TV technician for help

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions:

(1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Changes or modifications not expressly approved by StarTech.com could void the user's authority to operate the equipment.

Industry Canada Statement

This Class B digital apparatus complies with Canadian ICES-003.

Cet appareil numérique de la classe [B] est conforme à la norme NMB-003 du Canada.

CAN ICES-3 (B)/NMB-3(B)

This device complies with Industry Canada licence-exempt RSS standard(s). Operation is subject to the following two conditions:

(1) This device may not cause interference, and (2) This device must accept any interference, including interference that may cause undesired operation of the device.

Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes:

(1) l'appareil ne doit pas produire de brouillage, et (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

Warranty Information

This product is backed by a two year warranty.

For further information on product warranty terms and conditions, please refer to www.startech.com/warranty.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.



Points de collecte sur www.quefairedemesdechets.fr Privilégiez la réparation ou le don de votre appareil !

StarTech.com StarTech.com LLP 4490 South Hamilton 45 Artisans Cres Road Groveport, Ohio London, Ontario N5V 5E9 43125 U.S.A. Canada

Itd.

StarTech.com Ltd. StarTech.com Ltd. Siriusdreef 17-27 Unit B. Pinnacle 15 2132 WT Hoofddorp Gowerton Rd, The Netherlands Brackmills Northampton NN4 7BW

United Kinadom

| FR: startech.com/fr |
|---------------------|
| DE: startech.com/de |
| ES: startech.com/es |
| NL: startech.com/nl |
| IT: startech.com/it |
| JP: startech.com/jp |
| |