2067 TORX® HF screwdriver with holding function for electronic applications, TX 6 \times 40 mm

Series Kraftform Micro







EAN: 4013288108647 **Size:** 137x13x13 mm

Part number:05118182001Weight:12 gArticle number:2067 TORX® HFCountry of origin:CZ

Customs tariff 82054000

number:

















- Kraftform Micro TORX® HF screwdriver with holding function for recessed TORX® screws
- Multi-component Kraftform Micro handle with anti-roll feature and swivel cap
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Holding function for TORX® screws, chrome-plated
- Take it easy tool finder: colour coding according to profile and size

High quality Wera Micro nutsetter set for precision mechanical work. Comes with practical holding function: the wedging forces resulting from the contact pressure between the drive tip and the screw profile securely hold the screw on the tool. Rapid twisting is possible by fixing the hand on the twist cap and using the fast-turning zone just below it. This makes time-consuming grip adjustments unnecessary. Power zone with integrated soft zones ensure the transfer of higher tightening and loosening torque. Precision zone for the right angle for adjustment work. The Wera Black Point tip offers high corrosion protection and an exact fit. "Take it easy" tool finder with colour coding according to profiles and size stamp – for simple and rapid accessing of the required tool.

Web link

https://products.wera.de/en/screwdrivers_series_kraftform_micro_2067_torx_hf.html

Wera - 2067 TORX® HF 05118182001 - 4013288108647

2067 TORX® HF screwdriver with holding function for electronic applications, TX 6 \times 40 mm

Series Kraftform Micro

Screwdriving jobs in electrical and

precision engineering applications

are often tedious and time-

consuming. We learned from users

what is important for them:

working speeds, torque, precision

- and we then focused particularly

on these issues.



TORX® HF profile



In tight assembly or disassembly situations, for example in engine compartments, it is not possible to securely hold the screw with the hand on the screwdriver, and the screw subsequently often gets lost. Lengthy searches or the loss of the screw (with the associated danger that could bring about) are the consequence. The HF tools developed by Wera are ideal because they feature an optimised geometry of the original TORX® profile. The wedging forces from the surface resulting

pressure between the drive tip and the screw profile mean that the screw is securely held on the tool!

Kraftform Micro Handle




Multi-component screwdriver handle for ergonomic working.

The refined screwdriver for electronics technicians




The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The free-turning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.

The precision zone



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The power zone




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The fast-turning zone



The fast-turning zone just below the rotating cap allows rapid twisting.

"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link

https://products.wera.de/en/screwdrivers_series_kraftform_micro_2067_torx_hf.html

Wera - 2067 TORX® HF 05118182001 - 4013288108647

2067 TORX® HF screwdriver with holding function for electronic applications, TX 6 x 40 mm Series Kraftform Micro



Further versions in this product family:

	\odot	\ \rangle	Å ▼	\varnothing	
		mm	mm	mm	inch
05118180001	TX 4	40	97	2.5	1 9/16
05118181001	TX 5	40	97	3.0	1 9/16
05118182001	TX 6	40	97	3.0	1 9/16
05118183001	TX 7	60	97	3.0	2 3/8
05118184001	TX 8	60	97	3.0	2 3/8
05118185001	TX 9	60	97	4.0	2 3/8
05118186001	TX 10	60	97	4.0	2 3/8