

# har-modular P module female straight



Part number	02 52 900 0001
Specification	har-modular P module female straight
HARTING eCatalogue	https://b2b.harting.com/02529000001

Image is for illustration purposes only. Please refer to product description.

## Identification

Category	Connectors
Series	har-modular <sup>®</sup>
Identification	P module
Element	Female connector
Description of the contact	Straight

## Version

Width of the module	5.08 mm
Connection type	Motherboard to daughtercard Mezzanine

## Technical characteristics

Insulation resistance	>10 <sup>11</sup> Ω
Limiting temperature	-55 +125 °C
Mating cycles	≥500
Isolation group	I (600 ≤ CTI)
Hot plugging	No
Moisture Sensitivity Level (MSL)	1 acc. to ECA/IPC/JEDEC J-STD-020D

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material flammability class acc. to UL 94	V-0



## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals


JL / CSA	UL 1977 ECBT2.E102079
02,00,0	CSA-C22.2 No. 182.3 ECBT8.E102079
Railway classification	F1/I2 acc. to NFF 16-101/102

## Commercial data

Packaging size	20
Net weight	0.82 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27460201 PCB connector (board connector)



## Mating conditions



To ensure reliable connections and prevent unnecessary damage, please refer to the application data diagrams. These recommendations are set out in IEC 60603-2.

The connectors should not be coupled and decoupled under electrical load.