

1-1718484-1 ✓ ACTIVE

AMP | AMP MCP Connector System

TE Internal #: 1-1718484-1

AMP MCP Connector System, Housing for Female Terminals, Wire-to-Device / Wire-to-Board, 25 Position, .157 in / .197 in [5 mm / 4 mm] Centerline, Black

[View on TE.com >](#)



Connectors > Automotive Connectors > Connector Housings > AMP MCP, UNSEALED CONNECTOR HOUSING



Connector & Housing Type: **Housing for Female Terminals**

Mating Tab Width: **1.5 mm, 2.8 mm [.059 in, .11 in]**

Connector System: **Wire-to-Board, Wire-to-Device**

Number of Positions: **25**

Centerline (Pitch): **4 mm, 5 mm [.157 in, .197 in]**

[All AMP MCP, UNSEALED CONNECTOR HOUSING \(187\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Board, Wire-to-Device
Sealable	No
Hybrid Connector	Yes
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	25
Number of Rows	3

Electrical Characteristics

Operating Voltage	36 VDC
Nominal Voltage Architecture	12 V, 24 V

Body Features



Cable Exit Angle	180°
Body Material	PBT GF
Primary Product Color	Black
Connector Code	A

Contact Features

Mating Tab Width	1.5 mm, 2.8 mm [.059 in][.11 in]
------------------	----------------------------------

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	No
Strain Relief	No
Mating Alignment Type	Polarized

Housing Features

Centerline (Pitch)	4 mm, 5 mm [.157 in][.197 in]
--------------------	-------------------------------

Dimensions

Product Width	26 mm [1.02 in]
Product Length	42.3 mm [1.66 in]
Product Height	24.3 mm [.956 in]
Row-to-Row Spacing	4.2 mm, 8.1 mm [.165 in][.318 in]

Usage Conditions

Operating Temperature (Max)	120 °C [248 °F]
Operating Temperature Range	-40 – 120 °C [-40 – 248 °F]

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	900
Packaging Method	Box

Other

Serviceable	No
Connector Position Assurance Capable	No

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Also in the Series | [AMP MCP Connector System](#)



Automotive Connector Caps & Covers (24)



Automotive Connector Locks & Position Assurance(7)



Automotive Housings(352)



Automotive Seals & Cavity Plugs(6)




Automotive Terminals(126)



Insertion & Extraction Tools(13)



Other Automotive Connector Accessories(2)




PCB Headers & Receptacles(29)

Customers Also Bought



TE Part #SRK06-FLB-64A-001
PLG, 64P, BLK, E, B




TE Part #1-1718491-1
AMP MCP, UNSEALED CONNECTOR HOUSING




TE Part #1456985-2
1X6 Fem unsealed LP assy Key B w /CPA




TE Part #HDP24-24-33PN-L017
REC, 33P, BLK, N, RNG, 20, P




TE Part #2317001-1
26POS,MCON 1.2,REC HSG ASSY,SLD




TE Part #2358789-2
MACROS_GM E2UB JCSB SquibLok cable 180D



TE Part #2358789-3
MACROS_GM E2UB JCSB SquibLok cable 180D



TE Part #2359441-1
7POS,AMP MCP 2.8,REC HSG,UNSLD



TE Part #936568-2
SPT 2P PLUG ASSY BLK

Documents



Product Drawings

CARRIER FOR RECEPTACLE INSERTS

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-1718484-1_D_c-1-1718484-1-d.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1718484-1_D_c-1-1718484-1-d.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1718484-1_D_c-1-1718484-1-d.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

German

Product Environmental Compliance

Product Compliance

English

Product Compliance

English