



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

Features

Other

Applicator & Product Style	OCEAN
----------------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2151096-1
OCEAN-2.0-APPLICATOR-S-062F125F



TE Part # 2151071-1
OCEAN_2.0_Applicator-S-062F074F



TE Part # 2151030-1
OCEAN_2.0_APPPLICATOR-S-062F110F



TE Part # 2-2151030-1
OCEAN_2.0_APPPLICATOR-S-062F110F



TE Part # 2-2151071-1
OCEAN_2.0_Applicator-S-062F074F



TE Part # 2-2151071-2
OCEAN_2.0_Applicator-S-062F074F



TE Part # 2-2151096-1
OCEAN-2.0-APPLICATOR-S-062F125F



TE Part # 2-2151130-1
OCEAN_2.0_Applicator-S-062F130F



TE Part # 2-2151130-2
OCEAN_2.0_Applicator-S-062F130F



TE Part # 2151030-2
OCEAN_2.0_APPPLICATOR-S-062F110F



TE Part # 2151071-2
OCEAN_2.0_Applicator-S-062F074F



TE Part # 2151096-2
OCEAN-2.0-APPLICATOR-S-062F125FA



TE Part # 2151130-1
OCEAN_2.0_Applicator-S-062F130F



TE Part # 2151130-2
OCEAN_2.0_Applicator-S-062F130F



TE Part # 2151627-1
OCEAN_2.0_Applicator-S-062F0800



TE Part # 2151627-2
OCEAN_2.0_Applicator-S-062F0800




TE Part # 2151753-1
OCEAN_2.0_Applicator-S-062F080F



TE Part # 2151753-2
OCEAN_2.0_Applicator-S-062F080F




TE Part # 7-2151071-1
OCEAN_2.0_Applicator-S-062F074F



KIT
REPRESENTATION ONLY

TE Part # 7-2151071-7
OCEAN_2.0_SPARE_PART_KIT-062F074F

Customers Also Bought



TE Part #3-1333202-3
ANVIL, COMBINATION .062




TE Part #1-1633962-5
CRIMPER, INSULATION F PREMIUM



TE Part #456408-6
CRIMPER, WIRE .110 F




TE Part #201414-4
SERIES "M" JACK SCREW--FEMALE A



TE Part #1-1633129-3
ANVIL, COMBINATION .062




ANVIL REPRESENTATION ONLY
TE Part #2-1463047-0
ANVIL, HI-CURRENT M



TE Part #1729419-1
ANVIL, COMBINATION (HD-C APPL)



ANVIL REPRESENTATION ONLY
TE Part #1729419-8
ANVIL, COMBINATION (HD-C APPL)



TE Part #3-1891632-8
WIRE ANVIL, SIDE FEED



TE Part #3-1891946-5
WIRE CRIMPER, SIDE FEED

Documents

Datasheets & Catalog Pages

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English