

1-1634009-0 ✓ ACTIVE


TE Internal #: 1-1634009-0

RF Connectors, MMCX RF Interface, Jack, 50 Ω, Snap-On, 6 GHz
Operating Frequency, Cable-to-Board, 1 Position, Printed Circuit
Board, Board Mount

[View on TE.com >](#)



Connectors > RF Coax Connectors > RF Connectors



RF Interface: **MMCX**

RF Connector Style: **Jack**

Impedance: **50 Ω**

RF Connector Coupling Mechanism: **Snap-On**

Operating Frequency: **6 GHz**

Features

Product Type Features

RF Interface	MMCX
RF Connector Style	Jack
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	1
PCB Mount Orientation	Vertical
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Shape	Square
Body Material	Brass



Body Material Finish	Plated
----------------------	--------

Body Plating Material	Gold
-----------------------	------

Contact Features

RF Connector Center Contact Underplating Material	Copper
---	--------

RF Connector Center Contact Plating Material	Gold
--	------

RF Connector Center Contact Material	Beryllium Copper
--------------------------------------	------------------

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Termination Post & Tail Length	2.95 mm[.116 in]
--------------------------------	------------------

Mechanical Attachment

RF Connector Coupling Mechanism	Snap-On
---------------------------------	---------

Connector Mounting Type	Board Mount
-------------------------	-------------

RF Contact Captivation Method	Mechanical
-------------------------------	------------

Detent	Without
--------	---------

Dimensions

Mounting Post Length	3 mm[.118 in]
----------------------	---------------

Profile Height from PCB	4.5 mm[.177 in]
-------------------------	-----------------

Usage Conditions

Operating Temperature Range	-65 – 165 °C[-85 – 329 °F]
-----------------------------	----------------------------

Operation/Application

Operating Frequency	6 GHz
---------------------	-------

Packaging Features

Packaging Quantity	100
--------------------	-----

Packaging Method	Bag & Box
------------------	-----------

Other

Grade	Professional
-------	--------------

Dielectric Material	PTFE
---------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC	Compliant with Exemptions
-----------------------------	---------------------------



China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2022 (223)
 Candidate List Declared Against: JAN 2022 (223)
 SVHC > Threshold:
 Pb (2.22% in Component Part)

Article Safe Usage Statements:
 Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2118898-2
 902~928 & 2400~2483.5 Dual Band Antenna



TE Part # 2118898-1
 902~928 & 2400~2483.5 Dual Band Antenna



TE Part # 1-1634002-0
 MMCX R/A Plg Hex 50Ohm Gold RG174A/U, 18



TE Part # 2108793-1
 FPC Ant, MMCX, 170mm, B5 & Wi-Fi 2.4GHz



TE Part # 2108793-2
 FPC Ant, MMCX, 240mm, B5 & Wi-Fi 2.4GHz



TE Part # 6-1634001-0
 MMCX Str. Plg Crimp Gold, RG178



TE Part # 6-1634003-0
 MMCX Elb Plg Crimp Gold, RG178



TE Part # 6-1634007-0
 MMCX Str PCB Flg Rept

Customers Also Bought



TE Part #2-2176231-1
3522 68R 1% 3W



TE Part #3-1614883-5
CPF 0805 33R 0.1% 25PPM 5K RL




TE Part #2-1614884-9
CPF 0805 33R 0.1% 25PPM 1K RL




TE Part #1-2176308-9
RP 1E 0.1W 205K 0.1% 25PPM 5K RL



TE Part #1SNA232006R2200
RC65 41->50 (X10) HORIZONTAL




TE Part #1SNA232243R0300
RC65 3 (X100) VERTICAL



TE Part #1501032-1
LP CSDFA 50A EUIC L10 J3AV



TE Part #2-1768339-5
LBF-18857650



TE Part #8-1768083-5
LBF-18237261

Documents

Product Drawings

[MMCX Str PCB Skt 50Ohm Gold Pl](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-1634009-0_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1634009-0_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1634009-0_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

1-1634009-0

RF Connectors, MMCX RF Interface, Jack, 50 Ω , Snap-On, 6 GHz Operating Frequency, Cable-to-Board, 1 Position, Printed Circuit Board, Board Mount



[MD_1-1634009-0_09082017515_dmtec](#)

English

[MD_1-1634009-0_09082017515_dmtec](#)

English