




DATASHEET Part No. 1001932PT Product: PCB WiFi Tunable Embedded Antenna with Cable

Part No. 1001932PT WLAN / BT / Zigbee / WiFi 6E Tunable Embedded PCB Antenna

2.4 GHz, 5 GHz, 6 GHz, 7 GHz

Supports: Wi-Fi applications, Agriculture, Bluetooth, Zigbee, WLAN, Smart Home, Healthcare, Digital Signage



PCB WiFi Tunable Embedded Antenna with Cable

2.4 GHz; 5 GHz 6 GHz; 7 GHz

KEY BENEFITS

Stay-in-Tune

KYOCERA AVX antenna technology provides superior RF field containment, resulting in less interaction with surrounding components.

Quicker Time-to-Market By

optimizing antenna size, performance and emissions, customer and regulatory specifications are more easily met.

Environmental Compliance Products are the latest RoHS version compliant.

APPLICATIONS

- Embedded Telematics design Tracking Healthcare Cellular, • Headsets, • M2M, Tablets Industrial devices Gateway, Access Smart Grid Point OBD-II
- Handheld

KYOCERA AVX WLAN antennas deliver on the key needs of device designers for higher functionality and performance in smaller/thinner designs. These innovative antennas provide compelling advantages for a 2.4 GHz, 5.0 GHz, 6.0 GHz, and 7.0 GHz enabled devices.

Real-World Performance and Implementation

Antennas may look alike on the outside, but the important difference is inside. Other antennas may contain simple PIFA or monopole designs that interact with their surroundings, complicating layout or changing performance with use position. KYOCERA AVX antennas utilize patented Isolated Magnetic Dipole (IMD) technology to deliver a unique size and performance combination.

The 1001932PT is offered in many standard cable lengths ranging up to 200mm. Ordering part number guide is located at end of document for selection ease.

Electrical Specifications

Typical Performance using 100 mm cable tested on PC-ABS

Frequency (GHz)	2.400 – 2.485	4.900 – 5.825	5.925 – 7.125		
Peak Gain	2.03 dBi	4.45 dBi	6.11 dBi		
Average Efficiency	61%	82%	63%		
VSWR Match	2:1 max	2:1 max	2:1 max		
Feed Point Impedance	50 ohms unbalanced				
Polarization	Linear				
Power Handling	2.0 Watt CW				

Mechanical Specifications

Ordering Part #	1001932PT-AA10L0100
Dimensions (mm)	35.2 x 8.5 x 1.8
Weight (grams)	0.8
Cable/Connector (mm)	Length: 100, Diameter: 1.13, Color: Black; u.Fl compatible connector
Mounting	Adhesive on bottom side of antenna
Packaging	PE bags


*Additional variations with different cable lengths, colors and connectors are available.

Proprietary



VSWR, Efficiency and Peak Gain Plots

Typical Performance using 100 mm cable tested on PC-ABS




TDS-ANT-0004 | Rev. 2



Antenna Radiation Patterns

Typical Performance using 100 mm cable tested on PC-ABS Measured @ 2440, 5550 MHz





►Z

012

TDS-ANT-0004 | Rev. 2

►Z

022

tel +(1) 858.550.3820 email: antenna.info@kyocera-avx.com 1 Avx Blvd, Fountain Inn, SC 29644

0/Z


►X



Antenna Radiation Patterns

Typical Performance using 100 mm cable tested on PC-ABS Measured @ 6425 MHz








Antenna Tuning Options

Typical Performance using 100 mm cable tested on PC-ABS



*This antenna has unique features enabling limited range RF tuning by leaving P1 - P6 and C1 - C2 connected by "solder bridge" or disconnected with a "cut" to the trace. Refer to detailed tuning options below.

Ref: Baseline = Typical Performance using 100 mm cable tested on PC-ABS

Options for Tuning: "2.4GHz (Lower)"

MODE	<u>T1</u>	<u>T2</u>	<u>T3</u>	<u>T4</u>
PADS	Connect: P2	Connect: P1	Connect: P2+P3	Connect: P1+P3
Outcome: (Ref: Baseline)	~200 MHz shift low	~250 MHz shift low	~350 MHz shift low	~370 MHz shift low

Options for Tuning: "2.4GHz (Higher)"

MODE	<u>C1</u>	<u>C2</u>
PADS	Cut: C1	Cut: C2
Outcome: (Ref: Baseline)	~170 MHz shift high	~300 MHz shift high

Options for Tuning: "5GHz (Lower)"

MODE	<u>T5</u>	<u>T6</u>	<u>T7</u>	<u>T8</u>
PADS	Connect: P4	Connect: P4+P5	Connect: P6	Connect: P5+P6
Outcome: (Ref: Baseline)	~200 MHz shift low	~1500 MHz shift low	~500 MHz shift low	~1900 MHz shift low




Mechanical Dimensions

Typical antenna dimensions

Part Number	A (mm)	B (mm)	C (mm)	D (mm) Cable Length
1001932PT-AA10L0100	35.2 ± 0.3	8.5 ± 0.3	1.8 (max)	100 ± 3.0

*Total Height "C" measures 1.8 mm includes the cable solder connection + PCB + adhesive thicknesses



Bottom View

© 2022 KYOCERA AVX

TDS-ANT-0004 | Rev. 2

tel +(1) 858.550.3820 email: antenna.info@kyocera-avx.com 1 Avx Blvd, Fountain Inn, SC 29644



Ordering Part Numbers

Typical antenna dimensions

Part Number	A (mm)	B (mm)	C (mm)	D (mm) Cable Length
1001932PT-AA10L0025	35.2 ± 0.3	8.5 ± 0.3	1.8 (max)	25 ± 3.0
1001932PT-AA10L0050	35.2 ± 0.3	8.5 ± 0.3	1.8 (max)	50 ± 3.0
1001932PT-AA10L0075	35.2 ± 0.3	8.5 ± 0.3	1.8 (max)	75 ± 3.0
1001932PT-AA10L0100	35.2 ± 0.3	8.5 ± 0.3	1.8 (max)	100 ± 3.0
1001932PT-AC10L0100	35.2 ± 0.3	8.5 ± 0.3	1.8 (max)	100 ± 3.0
1001932PT-AA10L0150	35.2 ± 0.3	8.5 ± 0.3	1.8 (max)	150 ± 4.0
1001932PT-AA10L0200	35.2 ± 0.3	8.5 ± 0.3	1.8 (max)	200 ± 4.0

*Total Height "C" measures 1.8 mm includes the cable solder connection + PCB + adhesive thicknesses (AA10L = MHF connector), (AC10L = MHF4L connector)