




Connectors > Lighting Connectors > LED Holders



Compatible LED: Everlight EAHP2024 Series, Lumileds 1204, Lumileds 1204 GEN 3, Lumileds 1204CRSP, Lumileds 1205, Lumileds 1205 GEN 3, Lumileds 1205CRSP, Lumileds 1208, Lumileds 1208 CRSP, Lumileds 1208 GEN 3, Sharp Mega Tuneable White, Sharp Mega Zenigata

Lighting Connector Features Included: Dimmable (Linear Profile), Driver on Board, Enables Zhaga Compatibility, Not Programmable, Optic Compatible, Thermal Protection

Operating Voltage: 48 VDC

Termination Method to Wire & Cable: Mini CT Connector

Output Current: 500 mA

## Features

### Product Type Features

Product Type	LED Holder
Flicker (% Max)	5
COB Substrate Thickness	1 mm
Connector System	Wire-to-Device
Sealable	No

### Configuration Features

Lighting Connector Features Included	Dimmable (Linear Profile), Driver on Board, Enables Zhaga Compatibility, Not Programmable, Optic Compatible, Thermal Protection
--------------------------------------	---

### Electrical Characteristics

Operating Voltage	48 VDC
Output Current	500 mA

### Body Features

Compatible LED	Everlight EAHP2024 Series, Lumileds 1204, Lumileds 1204 GEN 3, Lumileds 1204CRSP, Lumileds 1205, Lumileds 1205 GEN 3, Lumileds 1205CRSP, Lumileds 1208, Lumileds 1208 CRSP, Lumileds 1208 GEN 3, Sharp Mega Tuneable White, Sharp Mega Zenigata
----------------	---

### Contact Features

Contact Mating Area Plating Material	Gold
Contact Base Material	Copper Alloy

### Termination Features

Termination Method to Wire & Cable	Mini CT Connector
------------------------------------	-------------------

### Housing Features

Housing Material	PBT
------------------	-----

### Usage Conditions

Operating Temperature Range	0 – 125 °C[32 – 257 °F]
-----------------------------	-------------------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in



articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Also in the Series | LUMAWISE LED Holders



LED Holders(79)

## Customers Also Bought

TE Part #1-440055-1  
2.0MM,HDR,11POS,R/ATE Part #1623804-8  
SQZ10 3R3 5% WIRETE Part #TAA545B1411-060  
M12A4-MS-FS-PVC-6.0MTE Part #8-2176407-8  
3560 27R 5%TE Part #4-2176414-8  
7W STD M/OX 5% 1K8TE Part #4-1879350-2  
RR01 5% 11R AMMOTE Part #8-1419125-5  
SDT-S-106LMR,000TE Part #1-1393250-7  
W28-XQAT-15=W28

## Documents

### CAD Files

[3D PDF](#)

[3D](#)

### Customer View Model

[ENG\\_CVM\\_CVM\\_1-2316511-2\\_1.2d\\_dxf.zip](#)

English

### Customer View Model

[ENG\\_CVM\\_CVM\\_1-2316511-2\\_1.3d\\_igs.zip](#)



English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1-2316511-2\\_1.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Datasheets & Catalog Pages**

[LUMAWISE DRIVE LED HOLDER TYPE Z50 DALI VERSION](#)

English

**Product Specifications**

[Application Specification](#)

English

**Agency Approvals**

[DEKRA\\_CERT\\_2224069.50\\_C1](#)

English