

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



PCB terminal block, nominal current: 41 A, nom. voltage: 1000 V, pitch: 6.35 mm, number of positions: 2, connection method: Screw connection with tension sleeve, mounting: Wave soldering, conductor/PCB connection direction: 0 °, color: green

The figure shows a 5-pos. version of the product

Your advantages

- Easy to adapt, thanks to their identical size and the same pinning for Push-in spring connections as for screw connections
- Well-known connection principle allows worldwide use



Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	4 055626 501482
GTIN	4055626501482
Weight per Piece (excluding packing)	8.570 g
Custom tariff number	85369010
Country of origin	China

Technical data

Item properties

• •	
Brief article description	PCB terminal block
Range of articles	TDPT 4/SC
Pitch	6.35 mm
Number of positions	2
Connection method	Screw connection with tension sleeve
Drive form screw head	Slotted (L)
Screw thread	M3
Mounting type	Wave soldering



Technical data

Item properties

Pin layout	Zigzag pinning W
Number of levels	1

Electrical parameters

Rated current	41 A
Rated insulation voltage (III/2)	1000 V
Rated surge voltage (III/2)	8 kV

Connection capacity

Conductor cross section solid	0.2 mm² 6 mm²
Conductor cross section flexible	0.2 mm² 6 mm²
Conductor cross section AWG / kcmil	24 10
Conductor cross section flexible, with ferrule without plastic sleeve	0.2 mm² 4 mm²
Conductor cross section, flexible, with ferrule, with plastic sleeve	0.2 mm² 4 mm²
2 conductors with same cross section, solid	0.2 mm² 1.5 mm²
2 conductors with same cross section, flexible	0.2 mm² 1.5 mm²
Stripping length	10 mm
Torque	0.5 Nm 0.6 Nm

Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/ JEDEC JESD 201
Contact material	Cu alloy
Surface characteristics	hot-dip tin-plated
Metal surface terminal point (top layer)	Tin (4 - 8 µm Sn)
Metal surface soldering area (top layer)	Tin (4 - 8 µm Sn)

Material data - housing

Insulating material	PA
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0
Glow wire flammability index GWFI according to EN 60695-2-12	850
Glow wire ignition temperature GWIT according to EN 60695-2-13	775
Temperature for the ball pressure test according to EN 60695-10-2	125 °C

Dimensions for the product

Length [1]	20.75 mm
Width [w]	13.5 mm
Height [h]	26.9 mm
Pitch	6.35 mm
Height (without solder pin)	23.4 mm
Solder pin [P]	3.5 mm
Pin dimensions	0.9 x 0.9 mm



Technical data

Dimension a

$\overline{}$		•		
	imensions	: tor	tha	nroduct
\boldsymbol{L}	1111011310113	, 101	uic	product

Dimensions for PCB design		
Hole diameter	1.7 mm	
Packaging information		
Type of packaging	packed in cardboard	
Pieces per package	50	
Denomination packing units	Pcs.	
Ambient conditions		

6.35 mm

Ambient temperature (storage/transport)	-40 °C 70 °C
Ambient temperature (assembly)	-5 °C 105 °C
Ambient temperature (operation)	-40 °C

Termination and connection method

Test for conductor damage and slackening	IEC 60999-1:1999-11
	Test passed

Pull-out test

Pull-out test	IEC 60999-1:1999-11		
	Test passed		
Conductor cross section / conductor type / tensile force	0.2 mm² / flexible / > 10 N		
	0.2 mm² / solid / > 10 N		
	6 mm² / flexible / > 80 N		
	6 mm² / solid / > 60 N		

Mechanical tests according to standard

Test specification	IEC 60947-7-4
--------------------	---------------

Electrical tests

Rated current	41 A		
Rated insulation voltage (III/2)	1000 V		
Rated surge voltage (III/2)	8 kV		

Air clearances and creepage distances

Insulating material group	I
Voltage	800 V
Rated insulation voltage (III/3)	800 V
Rated insulation voltage (III/2)	1000 V
Rated insulation voltage (II/2)	1000 V
Rated surge voltage (III/3)	8 kV
Rated surge voltage (III/2)	8 kV
Rated surge voltage (II/2)	6 kV

Current carrying capacity / derating curves



Technical data

Current carrying capacity / derating curves

Specification	IEC 60947-7-4
Standards and Regulations	

Standards and Regulations


Connection in acc. with standard	EN-VDE		
Flammability rating according to UL 94	V0		

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e		
	No hazardous substances above threshold values		

Drawings





Type: TDPT 4/...-SC-6,35-ZB

Classifications

eCl@ss

eCl@ss 5.1	27261100
eCl@ss 6.0	27261100
eCl@ss 7.0	27440401
eCl@ss 8.0	27440401
eCl@ss 9.0	27440401

ETIM

ETIM 5.0	EC002643
ETIM 6.0	EC002643

Approvals

Approvals

Approvals

cULus Recognized



Approvals

Ex Approvals

Approval details

cULus Recognized http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm E60425-20180				E60425-20180122	
	D		В	С	
Nominal voltage UN	300 V		600 V	600 V	
Nominal current IN	10 A		30 A	30 A	
mm²/AWG/kcmil	24-10		24-10	24-10	

Accessories

Accessories

Crimping tool

Crimping pliers - CRIMPFOX 6 - 1212034



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm² ... 6.0 mm², lateral entry, trapezoidal crimp

Crimping pliers - CRIMPFOX CENTRUS 6H - 1213146



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² ... 6 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

Screwdriver tools

Screwdriver - SZF 1-0,6X3,5 - 1204517



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: $0.6 \times 3.5 \times 100 \text{ mm}$, 2-component grip, with non-slip grip



Phoenix Contact 2018 © - all rights reserved http://www.phoenixcontact.com