

Power supply unit - TRIO-PS-IP67/1AC/24DC/20 - 1039830

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



TRIO POWER primary-switched power supply in IP67 die-cast housing, input: 1-phase, output: 24 V DC / 20 A

Your advantages

- ✓ Direct installation at the load in the field reduces cable lengths and saves space in the control cabinet
- ✓ The robust design (die-cast aluminum housing) ensures high system availability, thanks to resistance to extreme environmental conditions (temperature, dust, and water)
- ✓ Reliable startup of high loads, thanks to the dynamic boost
- ✓ High efficiency of > 93%, thanks to low power losses



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4055626598703
Weight per Piece (excluding packing)	4,100.000 g
Custom tariff number	85044030
Country of origin	China

Technical data

Dimensions

Width	151 mm
Height	304 mm
Depth	120 mm

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 85 °C (Derating >60°C: 2.5 %/K)
Ambient temperature (start-up type tested)	-40 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Power supply unit - TRIO-PS-IP67/1AC/24DC/20 - 1039830

Technical data

Ambient conditions

Max. permissible relative humidity (operation)	≤ 95 % (at 25 °C, non-condensing)
Climatic class	3K3 (in acc. with EN 60721)
Degree of pollution	4
Installation height	≤ 4000 m (> 2000 m, Derating: 10 %/1000 m)

Input data

Nominal input voltage range	100 V AC ... 240 V AC
	110 V DC ... 250 V DC
Input voltage range	100 V AC ... 240 V AC #10 %
	110 V DC ... 250 V DC #10 %
Dielectric strength maximum	≤ 300 V AC 15 s
AC frequency range	50 Hz ... 60 Hz
Discharge current to PE	< 3.5 mA
Current consumption	5.6 A (100 V AC)
	2.4 A (240 V AC)
Nominal power consumption	36.8 W
Inrush surge current	typ. 20 A (at 25 °C)
Mains buffering	typ. 10 ms (120 V AC)
	typ. 15 ms (230 V AC)
Input fuse	10 A (internal (device protection))
Choice of suitable circuit breakers	10 A ... 16 A (Characteristics B, C, D, K)
Type of protection	Transient surge protection
Protective circuit/component	Varistor

Output data

Nominal output voltage	24 V DC ±1 %
Nominal output current (I _N)	20 A
Dynamic Boost (I _{Dyn.Boost})	30 A (5 s)
Derating	> 60 °C ... 70 °C (2.5%/K)
Output overvoltage protection	≤ 30 V DC
Control deviation	< 1 % (change in load, static 10 % ... 90 %)
	< 3 % (Dynamic load change 10 % ... 90 %, 10 Hz)
	< 0.1 % (change in input voltage ±10 %)
Residual ripple	≤ 30 mV _{PP}
Output power	480 W
Typical response time	< 1 s
Maximum power dissipation in no-load condition	< 3 W (120 V AC)
	< 2.5 W (230 V AC)
Power loss nominal load max.	< 48 W (120 V AC)
	< 36 W (230 V AC)

General

Power supply unit - TRIO-PS-IP67/1AC/24DC/20 - 1039830

Technical data

General

Net weight	3.7 kg
Efficiency	91 % (100 V AC)
	93 % (230 V AC)
Insulation voltage input/output	4 kV AC (type test)
	1.5 kV AC (routine test)
Protection class	I
Degree of protection	IP67
MTBF (IEC 61709, SN 29500)	> 1400000 h (25 °C)
	> 800000 h (40 °C)
	> 400000 h (60 °C)
Assembly instructions	Alignable: 20 mm horizontally, 50 mm vertically above, 100 mm vertically below

Connection data, input

Connection method	Circular connector
-------------------	--------------------

Connection data, output

Connection method	Circular connector
-------------------	--------------------

Connection data for signaling

Connection method	Circular connector
-------------------	--------------------

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise emission	EN 55011 (EN 55022)
Noise immunity	Immunity according to EN 61000-6-1 (residential), EN 61000-6-2 (industrial)
Standards/regulations	EN 61000-4-2
Contact discharge	4 kV (Test Level 2)
Standards/regulations	EN 61000-4-3
Frequency range	80 MHz ... 1 GHz
Test field strength	10 V/m (Test Level 3)
Frequency range	1.4 GHz ... 2 GHz
Test field strength	3 V/m (Test Level 2)
Standards/regulations	EN 61000-4-4
Comments	Criterion B
Standards/regulations	EN 61000-6-3
	EN 61000-4-6
Frequency range	0.15 MHz ... 80 MHz
Voltage	10 V (Test Level 3)
Conducted noise emission	EN 55016 EN 61000-6-4 (Class A)
Standards/regulations	EN 61000-4-11
Low Voltage Directive	Conformance with Low Voltage Directive 2014/35/EC
Standard - Electrical safety	IEC 61010-2-201 (SELV)

Power supply unit - TRIO-PS-IP67/1AC/24DC/20 - 1039830

Technical data

Standards and Regulations


Standard – Safety extra-low voltage	EN 60204-1 (PELV)
Standard - Safe isolation	DIN VDE 0100-410
Standard – Limitation of mains harmonic currents	EN 61000-3-2
Shock	18 ms, 30g, in each space direction (according to IEC 60068-2-27)
Vibration (operation)	In each space direction (in acc. with EN 60068-2-6) 10 Hz - 19.9 Hz, ±2.5 mm amplitude, 19.9 Hz - 150 Hz, 4g acceleration
Overvoltage category (EN 61010-1)	III (≤ 2000 m)

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Drawings

Block diagram



Classifications

eCl@ss

eCl@ss 8.0	27049002
eCl@ss 9.0	27040701

ETIM

ETIM 5.0	EC002540
----------	----------

Approvals

Approvals

Approvals

CSA

Ex Approvals

Approval details

Power supply unit - TRIO-PS-IP67/1AC/24DC/20 - 1039830

Approvals

CSA



<http://www.csagroup.org/services-industries/product-listing/>

70175690

Accessories

Accessories

Circular connector (cable-side)

Power connectors - SACC-M12FSS-2PECON-PG 9-M - 1419640



Power connectors, 3-position, Socket straight M12, S-coded, Screw connection, knurl material: Zinc die-cast, nickel-plated, cable gland Pg9, external cable diameter 6 mm ... 8 mm, for AC current up to 16 A/230 V

Cable connector - ST-3EP1N8A8005 - 1624534



Cable connector, straight, Screw locking, M17, number of positions: 3+PE, type of contact: Pin, Crimp connection, shielded: yes, cable diameter range: 10 mm ... 12.5 mm

Connector - SACC-FS-5SC M SCO - 1432583



Connector, 5-position, Socket straight M12 SPEEDCON, A-coded, Spring-cage connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 4 mm ... 8 mm