



ENGL

Datasheet  
Stock No. 106-5309  
**RS MAGNETIC FIELD METER**



**Feature:**

- Display micro-Tesla & milli-Gauss in the same tester.
- Over load indication.
- Low battery Indication.
- Data hold and maximum hold function.

## Specifications:

- Display: LCD display with maximum reading of 1999.
- Sampling Rate: 2.5 times per second.
- Sensor: Single axis.
- Frequency response: 30Hz to 300Hz.
- Measuring Range: 200/2000 mG, 20/200 $\mu$ T.
- Accuracy:  $\pm(2.5\%\pm 6\text{dgt})$  at 50Hz/60Hz.
- Power Supply: 9V NEDA 1604, IEC 6F22, JIS 006 P. battery x 1pc.
- Battery life: About 100 hours
- Dimension: (LxWXH): 130mm x 55mm x 38mm.
- Weight: Approx. 160g with battery
- Accessories: Manual, 9V battery and carrying bag.