



Application Tooling > Portable Crimp Tools



TE Certification: **Cannot be Certified**

Power Technology Type: **Manual**

Tooling Type: **Insertion/Extraction Tool**

Features

Other

TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	Insertion/Extraction Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #812846-000
Bulbous Heat Shrink Boots: Lipped,
Right Angle



TE Part #F99802-000
S200-3-W1-22-9



TE Part #253627-000
MTCP-122-20S2



TE Part #650126-000
D-436-82



TE Part #625022-000
D-110-00



TE Part #350521-000
55A1831-24-MST3-9CS2275



TE Part #460870N003
S02-07-R-9CS925



TE Part #733509N001
S02-17-R-5CS928



TE Part #675684N001
S02-18-R-4CS1092

Documents

Product Drawings

CTA-1160

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_110219-000_O_c-110219-000-o.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_110219-000_O_c-110219-000-o.3d_igs.zip](#)

English



Customer View Model

[ENG_CVM_CVM_110219-000_O_c-110219-000-o.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.