
## Magnifier luminaire RING LED RLLQ 63 R


113142000-00618830











light source work equipment connected load power consumption luminous flux luminous efficiency light distribution direct ratio colour temperature colour temperatur color rendering index (CRI) chromaticity tolerance LED system of protection class of protection technology operation housing

fastening lens, dimensions lens, diopters

add-on lens

mains lead

cover

arm

electronic plug-in transformer
100-240 V, 50/60 Hz
env. 6 W
approx. 420 Im
approx. 70 Im/W
direct
approx. 100 %
neutral white
approx. 5.000 K
>= 90 (R9>50)
< 3 SDCM
IP 20
II

continuously dimmable
Touch-LED
aluminium/plastic; anodised; black

Acrylic satine aluminium coloured anodised

approx. 2.3 m; mains plug; CEE 7/XVI; BS 1363; NEMA 1-15P table clamp (accessory); wall bracket (accessory);

screw-down flange; magnetic base (accessory)
Ø 72 mm

6 1