
Pivoting-head luminaire ROCIA.focus RFJ 600/850/S


113185000-00680293






CE 🚇







light source work equipment connected load power consumption luminous flux luminous efficiency light distribution beam angle colour temperature colour temperatur color rendering index (CRI) chromaticity tolerance LED glare control luminance (L65) unified glare rating (4H 8H) system of protection class of protection technology operation housing cover mains lead fastening accessory special features

LED without 12-28V AC and 12-40V DC env. 8 W approx. 550 lm approx. 69 lm/W direct, wide-angled beam 30° neutral white approx. 5.000 K >= 80 < 4 SDCM screen $<= 6000 \text{ cd/m}^2$ <= 19 IP 67 Ш switchable external aluminium; anodised; black glass screen approx. 3,7 m; with free stranded wires wall bracket (accessory); screw-down flange; magnetic base (accessory); table base ballast Flood with 40° angle of radiation

Pivoting-head luminaire ROCIA.focus RFJ 600/850/S



113185000-00680293

