




CE



**light source**  
**work equipment**  
**connected load**  
**power consumption**  
**luminous flux**  
**luminous efficiency**  
**light distribution**  
**direct ratio**  
**colour temperature**  
**colour temperatur**  
**color rendering index (CRI)**  
**chromaticity tolerance LED**  
**system of protection**  
**class of protection**  
**technology**  
**operation**  
**housing**  
**cover**  
**arm**  
**balance of articulation joints**  
**weight (net)**  
**mains lead**  
**fastening**  
**lens, dimensions**  
**lens material**  
**lens, diopters**  
**special features**

LED  
 electronic plug-in ballast  
 100-240 V, 50/60 Hz  
 env. 13 W  
 approx. 750 lm  
 approx. 58 lm/W  
 direct  
 approx. 100 %  
 neutral white  
 approx. 4.000 K  
 >= 90 (R9>50)  
 < 3 SDCM  
 IP 20  
 II  
 multi-stage switchable; continuously dimmable  
 multi-function switch  
 plastic; untreated; black  
 screen, milky; Polyamide  
 tubular aluminium section; anodized; aluminium  
 coloured anodised  
 spring  
 env. 3 kg  
 approx. 3.4 m; mains plug; CEE 7/XVI; BS 1363;  
 NEMA 1-15P  
 screw-down flange  
 Ø 160 mm  
 glass  
 3,5  
 long arms; light characteristic can be adjusted with  
 a three-way switch