


113A.C - CHROMED ADJUSTABLE WRENCHES



Description :

- Tool equipped with a FACOM SLS attachment solution, preventing any risk of accidental falls.
- Good access to the button = easy setting.
- Non-protruding moving jaw at maximum capacity.
- Pre-adjustment of jaw opening thanks to millimetric gradation.
- Right-hand button rotation.
- Range from 4" to 24".
- Presentation: chromed body and polished head faces.
- Clés à molette avec trou dans le manche : accrochage directe par mousqueton.



References :

	A [mm]	B [mm]	E [mm]	L [mm]	L1 [mm]	[g]
113A.8C	27	61,5	6,5	206	24	275
113A.10C	30	69,5	9,0	255	29	480
113A.12C	34	80,0	10,0	306	34	700
113A.15C	44	97,0	13,5	380	44	
113A.18C	53	115,0	16,0	456	53	