



**light source**

- work equipment**
- connected load**
- Power consumption**
- luminous flux**
- luminous efficacy**
- colour temperature**
- color rendering index (CRI)**
- chromaticity tolerance LED**

- System of protection**
- class of protection**
- technology**
- operation**
- luminaire body**
- lamp cover**
- tubular sections**

- balance of articulation joints**
- weight (net)**
- mains lead**

- Fastening**
- lens; dimensions**
- lens material**
- lens; diopters**
- special features**

**LED**

Energy efficiency category A/A+/A++  
 electronic plug-in ballast  
 100-240 V; 50/60 Hz  
 approx. 13 W  
 approx. 750 lm  
 approx. 57 lm/W  
 neutral white, approx. 4000 K  
 >= 90 (R9>50)  
 3 SDCM  
 IP20  
 II  
 multi-stage switchable, continuously dimmable  
 multi-function switch  
 plastic, untreated, black  
 screen, milky, Polyamide  
 tubular aluminium section, anodized, aluminium coloured  
 anodised  
 spring  
 approx. 2.0 kg  
 approx. 3.6 m; mains plug  
 BS 1363  
 CEE 7/XVI  
 NEMA 1-15P  
 screw-down flange  
 Ø 160 mm  
 PMMA  
 3,5  
 2D head joint, light characteristic can be adjusted with a three-way switch



BS 1363



CEE 7/XVI



NEMA 1-15P

**illuminance**

distance: 15 cm

Em: 4099 lx  
 Emax: 5537 lx  
 Emin: 1894 lx

