

Product Image



/publicpictures/Produktbild/1171410301.tif

Master data

Product number:	1171410301
EAN:	4007123671557
Artikelverantwortlicher:	Brennenstuhl Tübingen
manufacturer:	Brennenstuhl
Product line:	BF
Kundenspezifisch:	No
Minimalpflege:	No
Ausleitungskennzeichen:	J
Gewählte Vertriebsregion:	De
Gewählte Sprache:	en

Texts

Is4-Bezeichnung 1/2:

Mob.360°LED Akku Strahler BF 3000 MA 3000lm, IP54, eingeb. Akku

Short description for the internet:

Brennenstuhl LED 360° lighting / rechargeable Work light (Portable LED Floodlight 3000lm with Charging Indicator, max. 12h lighting duration, Construction Light for outside, IP54)

Website-Kurztext:

Print-Kurztext:

360° Rechargeable LED work light BF 3000 MA 3000lm, IP54

Bulletpoint 1:

LED work lamp with integrated Li-Ion battery provides 360° room lighting and can be used standing, hanging or mounted on a tripod

Bulletpoint 2:

Construction light with on/off switch is perfectly suited for permanent outdoor use thanks to its IP54 protection class (dust and splash-proof)

Bulletpoint 3:

LED floodlight 30W made of robust, break and impact resistant plastic case is ideal for painting work or use on construction sites

Bulletpoint 4:

The LED work lamp has three lighting modes: 100% - 50% - 25% for long duration of light

Bulletpoint 5:

Scope of delivery:

1x LED 360° work light 30W, on/off switch, Li-Ion battery (11,1V/4,4 Ah) with charging indicator - in best brennenstuhl® quality

Online-Beschreibung:

The stable 360° LED Battery Spotlight BF 3000 MA by Brennenstuhl is perfectly suited for permanent outdoor use thanks to its protection class IP54. Thanks to its 360° angle, the construction light provides glare-free, low-shadow room illumination. In addition, the work light convinces with the following features:

*Luminous flux: 3000 lm

*Colour temperature: 6500 K

*Battery Technology: Lithium-Ion

*Voltage: 11.1 V

- *Battery capacity: 4.4 Ah
- *Lighting duration max.: 12 h
- *Charging time: approx. 5 h
- *Degree of protection (IP): IP54
- *Impact strength: IK08
- *Protection class: III
- * Category 2 (K2) equipment: for use in harsh environments with high mechanical, physical and chemical impact

Website description:

Schlagworte:

brennenstuhl, work light, led work light, led worklight, led flood light, led floodlight, inspection lamp, rechargeable work light, rechargeable flood light, site lights, rechargeable led work light, rechargeable led floodlight, rechargeable led flood light

Subtitle:

For indoors and outdoors use, IP54, IK08.

Print-Beschreibung:

- * Excellent all-round lighting thanks to 360° beam angle, anti-glare and wide diffusion.
- * Switch with light functions 100 - 50 - 25 %.
- * The light can be used when placed upright, hanging or mounted on a stand.
- * Robust, break and impact resistant plastic casing.
- * Integrated lithium-ion battery 11.1 V/4.4 Ah with charging indicator.
- * With ON/OFF switch.
- * In colourful display-packaging.

Infotext:

Table article information:

Scope of supply:

Media



/publicpictures/icon/icon-schutzart-ip54.eps



/publicpictures/icon/icon-stosstest-ik08.eps



/publicpictures/icon/icon-inclusive-akku-batterie-li-ion.eps



/publicpictures/icon/icon-leuchtdauer-12h-max.eps



/publicpictures/icon/icon-lumen-3000.eps



/publicpictures/Detailansicht/1171410301-schalter.tif



/publicpictures/Detailansicht/1171410301-ladeanzeige.tif



/publicpictures/Detailansicht/1171410301-oben.tif



/publicpictures/Detailansicht/1171410301-unten-laden.tif



/publicpictures/Detailansicht/1171410301-unten.tif



/publicpictures/Ausstattung/1171410301-netzstecker.tif



/publicpictures/Anwendung/1171410301-anwendung-haken-haengend.tif



/publicpictures/Anwendung/1171410301-1170310020-anwendung-kfz-werkstatt-karosserie-6.tif




/publicpictures/Anwendung/1171410300-1171410500-1171410301-anwendung-baustelle-4.tif



/publicpictures/Anwendung/1171410300-1171410500-1171410301-ambiente-baustelle-1.tif



/publicpictures/Anwendung/1171410301-1171411500-anwendung-haken-haengend-schalter.tif



/publicpictures/Anwendung/1171410301-baustelle-industriehalle-stativ-4.tif



/publicpictures/Anwendung/1171410301-baustelle-industriehalle-stativ-1.tif

/restrictedpictures/QR-Code/1171410301-qr-code-info.eps

Context

Attributkategorie:

Light

Accessories:

Garantie:

Other (legal)

Ersatzteil:

0172640058

Similar products:

Technical data

Batterie		Dimmable:	No
Battery type:	Built-in battery pack	Remotely controllable:	No
Battery technology:	Lithium-ion	With wireless control:	No
Rechargeable:	Yes	Handling:	mobile
Replaceable:	No	Suitable for surface mounting:	No
Number of cells:	6	Suitable for built-in mounting:	No
Light duration:	12h	Suitable for ceiling mounting:	No
Capacity:	4.4Ah	Suitable for wall mounting:	No
Voltage:	11.1V	Suitable for suspended mounting:	No
IEC indication:	ICR18650	With mounting bracket:	No
Einsatz im Ex-Bereich - ep:	No	With mounting materials:	No
With battery charging indicator:	Yes	With fastening strap:	No
With battery status indicator:	Yes	Degree of protection (IP):	IP54
Low-voltage indicator:	No	Suitable for outdoor area:	Yes
With backup battery:	No	Impact strength:	IK08
Included backup battery rechargeable:	No	Shock resistance:	No
Traction battery:	No	Watertight:	No
Power:	48.84Wh	Min. operation temperature:	-10°C
Loading current:	1,000mA	Max. operation temperature:	40°C
Charging time:	5h	Leuchte3Stecksystem	
Dangerous goods regulations:	Yes	With socket outlet:	No
Closed (sealed):	Yes	Leuchtmittel0Allgemein	
Leuchte0Allgemein		Lamp type:	LED non-replaceable
Type of lamp:	Floodlight	Leuchtmittel1Betriebseigenschaften	
Type of accessories:	Tripod	Colour rendering index CRI:	80-89 (class 1B)
Housing material:	Plastic	Colour temperature:	6,500K
Housing colour:	black	Colour of light - ep:	865
Colour cover:	white	Fluorescent colour:	white
Colour:	black	Multicolour- switch steps:	No
Lamp type included:	Yes	Netzteil	

Number of lamps:	66	externes Netzteil:	Yes
Number of batteries:	1	Frequency at external charger unit:	50/60 Hz
Battery included:	Yes	Min. Nominal input voltage:	100V
Collapsible/ Bendable:	No	Max. Nominal input voltage:	240V
With carrying handle:	No	With power supply:	Yes
With turn handle:	No	Type of plug - Input:	Type C (euro plug)
Hook rotatable:	Yes	Type of plug - Output:	Hollow plug 2.5 mm
Number of hooks:	1	With charge cable:	Yes
Integrated magnet:	No	Mgv	
Height adjustable:	No	Packaging unit (UP):	1
With loudspeaker:	No	Weight of product (without packaging):	1.48kg
With radio:	No	Length of product (without packaging):	21cm
With frame:	No	Width of product (without packaging):	20.5cm
With tripod holder:	No	Height of product (without packaging):	22.5cm
With ground spike:	No	Weight of product (including packaging):	1.95kg
With protective grille:	No	Length of product (including packaging):	21.5cm
With pocket torch function:	No	Width of product (including packaging):	21cm
Focus:	No	Height of product (including packaging):	29cm
Laserpointer:	No		
With quick-acting facility:	No		
Colour controllable (RGB):	No		
Packaging:			
Lamp efficacy:	100lm/W		
Fluorescent colour:	white		
Luminous flux:	3,000lm		
Leuchte1elektrWerte			
Protection class:	III		
Power supply:	Rechargeable battery		
Load input for external power supply:	Yes		
Leuchte2Anwendung			
With light sensor:	No		

With on/off switch:	Yes
Illuminated switch:	No
With twilight switch:	No
With motion detector:	No

Variantgroup

360° Rechargeable LED Work Light

- * Excellent all-round lighting thanks to 360° beam angle, anti-glare and wide diffusion.
- * Switch with light functions 100 - 50 - 25 %.
- * The light can be used when placed upright, hanging or mounted on a stand.
- * Robust, break and impact resistant plastic casing.
- * Integrated lithium-ion battery 11.1 V/4.4 Ah with charging indicator.
- * With ON/OFF switch.

Related Article

1171410301

Variant Differentiation