


# VALUE Flat DisplayPort Cable, v1.4, DP-DP, M/M, black, 3 m

<b>Product No.</b>	11.99.5863
<b>Manufacturer</b>	VALUE
<b>Manufacturer No.</b>	11.99.5863
<b>EAN (single piece)</b>	7630049626973



**8K**

**HDR**

**VALUE DisplayPort Cable with DP connection on both sides for connecting an Ultrabook, Notebook/Laptop or PC to a monitor, TV or projector - for screen transmissions in excellent quality with resolutions of up to 7680x4320 @60Hz!**

- DisplayPort is a universal connection standard for the transmission of picture and sound signals, widely known and appreciated in computer, industry and modern house wiring. Applications include mainly the connection of monitors or projectors to computers, notebooks/laptops, ultrabooks, NUCs and similar devices.
- The connector requires less space than VGA or DVI and is therefore more suitable for portable devices for two connectors on a graphics card (on one slot plate).
- DisplayPort v1.4 supports Display Stream Compression 1.2a (DSC), Forward Error Correction and the HDR10 standard.
- DP v1.4 can reach a maximum resolution of 8K (7680x4320) @60Hz or 4K (3840x2160) @120Hz
- The practical plug design prevents the cable from slipping out of the DisplayPort socket and guarantees a stable audio and video transmission.
- Compliant DP v1.4 (max. 7680 x 4320 @60Hz)

**Technical specifications**

Manufacturer	VALUE
Product group	Cable
Product type	DisplayPort Monitor Cable
Colour	black
Length	3 m
Transfer quality	DisplayPort v1.4
Max. resolution	7680 x 4320 @60Hz (8K, UHD-2)
side 1 connector	DisplayPort M
side 2 connector	DisplayPort M
Side 1 Connector Type	DisplayPort
Side 1 Connector Gender	Male
Side 2 Connector Type	DisplayPort
Side 2 Connector Gender	Male
Ribbon cable	Yes
Area of application	External
Cable shielding	Screened
Height of packaging (single piece)	20 mm
Width of packaging (single piece)	100 mm
Depth of packaging (single piece)	100 mm
Package weight (single piece)	0.3 kg