WIRE STRIPPERS


Insulation Strippers

- > for single, multiple and fine stranded conductors with plastic or rubber insulation max. 5.0 mm dia. or resp. 10 mm² cable cross section
- > easy adjustment to the required diameter of solid or stranded wire with knurled screw and lock nut
- > Special tool steel, forged, oil-hardened





11



	EAN	4->					Stripping ca		47	
Article No.	4003773-	mm		Pliers	Head	Handles	Ømm	mm ²	AWG	g
11 01 160	013556	160	MM	black atramentized	polished	plastic coated	5.0	10	7	131
11 02 160	023180	160	MM	black atramentized	polished	with multi-component grips	5.0	10	7	165
11 05 160	039570	160	MM	chrome plated		with multi-component grips	5.0	10	7	157
11 06 160	021933	160	£ 1000 V @€ \\\\	chrome plated		insulated with multi-component grips, VDE-tested	5.0	10	7	166
11 07 160	015499	160	<u> </u>	chrome plated		with dipped insulation, VDE-tested	5.0	10	7	180
11 12 160	034964	160		black atramentized	polished	with multi-component grips	5.0	10	7	156
11 17 160	015505	160	£ 1000 V 🖄 🚰	chrome plated		with dipped insulation, VDE-tested	5.0	10	7	181


Electronics Wire Stripping Shears

11 8





- > for cutting and stripping single, multiple and fine-stranded conductors with up to 0.75 mm² cable cross-section
- > easy adjustment to the required diameter of solid or stranded wire with knurled screw and lock nut
- > with opening spring
- > Special tool steel, oil-hardened



	EAN	∢ —▶				Stripping capacities	52
Article No.	4003773-	mm		Head	Handles	mm ²	g
11 82 130	071648	130	X\$\$ MM	polished	with multi-component grips	0.01 - 0.75	75