

FEATURES

- Flexible LSZH lead conforming to Harmonisation code H05Z1Z1-F
- Terminated with IEC C14 and C13 connector
- Rated at 230/240 V ac, 10 A maximum
- Fully moulded connector design for strength and durability
- Reliable integrated strain relief for connection support and protection

RS PRO 3m Power Cable, LSZH C13, IEC to C14, IEC, 10 A

RS Stock No.: 123-0961



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS Pro a high quality and durable power cable assembly or power extension cord for connecting a computer to a monitor or printer or extending an existing power lead. This extension cord is fully equipped with an IEC C13 type connector on one end and an IEC C14 connector on the other. The cable features integrated strain reliefs that provide additional protection and support to the connectors and protects them against damage from excessive bending

General Specifications

Connector A	C13, IEC
Connector B	C14, IEC
Sheath Colour	Black
Mains Plug Type	IEC 60320 C14
Mains Socket Type	IEC 60320 C13
Fire Behaviour	Low Smoke Zero Halogen (LSZH)
Connector A Angle	Straight
Connector B Angle	Straight
Connector A Gender	Female
Connector B Gender	Male
Terminals	Brass
Conductor	3 Wire
Applications	DIY and home improvements Maintenance work Household entertainment (TVs, satellite boxes, routers etc.) Industrial machines and equipment Office desks (Monitors, computers, phones) Any electrical device needed to be powered by the mains

Electrical Specifications

Current Rating	10A
Voltage Rating	230/240V
Insulation Resistance	>10MΩ
Cable Retention	0.5mm ² -1mm ² >30N 1.25mm ² -1.5mm ² >60N
Electrical Strength	2.5kV 50Hz
Safety Test	4.4kV 50Hz
Capacitance	95.08pF/m
Inductance	0.43μH/m

Mechanical Specifications

Length	3m
Weight	175g
Withdrawal Force	10N-50N
Gauge	1.5mm ²

Operation Environment Specifications

Maximum Pin Temperature	65°C
--------------------------------	------

Approvals

Compliance/Certifications	CE / UR / cUR
Standards Met	IEC 60320

