

#### **FEATURES**

- Clears dirty water and is suitable for general duties
- High volume water pump is Ideal for flooded basement
- Float switch turns the pump on and off automatically
- Comfortable carry handle
- Can be fully submerged and works in depth of up to 7 m
- Clears dirty water and is suitable for general duties
- High volume water pump is Ideal for flooded basement

# RS PRO, 230 V Submersible Water Pump, 216L/min

RS Stock No.: 124-1949



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



## **Product Description**

RS PRO submersible water pumps, designed to clear dirty water in general applications. These high volume water pumps are ideal for flooded basements, rain socked foundations or draining containers. Offers a float switch which turns the pump on and off automatically with changes to the water level.

#### **General Specifications**

Туре	Submersible Water Pump
Maximum Flow Rate	216L/min
Output Connection Size	1" (25mm); 1-1/4" (32mm); 1-1/2" (40mm)
Maximum Pressure	20psi/10bar
Body Material	Plastic
Maximum Fluid Temperature	35°C
Application	Residential, Commercial, Municipal And Industrial Water Extraction Application

### **Mechanical Specifications**

# **Electrical Rating**

Phase	750W
Supply Voltage	230V/50Hz

#### **Protection Category**

IP Rating	IPX8



