




© Waldmann-Leuchten



QUICKTRONIC® PROFESSIONAL



QTP-DL 2x55/220-240

Your benefits

- Improved thermal behavior for even smaller luminaires
- Long life time of 50,000 hours*
- Exceptionally reliable end-of-life safety shutdown as per Test 2
- Only 6 instead of 11 types for space-saving and cost-saving storage
- Uniform wiring and geometry with the appropriate QT_i, QT_i DIM and QT_i DALI® devices for 55W types
- Combi-Wiring terminal for automatic or manual wiring

Applications

- New creative and economical luminaire solutions in small spaces
- Modern luminaires for foyers, offices, retail outlets and exhibition rooms
- Floor-standing luminaires, wall lights, film lights and ceiling coffer luminaires

* for $t = 75^{\circ}\text{C}$ at t_c ; max. failure rate of 10 %

NEW!

QUICKTRONIC® PROFESSIONAL QTP-DL Electronic control gear


Fewer types, more options: The innovative range of ECG as perfect partners for all OSRAM DULUX® L and OSRAM DULUX® F lamps.

SEE THE WORLD IN A NEW LIGHT

OSRAM



TECHNICAL DATA



Product reference	Product number		V ¹⁾ min-max	kHz ECG	A	λ
QUICKTRONIC® PROFESSIONAL for OSRAM DULUX® L and OSRAM DULUX® F						
QTP-DL 1x18-24/220-240	4008321117861	1xDL 18, 1xDF 18	198...264	45-50	0.085	0.95
		1xDL 24, 1xDF 24		45-50	0.115	0.95
QTP-DL 2x18-24/220-240	4008321117885	2xDL 18, 2xDF 18	198...264	41-46	0.16	0.98
		2xDL 24, 2xDF 24		41-46	0.22	0.98
QTP-DL 1x36-40/220-240	4008321117908	1xDL 36, 1xDF 36	198...264	45-50	0.17	0.99
		1xDL 40		45-50	0.21	0.99
QTP-DL 2x36-40/220-240	4008321117922	2xDL 36, 2xDF 36	198...264	45-50	0.33	0.99
		2xDL 40		45-50	0.41	0.99
QTP-DL 1x55/220-240	4008321117946	1xDL 55	198...264	45	0.28	0.97
QTP-DL 2x55/220-240	4008321117960	2xDL 55	198...264	45	0.55	0.97

Product reference	W SYSTEM	Im	°C min-max	l [mm]	b [mm]	h [mm]	a [mm]		
QTP-DL 1x18-24/220-240	18	1x1200, 1x1100	-20...+50	239	30	28	230	20	190
	26	1x1800, 1x1700							
QTP-DL 2x18-24/220-240	36	2x1200, 2x1100	-20...+50	239	40	28	230	20	230
	49	2x1800, 2x1700							
QTP-DL 1x36-40/220-240	35	1x2900, 1x2800	-20...+50	239	30	28	230	20	190
	45	1x3500							
QTP-DL 2x36-40/220-240	68	2x2900, 2x2800	-20...+50	280	40	28	270	20	290
	90	2x3500							
QTP-DL 1x55/220-240	59	1x4800	-20...+50	360	30	21	350	20	260
QTP-DL 2x55/220-240	128	2x4800	-20...+50	423	30	21	415	20	400

¹⁾ Sinusoidal line voltage



If ECGs and lamps from OSRAM are used together, OSRAM offers a full five-year guarantee on selected electronic control gear.*

* after registering the system and under certain conditions of use; for terms and conditions and information on registration go to: www.osram.com/system-guarantee



SEE THE WORLD IN A NEW LIGHT

