





Datasheet

## Foot Switch, Lightweight Polymeric Housing

RS Article No.125-3717



## **Specifications:**

**Operating Frequency:** 60 ops/min Insulation Resistance: >100 MΩ@500 V dc Contact Resistance:  $<25 \text{ m}\Omega$  (initial) Rated Current/Voltage: 15 A,1/2HP,125/250 V ac Dielectric Strength : 1000 V ac for 1 min between current carrying parts 2500 V ac for 1 min between non-current carrying parts Mechanically 1 x 10<sup>6</sup> Electrically 5 x 10<sup>5</sup> Service Life: Operating Temperature : -20~+80° C (-4~176° F) Degree of Protection: **IP20** 100 x 75 x 33 mm Size (L x W x H):

10/05/2016

## Features:

- Robust glass fiber reinforced plastic
- UL/CSA/CE Certified
- Galvanically separated contacts
- SPDT TYPE
- Momentary type



