Dimensions



Model Number MLV12-54-LAS/92/120

position

•

•

•

٠

•

•

Features

Retroreflective sensor

standard housing

thanks to small light spot

to 0 mm: no blind zone

tal housing frame

ration under all conditions

with 4-pin M12 connector, 90° adjustable

Series of sensors in a widely used

Visible red light, pulsed LASER light

Precision: high degree of repeatability


Objects can be reliably detected down

Resistant against noise: reliable ope-

High level of stability thanks to the me-

M4 / ODUC M12x1

Electrical connection





Pinout





Wire colors in accordance with EN 60947-5-2

2 3

BN WH BU BK (brown) (white) (blue) (black)

Indicators/operating means





USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com PEPPERL+FUCHS



UB

 I_0

 U_{d}

Technical data General specifications Effective detection range

Reflector distance

Reference target Light source

Polarization filter

Laser class

Wave length Beam divergence

Pulse length

Repetition rate

max. pulse energy

Angle of divergence

Continuous light Modulated light

Ambient light limit

Mission Time (T_M)

Operation indicator

Function indicator

Control elements

Operating voltage

Switching type

Signal output

Voltage drop

Response time

Housing height

Housing depth Degree of protection

Connection Material

Housing

Mass

ves

Optical face

Standard conformity

Product standard

Vibration resistance

Approvals and certificates Protection class

Pepperl+Fuchs Group

www.pepperl-fuchs.com

Laser class

UL approval

CCC approval

Compliance with standards and directi-

Shock and impact resistance

Ambient conditions

Ambient temperature

Storage temperature

Mechanical specifications Housing width

Switching voltage

Switching current

Switching frequency

Ripple

Output

Electrical specifications

No-load supply current

Diagnostic Coverage (DC)

Indicators/operating means

 $\mathsf{MTTF}_{\mathsf{d}}$

Diameter of the light spot

Functional safety related parameters

Laser nominal ratings

Light type

Note

Threshold detection range

	Accessories
0 12 m	OMH-MLV12-HWG
0 12 m	Mounting bracket for series MLV12 sen-
17 m	sors
MH82 reflector	OMH-MLV12-HWK
laser diode	Mounting bracket for series MLV12 sen-
modulated visible red light	sors
yes	ONUL Kod
LASER LIGHT , DO NOT STARE INTO BEAM	OMH-K01
1	dove tail mounting clamp
650 nm	OMH-K02
< 1.5 mrad	dove tail mounting clamp
1.8 μs	
17.86 kHz	ОМН-К03
6.7 nJ	dove tail mounting clamp
approx. 5 mm x 12 mm at 15 m detection range	OMH-01
0.02 °	Mounting aid for round steel ø 12 mm or
50000 Lux	sheet 1.5 mm 3 mm
5000 Lux	
	OMH-06
930 a	Mounting aid for round steel ø 12 mm or
10 a	sheet 1.5 mm 3 mm
0 %	REF-MH82
	Reflector with Micro-structure, rectangu-
LED green, flashes in case of short-circuit	lar 82 mm x 60 mm, mounting holes
2 LEDs yellow, light up when light beam is free, flash when falling	-
short of the stability control, off when light beam is interrupted	REF-MH50
rotary switch for light/dark, sensitivity adjuster	Reflector with Micro-structure, rectangu-
10 30 V DC	lar 50.9 mm x 50.9 mm, mounting holes,
max. 10 %	fixing strap
max. 40 mA	REF-MH78
	Reflector with Micro-structure, hexagonal
light/dark on switchable	78 mm x 61 mm, mounting holes
2 PNP outputs, complementary, short-circuit protected, reverse	-
polarity protected, open collector	REF-MH20
max. 30 V DC max. 0.1 A	Reflector with Micro-structure, rectangu-
≤ 2.5 V DC	lar 32 mm x 20 mm, mounting holes
2500 Hz	REF-MA21
0.2 ms	Reflector with Micro-structure, round ø 21
	mm, self-adhesive
-10 50 °C (14 122 °F)	
-20 65 °C (-4 149 °F)	Other suitable accessories can be found at
	www.pepperl-fuchs.com
41.5 mm	
49 mm	
15 mm	
IP67 4-pin, M12 metal connector, 90° rotatable	
Frame: nickel plated, die cast zinc,	-
Laterals: glass-fiber reinforced plastic PC	
Plastic pane	
60 g	
-	
EN 60947-5-2:2007	
IEC 60947-5-2:2007	
IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions	
IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions	-
IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11	
except for deviations pursuant to Laser Notice No. 50, dated	
June 24, 2007	
II, rated voltage \leq 300 V AC with pollution degree 1-2 accor-	
ding to IEC 60664-1	
cULus Listed, Type 1 enclosure	
CCC approval / marking not required for products rated <36 V	


USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com


CCC approval / marking not required for products rated ≤36 V

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS



Curves/Diagrams



Laser notice laser class 1

- The irradiation can lead to irritation especially in a dark environment. Do not point at people!
- ٠ Maintenance and repairs should only be carried out by authorized service personnel!
- Attach the device so that the warning is clearly visible and readable.
- The warning accompanies the device and should be attached in immediate proximity to the device. •
- Caution - Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

www.pepperl-fuchs.com

