

RAFIX 22 FS⁺, illuminated pushbutton, protruding front ring, round collar, momentary contact function, frontring light gray, bezel blue



fields of application

- > Measurement-control-regulation
- > Electrical engineering
- > Mechanical and system engineering
- > Vehicle construction
- > Handheld terminals
- > Industrial robots

special features

- > Illuminated pushbutton, panel illumination with SMT LED
- > Low installation depth 9.2 mm (PCB) or 27 mm (QC)
- Special tactile feedback
- > Ideal for operation with gloves
- > Connection types: printed circuit board connection (PCB) or plug-in connection
- > PCB switching elements minimize assembly errors
- > Switching elements with silver contacts (max. 250 V/4 A) or gold contacts (max. 35 V/100 mA)
- > The tactile switch adapter allows MICON 5 tactile switches to be used as switching elements
- > Design adaptation by different front ring variations
- > Degree of protection: IP 65 at the front
- > Two collar shapes: round and square











description

RAFIX control devices are defined at RAFI as modular elements, consisting of an actuating element, if necessary a coupling and an individual contact or lighting unit.

Actuating elements (such as pushbuttons, emergency stop actuators, etc.) have the intended tactility, reset and function only when assembled with the appropriate switching elements.

Pushbutton with translucent bezel. In combination with a corresponding switching element, the bezel can be fully illuminated.



technical data

> general

Disassembly possible no

Bezel color blue

Property of bezel / mushroom translucent Front ring color light gray Collar shape round Operating temperature, min. -25 °C 70 °C Operating temperature, max. -40 °C Storage temperature, min. 80 °C

illuminated Yes Packaging Box Packaging unit 10 pcs. net weight 6.7 q

Operating life 1,000,000 cycles B10 1,300,000 cycles

Degree of protection, front side,

according to DIN EN 60529

Storage temperature, max.

UL Enclosure Type Rating front type 1 type 4X

Environment resistance IEC 60068-2-14

> IEC 60068-2-30 IEC 60068-2-33 IEC 60068-2-78 IEC 60068-2-11

IP65

Salt-spray resistance according to

standard

MOQ order 100 pcs. RoHS compliant Yes **REACH** compliant Yes

> mounting diameters

Outside dimension, length 29.8 mm Outside dimension, width 29.8 mm Outside dimension, height 21.5 mm Mounting hole 22.3 mm Mounting depth 9.2 mm 12.85 mm Installation height Grid, min. 30 x 30 mm Collar dimension ø 29.8 mm

> mechanical data

Actuation function momentary contact function

Operating force, max. 100 N Operating travel, max. 4 mm

Threaded ring Fixing


Threaded ring torque, max. 1.2 Nm direct links

> RAFI eCatalog



drawings

Dimensioned drawing




System drawing




RAFI GmbH & Co. KG



System drawing




Mounting hole drawing



acc. to IEC 60947-5-1



front panel drawing



RAFI GmbH & Co. KG

Ravensburger Str. 128-134